

# Onyx

Simply NUC Business NUC – NUC130Xi7 / NUC130XKi7



Simply **NUC**<sup>®</sup>

# Onyx i7

## Simply NUC Business NUC – NUC130Xi7 / NUC130XKi7 Unmatched Performance for Modern Business

Onyx is the latest and greatest in ultra-small form factor compute power from Simply NUC, driving unmatched performance for modern business from the desk to the edge to the cloud and back. Powered by Intel's 13th Gen Raptor Lake 13700H processor and kept cool with Simply NUC's Dual Exhaust Cooling solution, Onyx has support for up to 64GB of DDR5-5200 memory, up to 16TB of storage, and off-the-charts benchmark results, delivering all the power, without the tower.

### Onyx - Defined by You, Built for You

Onyx may be a Simply NUC product, but it was defined by our customers, and built to meet your needs, with key features like dual HDMI 2.1, dual USB 4.0 Type-C, and a 2.5Gb Ethernet port to name a few. The Onyx NUC gives you the ability to expand its feature set to match your specific usage needs, with a rear I/O expansion panel on the full height chassis and a replaceable lid, giving you a plethora of additional I/O options such as USB, HDMI, LAN, or serial ports. From office workstations, to on-prem heavy edge computing, to robotics and sophisticated IoT networks, Onyx i7 has the flexibility and performance options to perfectly serve your usage requirements.

### Performance with Uncompromised Security and Reliability

Powered by Intel's 13th Gen Raptor Lake 13700H processor, featuring 14 cores and 20 threads, Onyx packs outsized performance into a small chassis. Raptor Lake processors feature Intel Thread Director, using machine learning to schedule tasks on the right core at the right time, preventing background tasks from slowing you down, and keeping the focus on the primary workload. Keep your fleet of 24x7 tested computers with Intel Boot Guard, keeping your system's pre-OS environment safe from viruses and malicious software attacks. Upgrade to Onyx i7 today, and enjoy uncompromised and highly reliable processing power.

### Features

- Intel® Core™ i7-13700H Processor
- Intel® Iris® Xe Graphics
- 2x DDR5-5200 SO-DIMM Sockets
- 1x M.2 22x80 M-key supporting PCIe x4 Gen4 NVMe
- 1x 2.5" drive bay supporting SATA SSDs (Full height chassis only)
- MicroSD card slot
- TPM (Infineon 2.0)
- 2x HDMI 2.1 TMDS
- 2x USB 4 Type-C (Alt-DP)
- Intel® Wi-Fi 6E + Bluetooth 5.2
- 1x Intel 2.5Gb LAN
- 2x USB 4 Type-C
- 3x USB 3.2 Gen2 Type-A
- 1x USB 2.0 Type-A
- 3.5mm stereo headset jack
- Kensington lock support
- VESA mount included
- 19V, 120W power supply included
- Extended service support (3-year)



### Customization

- Primary storage up to 8TB Gen4 NVMe
- Secondary 2.5" drive up to 8TB SATA SSD (full height chassis only)
- Memory up to 64GB
- Replaceable lid for I/O expansion
- Rear panel expansion (Full height chassis only)
- OS options: Windows 11 Home & Pro, Windows IoT, Ubuntu

# Technical Specification

<b>Processor</b>	Intel® Core™ i7-13700H Processor   6P+8E/20T   P-Cores: up to 5.0 GHz - E-Cores: up to 3.7 GHz   24MB Intel® Smart Cache   45W TDP
<b>Graphics</b>	Intel® Iris Xe Graphics up to 1.50GHz   4x 4K Displays Supported via: 2x HDMI 2.1 TMDS + 2x USB-C (Alt-DP)   1x 8K Display supported via USB-C (Alt-DP)
<b>Memory</b>	Dual DDR5-5200 SODIMMs 1.2V   64GB Max
<b>Storage</b>	1x M.2 22x80 socket supporting PCIe x4 Gen4 NVMe from 128GB to 8TB or SATA SSD from 128GB to 2TB   1x 2.5" bay supporting SATA SSDs (128GB to 8TB) (full height chassis only)
<b>Peripherals</b>	Intel Wi-Fi 6E AX210 + Bluetooth 5.2   1x Intel 2.5Gb LAN (i225-V)   1x Front USB 3.2 Gen2 Type-A   1x Front USB 2.0 Type-A   2x Rear USB 4 Type-C   2x Rear USB 3.2 Gen2 Type-A
<b>Chassis</b>	117x112x54mm (Full height) / 117x112x37mm (Slim height)   Kensington lock support   VESA mount kit support
<b>Expansion</b>	1x USB 2.0 header   1x USB 3.0 header   1x COM header (RS-232/422/485)   1x Front panel header   Replaceable lid   Rear expansion panel (Full height chassis only)
<b>Audio</b>	3.5mm Front Stereo Headset Jack
<b>Power</b>	12-24V <sub>DC</sub> Input Supply Range   19V <sub>DC</sub> , 120W Power Supply Included

## Certifications and Regulations

<b>Safety Regulations and Standards</b>	J62368-1 (2020)   GB 17625.1-2012   GB 4943.1-2011   GB/T 9254.1-2021 (Class A)   KCC   UL 62368-1: 2019   EN IEC 62368-1:2020
<b>EMC/RF Regulations &amp; Standards</b>	FCC CFR Title 47, Chapter I, Part15, Subparts B, C, E   ETSI EN 301 489-1 V2.2.3 (2019-11)   Draft ETSI EN 301 489-17 V3.2.5 (2022-08)   EN 55032:2015   EN 55035:2017   EN IEC 61000-3-2:2019   EN 61000-3-3:2013   ETSI EN 300 328 V2.2.2 (2019-07)   EN 61000-3-3:2013
<b>Environmental Regulations</b>	RoHS Compliant   REACH Compliant
<b>Certified Operating Systems</b>	Windows 11 (Pro and Home)   Windows IoT   Linux (Ubuntu)
<b>Environmental Operating Temp etc.</b>	0°C to +40°C   Non-Condensing Humidity