

M/Flex for M2.1 M8.1 and M10

Model Number: X8NTNCEWCTBCTB---18-----

List Price (As of 06/05/24): CAN\$2,149.00

Buy Now Price: CAN\$1,521.00



FEATURES

- Scalable solution accommodates future additions of up to 6 monitors
- Compatible with Humanscale’s M2.1, M8.1 and M10 monitor arms
- Reduces future installation costs by allowing for simple reconfigurations
- Available with accessories such as Notebook Holders, Crossbars, Thin Client Holders, UFEAs, Colored VESA Covers and Sliders
- Patent-pending Smart Stop allows the user to customize the rotation of the arm, preventing overhang and protecting surrounding equipment.
- Patent-pending Quick Release Joints instantly snap together for a secure and robust fit, simplifying installation
- Compatible with M/Connect, M/Connect 2 and M/Power, the first-ever integrated monitor arm bases and docking stations of their kind

SPECIFICATIONS

Maximum Arm Reach - Up to 28”

Maximum Height Adjustment - Up to 10” dynamic // 30” static

Monitor Capacity - Up to 6 monitors

Color Options:

- Polished Aluminum with White Trim
- Silver with Gray Trim
- Black with Black Trim

Product Material - Recycled Aluminum

Warranty - 15 years 24/7

CONFIGURATION DETAILS

CODE DESCRIPTION

- X8 - M/Flex for M8.1 Monitor Arm
- NT - Base Without Technology
- N - No Technology
- C - Clamp
- E - Two Single Monitor Brackets for 2 Monitors
- W - Polished Aluminum with White Trim
- C - 4" Straight Link/Dynamic Link
- T - Standard Monitor Tilt (one per monitor)
- B - Standard 100mm x 100mm, black
- C - 4" Straight Link/Dynamic Link
- T - Standard Monitor Tilt (one per monitor)
- B - Standard 100mm x 100mm, black
- 18 - 18" High Post

SUSTAINABILITY

By purchasing this product you are helping create a cumulative Net Positive impact on the environment by the following amounts:

Climate Positive - M2.1: 2 kg CO2 M8.1: 2kg CO2 M10: 3kg CO2

Water Positive - M2.1: 5 k Gallons M8.1: 5 k Gallons M10:6 k Gallons

Energy Positive - M2.1: 4 kWh M8.1: 6 kWh M10: 9 kWh

FIND OUT MORE

[Humanscale.com](https://www.humanscale.com)

To see all Humanscale Terms and Conditions, please visit:

www.humanscale.com/terms-conditions