



Models may vary from the image shown

THE ULTRA-CUSTOMIZABLE K5. VERSION 2.
One of the most customizable keyboards in the world – now the first gaming keyboard to be equipped with CHERRY MX2A switches. K5V2 is the next level in design and performance.

CHERRY MX2A RED SWITCHES.
The world's most trusted mechanical keyboard switch just got better. CHERRY MX2A is a transformative upgrade to the CHERRY MX – used in more than 60 million keyboards worldwide. With precisely applied premium-grade lubricant and a new innovative spring design, the MX2A brings you smoother actuation, improved acoustics, and a lifespan of 100 million keystrokes. And if you'd like to try different switch characteristics to find the perfect touch and feel, the switches are hot-swappable so you can easily replace them – no soldering required.

CUSTOMIZE EVERYTHING.
Customizing your keyboard has never been easier. On the K5V2, everything from the switches, stabilizers and keycaps to the cable, frame and even the little plate for the logo is swappable.

65% SIZE.
This keyboard comes in a 65% format – bringing you

an extremely compact design without sacrificing the convenience of arrow keys.

HOW TO GET FASTER: SUPER-SCAN TECHNOLOGY.
Your keyboard is never faster than its ability to detect your keystrokes – no matter how many times per second it reports to the computer (Polling rate). The K5V2 features a new super-scan technology, scanning all keys every half a millisecond.

UNBELIEVABLE RGB.

“The best RGB experience we’ve had” said one of the UK’s largest tech review sites about the previous generation of Xtrfy keyboards. On the K5, we’ve developed the RGB implementation even further to bring you a more impactful illumination than ever. Connecting the keyboard to a USB 3 port? Switch to USB 3 mode to boost the RGB!

OUR SMALLEST BUT MOST ADVANCED KEYBOARD YET.

Small doesn't mean less. This keyboard is extremely compact yet fully featured, with per-key customizable RGB illumination, macros, media controls and more. All settings are made using the keys. No software needed.

BUILD QUALITY ON A NEW LEVEL.

Feel. Sound. Durability. It all comes down to build quality. The K5 is built with a metal plate construction, double layers of sound-dampening foam and high-quality PCB-mounted stabilizers – pre-lubed by hand.

HIGHLIGHTS

- 65% size
- Ultra-customizable
- Strip LED RGB illumination
- Hot-swappable CHERRY MX2A Red switches
- Super-scan technology for instant response
- Pre-lubed PCB-mounted stabilizers
- Double layers of sound-dampening foam

PRODUCT SPECIFICATIONS

Weight main product:	30 oz
Dimensions product without packaging:	12,8 in x 4,33 in x 1,46 in
Cable-length:	6.56 ft
Product approvals:	<ul style="list-style-type: none"> • CE • FCC • KCC • UKCA • BSMI • China RoHS • EU RoHS • Taiwan RoHS • CB • IC
Scope of delivery:	<ul style="list-style-type: none"> • Keyboard • USB-cable • key cap puller • Manual • 2 spare switches
Keyboard format:	Compact (65%)
N-key rollover:	N-Key Rollover

Anti-ghosting:	yes
Response time:	1 ms
Palm rest:	Palm rest available as accessory
Special key functions:	<ul style="list-style-type: none"> • FN Key • Illumination settings • Media controls • Play/Pause • Volume up • Volume down • Unmute/Mute
Illumination:	Strip LED RGB
Adjustable feet:	integrated
Status LEDs:	in housing
Key technology:	Mechanical
Switches:	CHERRY MX2A RED
Keycap material:	ABS
Model number:	CX-K5V2-RGB-CPT

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Designation

K5V2 COMPACT

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.