



Rugged, convertible Chromebook

The rugged HP Fortis x360 Chromebook provides reliability and performance in a rugged 360-degree design. It features an Intel® quad-core processor^[8], plenty of memory, and long battery life for productivity throughout the day. The 360-degree hinge allows multiple modes of use, while enhanced durability testing gives you peace of mind.



Immersive 360-degree design

Work with flexibility in laptop, tablet, tent, or stand mode, thanks to a durable 360-degree hinge.

Durable, reliable design

Designed and tested for durability, featuring a keyboard that resists picking, minor spills, and dust.^[12]

Productivity empowered

Quickly access data, apps, and more in crowded wireless networks with Wi-Fi 6E^[6] and an Intel® quad-core processor.^[8]

Featuring

Simplify deployments

Get a low-maintenance experience with the automatic software updates and virus protection of the Chrome OS.^[1]

Universal connectivity and charging with USB-C™

Use the USB-C™ port to access and charge your USB-C™ accessories from your Chromebook™ or charge your Chromebook™ from any USB-C™ adapter.

Apps and content for expanded learning

Take learning in new directions with access to the Google Play™ Store and Android™ apps, which include thousands of instantly shareable and easily manageable innovative education apps.^[1]

Simple PC management

Spend less time and get right to the updates you need with HP Support Assistant.^[2]

Advanced wireless connectivity

Stay connected, even in crowded wireless networks, with a fast, reliable wireless connection. This Fortis Chromebook's Wi-Fi 6E or optional Wi-Fi 6 wireless LAN comes with MU-MIMO, HP Extended Range Wireless LAN, and supports Bluetooth® technology.^[3]

Specifications

Operating system	ChromeOS
Product color	Jack black
Processor family	Intel® Processor N-series
Processor	Intel® Processor N200 (up to 3.7 GHz with Intel® Turbo Boost Technology, 6 MB L3 cache, 4 cores, 4 threads) ^[6,7]
Memory	8 GB LPDDR5x-7500 MHz RAM (onboard)
Internal Storage	64 GB eMMC
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics
Display	11.6" diagonal, HD (1366 x 768), touch, BrightView, 250 nits, 50% NTSC ^[10,11,12,13]
Display size (diagonal)	11.6"
Audio	Waves MaxxAudio®, dual speakers, dual array microphones
Minimum dimensions (W x D x H)	29.5 x 20.4 x 2.1 cm
Minimum dimensions (W x D x H)	11.61 x 8.03 x 0.78 in
Weight	Starting at 1.46 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Weight	Starting at 3.21 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Keyboard	Full-size, island-style, flint gray keyboard
Camera	8 MP camera
Ports	2 USB Type-C® 5Gbps signaling rate (USB Power Delivery, video and data support); 2 USB Type-A 5Gbps signaling rate; 1 HDMI 1.4; 1 stereo headphone/microphone combo jack <i>(HDMI cable sold separately.)</i>
Package dimensions (W x D x H)	6.7 x 43.5 x 26 cm
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card
Power	45 W USB Type-C™ adapter
Battery type	HP Long Life 2-cell, 47 Wh Li-ion polymer
Battery weight	0.42 lb
Battery weight	190 g
Sustainable impact specifications	Low halogen; Bulk packaging available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 2% post-consumer recycled plastic
UPC number	197961956474
Manufacturer Warranty	1 year (1/1/0) limited warranty includes 1 year of parts and labor. No on-site repair. Terms and conditions vary by country. Certain restrictions and exclusions apply.

Top Recommended Displays, Accessories and Services

P-Series

HP P27h G5 FHD Monitor	64W41AA
HP P24h G5 FHD Monitor	64W34AA

Personal Systems Commercial Care Pack Services

HP 3y Care Notebook HW Supp	U67XQE
HP 3y Onsite Care Notebook HW Supp	U67XXE
HP 3y Active Care Next Business Day Response Onsite Notebook HW Supp	U67WYE

Speakerphones

Poly Sync 20+ USB-C Speakerphone	772D0AA
Poly Sync 20 USB-C Speakerphone	7F0J7AA
Poly Sync 10 USB-A USB-C Speakerphone	772C3AA

Wireless Headset

Poly Voyager Focus 2 USB-C-C Headset +USB-C/A Adapter	9T9J3AA
Poly Voyager 4320 USB-C Headset +BT700 dongle +Charging Stand	77Z31AA

Wired Headset

Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA
---	---------

Wireless Keyboards

HP 355 Compact Multi-Device Bluetooth Keyboard	692S9AA
HP 475 Dual-Mode Wireless Keyboard	7N7B9AA

Wired Keyboards

HP 405 Multi-Device Backlit Wired Keyboard	7N7C1AA
--	---------

Wired Mice

HP Wired Desktop 320M Mouse	9VA80AA
-----------------------------	---------

Wireless Mice

HP 245 Bluetooth Mouse	81S67AA
------------------------	---------

Messaging Footnotes

[1] Internet access required and sold separately. Some apps may require purchase.

[2] Internet access required.

[3] Wi-Fi 6E requires a Wi-Fi 6E router, sold separately, to function in the 6GHz band. Availability of public wireless access points limited. Wi-Fi 6E is backwards compatible with prior 802.11 specs and available in countries where Wi-Fi 6E is supported. Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 (802.11 ax) is backwards compatible with prior 802.11 specs. Multiple-Input Multiple-Output (MU-MIMO) is a wireless technology that uses multiple transmitters and receivers to enhance data transfer. MIMO requires a MU-MIMO router, sold separately.

[6] Wi-Fi 6E requires a Wi-Fi 6E router, sold separately, to function in the 6GHz band. Availability of public wireless access points limited. Wi-Fi 6E is backwards compatible with prior 802.11 specs and available in countries where Wi-Fi 6E is supported.

[8] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of clock speed.

[12] HP Total Test Process testing is not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[10] FHD/HD content required to view FHD/HD images.

[11] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[12] Actual brightness will be lower with touchscreen.

[13] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. © 2023 Google LLC All rights reserved. Google and the Google Logo are registered trademarks of Google LLC.

