

SRG-X400

Standard 4K30P IP PTZ
Camera with 30x (w/CIZ)
zoom and NDI®|HX
capability for a wide range of
applications



Overview

Capture every point of view with excellent 4K* picture quality and efficient IP production workflow

The versatile SRG-X400 remotely controlled PTZ camera is ideal for a wide range of applications—from classrooms and meeting spaces to faith centers, lecture halls, and medical environments.

The camera's 1/2.5-type Exmor R™ sensor captures up to 4K* resolution images with excellent sensitivity, very low noise, and rich, natural color reproduction. It's complemented by the integrated high-resolution lens that offers zoom capability up to 40x in Full HD*** (30x in 4K), with an expansive wide-angle coverage of approx. 70 ° to capture every point of view.

High speed movement during preset recall captures the speaker's every movement, while Picture Freeze during transitions ensures your audience isn't disturbed by rapid camera movements. PTZ Motion Sync*** function allows smooth blending of separate pan, tilt and zoom movements for seamless, professional-looking transition.

Efficient IP-based live production is augmented with

support for NDI®|HX (via optional license), allowing flexible configuration with other networked NDI®-enabled devices.

Images also can be reviewed remotely via a web browser, with support for RTSP (Real Time Streaming Protocol), RTMP*** (Real Time Messaging Protocol) and SRT*** (Secure Reliable Transport) ensuring smooth, stable streaming of video plus audio (from an optional microphone, available separately) over an IP network.

Installation and set-up is easy, with a new Picture Setting File**** allowing the same settings to be applied to multiple cameras through a web interface from a laptop or PC.

*NDI® is a registered trademark of NewTek, Inc.

**With Clear Image Zoom and Tele Convert Mode

***Requires firmware V3.00

****Requires firmware V2.00

Note 1: This product contains pre-installed software and requires the purchase of license keys to activate some functions.

Note 2: When using RM-IP500 firmware should be updated to V2.10 and for RM-IP10, firmware should be updated to V2.17.

Features

Excellent images, even in low light

The sensitive 1/2.5-type Exmor R™ sensor captures high-quality images with very low noise, even in dimly lit environments.

4K upgrade option

Upgrade to 4K shooting via optional license.

Up to 40x zoom

Powerful zoom up to 40x* (in Full HD) allows finely detailed frame-filling close-ups. Responsive autofocus ensures that images stay clear and sharp, even at high zoom settings.

*With Clear Image Zoom

Wide viewing angle

Cover the whole scene in meetings and lecture theaters with a horizontal viewing angle of approx. 70°.

Ideal for lecture capture

Use the camera in conjunction with the AI-based REA-C1000 Edge Analytics Appliance to smoothly track the speaker's movements and automatically generate a cut-out image of speaker.

High-speed movement and Picture Freeze Preset

Accurately capture the presenter's movements with maximum 300°/s pan and tilt movement during preset recall. Picture Freeze Preset maintains a steady image while the camera moves to a new preset position—with no uncomfortable transitions for your audience.

Smooth pan-tilt-zoom

PTZ Motion Sync function* allows smooth blending of separate pan, tilt and zoom movements for seamless, professional-looking transitions.

*Requires firmware V2.00.

Simpler installation, lower costs

A single network cable carries camera power, video

output, and control signals to simplify installation and reduce cabling costs.

Support for NDI®*|HX

NDI®|HX compatibility (via optional license) enables cost-effective school studio system integration, allowing flexible configuration with other networked NDI®-enabled devices.

Network services, content, and the operating system and software of this Product may be subject to individual terms and conditions and changed, interrupted, or discontinued at any time and may require fees, registration, and credit card information.

Flexible and efficient IP-based production

In addition to RTSP, RTMP(S)* and SRT* (Secure Reliable Transport) are supported. Video can be streamed directly from a camera to an online streaming service, and can be transmitted more securely, with lower latency and more stably even in unstable network environments.

* Requires firmware V3.00.

Fast, fuss-free set-up

The new Picture Setting File* function can apply the same camera settings among multiple cameras for fast set-up.

*Requires firmware V2.00.

Specifications

Camera

Image Sensor

1/2.5 Exmor R CMOS

Image Sensor (Number of Effective Pixels)	Approx. 8.5M pixels
Signal System	2160 ^{*1} / 29.97p, 25p, 23.98p 1080/59.94p, 50p, 29.97p, 25p, 23.98p 1080/59.94i, 50i 720/59.94p, 50p
4K Capability	Yes (requires 4K optional license)
Minimum Illumination (50IRE)	1.6 lux (1/30s 50IRE F2 high-sensitivity OFF)
Horizontal Resolution	1700 TV lines (Center) (4K ^{*1}) 1000 TV lines or higher (Center) (FHD)
Gain	Auto/Manual (0 to +48 dB) (High Sensitivity On)
Shutter Speed	1/1 to 1/10000 sec (59.94 Hz system) 1/1 to 1/10000 sec (23.98 Hz system) 1/1 to 1/10000 sec (50 Hz system)
Exposure Control	Auto, Manual, Priority AE (Shutter, Iris)
White Balance	Auto1, Auto2, One Push WB, Indoor, Outdoor, Manual
Zoom capability	30x (4K ^{*1} with CIZ**), 40x (HD with CIZ)

**CIZ = Clear Image Zoom

Focusing System	Auto/Manual
Horizontal Viewing Angle	Approx. 70° (Wide)
Focal Length	f=4.4 mm (Wide) to 88.0 mm (Tele) F2.0 to F3.8
Minimum Object Distance	80 mm (Wide)~ 800 mm (Tele)
Pan/Tilt Angle	Pan: ±170° Tilt: +90°/-20°
Pan/Tilt Speed (Max.)	Pan: 300°/s Tilt: 126°/s
Pan/Tilt Speed	Pan: 1.1° to 101°/s Tilt: 1.1° to 91°/s
Pan/Tilt Speed (Slow)	Pan: 0.5° to 60°/s Tilt: 0.5° to 60°/s
Pan/Tilt Slow Mode	Yes
Pan/Tilt Operation Noise	NC30 or less* *Sony measurement conditions
Preset Position	256 (CGI) 100 (VISCA)
Picture Freeze Preset	Yes
PTZ Motion Sync	Yes

Network

IP Video Resolution	3840 x 2160* ¹ , 1920 x 1080, 1280 x 720, 720 x 576, 720 x 480, 640 x 360
Compression Format	H.264: High, Main, Baseline Profile H.265: Main Profile
Maximum Frame Rate	H.264: 60 fps H.265: 60 fps
Bitrate Compression Mode	CBR/VBR (selectable)
Range of Bitrate Setting	512 Kbps ~50 Mbps
Multi Streaming Capability	3
Maximum Number of Clients	5
Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, DHCP, DNS, RTP/RTCP, RTSP, UPnP, VISCA over IP
NDI® HX Capability	Yes (requires a license; sold separately)

Camera Features

Auto ICR (Auto mode of IR Cut filter Removal)	Yes
---	-----

Day/Night	Yes
Visibility Enhancer	Yes
Image Stabilization	Yes
Image Flip	Yes
Picture Setting File	Yes
Flicker Cancel	On/Off
Hide OSD Menu	On/Off
Standby Mode	Yes
Remote Standby	Yes

Web UI

Ver Up	Yes
--------	-----

Audio

Channel	2 ch
Audio Codec	AAC LC 128 kbps/ST (IP) AAC LC 256 kbps/ST (IP)
Setting Option	Auto Level Control (ALC): On/Off Equalizer: Off, Low cut, Voice enhancement Input selection: Microphone/Line Mic volume: -10 to +10 (21 steps) Audio codec

Embedded Audio in Baseband Video	Yes (3G-SDI, HDMI)
----------------------------------	--------------------

Embedded Audio in IP Streaming	Yes
--------------------------------	-----

Interface

4K Video Output	HDMI x1 and IP (streaming) x1*1
-----------------	---------------------------------

HD Video Output	3G-SDI x1, HDMI x1, IP (streaming) x1
-----------------	---------------------------------------

Remote Video Format Switching	Yes
-------------------------------	-----

HDMI Color Space	YCbCr, 4:2:2 8 bit RGB, 4:4:4 8 bit
------------------	--

Camera Control Interface	VISCA RS-422 RJ45 (In/Out) VISCA over IP RJ-45
--------------------------	---

IR Remote Control	Yes
-------------------	-----

Microphone Input	Mini-phone (φ3.5mm) x2 (Mic/Line Selectable)
------------------	---

Sync. System	INT
--------------	-----

Power Connector Type	IEC60130-10 (JEITA standard RC-5320A) TYPE4
----------------------	---

General

Power	DC 12V (DC 10.8 to 13.2V),
-------	----------------------------

Requirements	PoE+ (IEEE802.3at compliant)
Power Consumption	25.5 W Max.
Operating Temperature	0 °C to 40 °C (32 °F to 104 °F)
Storage Temperature	-20°C to + 60°C -4 °F to + 140 °F
Dimensions (W x H x D) ^{*2}	158.4 x 177.5 x 200.2 mm 6 1/4 x 7 x 8 inch
Mass ^{*2}	Approx. 1.8 kg 3 lb 15.5 oz
Camera Body Color	White/Black
Size of Screw Hole for Tripod	1/4-20UNC x1
Mountable Angle	< ±15°
Ceiling Mount	Yes
Supplied Accessories	AC power adapter (1) IR Remote Commander Unit (1) Ceiling bracket (2) Wire rope (1) Screw M3 x 8(8) Screw M2.6 x6 BLACK (1) HDMI cable fixing plate (1) Safety regulation (1) Download site information (1) Warranty (1)

Notes

*1

Available after an upgrade via a 4K optional license

*2

The values for dimensions and mass are approximate

Related products



RM-IP500

PTZ Camera Remote Controller



RM-IP10

IP remote control panel for BRC cameras



REA-C1000

Edge Analytics Appliance

Edge Analytics Appliance



MCX-500

Multi-Camera Live Producer



SRG-XP1

Compact 4K60P IP POV Remote Camera with a 101° wide viewing angle lens



SRG-XB25

Compact 4K60P IP BOX-style Remote Camera with 25x optical zoom



SRGL-4K

4K license for SRG-X400/SRG-X120



NUCLEUS

The smart digital imaging platform for medical environments

Gallery

