

HP Fortis 14 inch G11 Chromebook (9R377UT)



Work worry-free with a ruggedized Chromebook

The HP Fortis 14 inch G11 Chromebook provides performance in a rugged design. It features a large, 14-inch screen, an Intel® quad-core processor[7], plenty of memory, and long battery life for productivity throughout the day. Work collaboratively and confidently with the reinforced 180-degree lay-flat hinge and HP Privacy Camera.



Engineered for durability

Rugged, fan-less, durable design undergoes MIL-STD 810[3] and drop testing[4], and resists keycap picking.

Productivity empowered

Quickly stream and access online content, thanks to an Intel® quad-core processor[7] and plenty of memory.

Immersive interaction

Confidently engage others with a lay-flat hinge and an HDMI port to connect displays and projectors.[10]

Featuring

Universal connectivity and charging with USB-C™

Use the USB-C™ port to access and charge your USB-C™ accessories from your Chromebook™ or charge your Chromebook™ from any USB-C™ adapter.

Apps and content for expanded learning

Take learning in new directions with access to the Google Play™ Store and Android™ apps, which include thousands of instantly shareable and easily manageable innovative education apps. [1]

Simple PC management

Spend less time and get right to the updates you need with HP Support Assistant. [2]

Specifications

| | |
|--|---|
| Operating system | ChromeOS |
| Product color | Flint gray |
| Processor family | Intel® Core™ N-series processor |
| Processor | Intel® Processor N100 (up to 3.4 GHz with Intel® Turbo Boost Technology, 6 MB L3 cache, 4 cores, 4 threads) ^[6,7] |
| Memory | 4 GB LPDDR5-6400 MHz RAM (onboard) |
| Internal Storage | 32 GB eMMC |
| Graphics | Integrated |
| Graphics (integrated) | Intel® UHD Graphics |
| Display | 35.6 cm (14") diagonal, HD (1366 x 768), anti-glare, 250 nits, 45% NTSC |
| Display | 14" diagonal, HD (1366 x 768), anti-glare, 250 nits, 45% NTSC ^[10,11,12,13] |
| Display size (diagonal) | 35.6 cm (14") |
| Display size (diagonal) | 14" |
| Audio | Waves MaxxAudio®, dual speakers, dual array microphones |
| Minimum dimensions (W x D x H) | 33 x 23 x 2.2 cm |
| Minimum dimensions (W x D x H) | 12.9 x 9 x 0.86 in |
| Weight | Starting at 1.63 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i> |
| Weight | Starting at 3.59 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i> |
| Keyboard | Full-size, backlit, textured, flint silver keyboard |
| Camera | HP camera |
| Ports | 2 USB Type-C® 5Gbps signaling rate (USB Power Delivery, video and data support); 2 USB Type-A 5Gbps signaling rate; 1 HDMI 1.4; 1 stereo headphone/microphone combo jack <i>(HDMI cable sold separately.)</i> |
| Package dimensions (W x D x H) | 6.7 x 43.5 x 26 cm |
| Wireless | Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card |
| Power | 45 W USB Type-C™ adapter |
| Battery type | HP Long Life 2-cell, 47 Wh Li-ion polymer |
| Battery weight | 0.42 lb |
| Battery weight | 190 g |
| Sustainable impact specifications | Low halogen; Bulk packaging available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; Ocean-bound plastic in speaker enclosure(s) |
| UPC number | (ABA) 197961955378; (ABL) 197961955385 |
| Manufacturer Warranty | HP Services offers 1-year limited warranties and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty except for Long Life batteries which will have same 1-year or 3-year limited warranty as the platform. Refer to http://www.hp.com/support/batterywarranty/ for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc . |

Top Recommended Displays, Accessories and Services

P-Series

| | |
|------------------------|---------|
| HP P27h G5 FHD Monitor | 64W41AA |
| HP P24h G5 FHD Monitor | 64W34AA |

Speakerphones

| | |
|---------------------------------------|---------|
| Poly Sync 20+ USB-C Speakerphone | 772D0AA |
| Poly Sync 20 USB-C Speakerphone | 7F0J7AA |
| Poly Sync 10 USB-A USB-C Speakerphone | 772C3AA |

Wireless Headset

| | |
|---|---------|
| Poly Voyager 4320 USB-C Headset +BT700 dongle +Charging Stand | 77Z31AA |
|---|---------|

Wired Headset

| | |
|---|---------|
| Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter | 8X231AA |
| Poly Blackwire 3320 Stereo USB-C Headset +USB-C/A Adapter | 8X219AA |

Topload Bags

| | |
|---------------------------------|---------|
| HP Prelude 15.6-inch Laptop Bag | 2Z8P4AA |
|---------------------------------|---------|

Backpacks

| | |
|---|---------|
| HP Campus Green Backpack | 7K0E4AA |
| HP Travel 18 Liter 15.6 Iron Grey Laptop Backpack | 6H2D9AA |

Wireless Keyboards

| | |
|--|---------|
| HP 355 Compact Multi-Device Bluetooth Keyboard | 692S9AA |
| HP 475 Dual-Mode Wireless Keyboard | 7N7B9AA |

Wired Keyboards

| | |
|--|---------|
| HP 405 Multi-Device Backlit Wired Keyboard | 7N7C1AA |
|--|---------|

Wired Mice

| | |
|-----------------------------|---------|
| HP Wired Desktop 320M Mouse | 9VA80AA |
|-----------------------------|---------|

Wireless Mice

| | |
|------------------------------------|---------|
| HP 245 Bluetooth Mouse | 81S67AA |
| HP 435 Multi-Device Wireless Mouse | 3B4Q5AA |

Messaging Footnotes

[1] Internet access required and sold separately. Some apps may require purchase.

[2] Internet access required.

[3] MIL-STD testing is not intended to demonstrate fitness for U.S. Department of Defense contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.

[4] 122cm test on plywood and 76cm test on concrete. Drop test is not a guarantee of future performance under these test conditions. Any accidental damage requires an optional HP Accidental Damage Protection Care Pack.

[7] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[10] HDMI cables sold separately and not included.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[10] FHD/HD content required to view FHD/HD images.

[11] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[12] Actual brightness will be lower with touchscreen.

[13] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. © 2023 Google LLC All rights reserved. Google and the Google Logo are registered trademarks of Google LLC.

