


Lenovo 100e Chromebook Gen 4 (Intel)

Elevate your workflow and stay ahead of the curve with this cutting-edge Chromebook tailored to meet your professional needs. Featuring a sleek 11.6" HD screen with optional multi-touch functionality, this compact powerhouse ensures an immersive and interactive computing experience. The Intel N-Series processor and Intel UHD graphics, delivers seamless multitasking, enabling you to effortlessly tackle demanding workloads, creative projects, and everything in between. With a feather-light weight of 1.23kgs and an impressive battery life of up to 12 hours, it ensures that your office is wherever you are.



Built for business with cutting-edge technology

Purpose-built for modern education. Robust, secure, and easy to manage, our laptops offer versatile performance and collaboration tools to support teachers and students in the classroom or at home.

The Intel Wi-Fi 6E and USB-C 3.2 Gen 1 ports guarantee lightning-fast data transfer and a seamless online experience whereas the HD audio chip, dual 2W stereo speakers and HD 720p camera ensures that your virtual meetings, presentations, and multimedia experiences are crisp and clear.

Security features such as Google Security H1 chip, Kensington Nano security slot and camera privacy shutter protects the device and data from potential cyberattacks. Plus, the ENERGY STAR 8.0 and EPEAT Gold certifications ensure optimum power consumption and reduced environmental impact.

The 11.6" HD screen with an anti-glare surface, maintains visibility even in challenging lighting conditions. The 16:9 aspect ratio enhances your viewing experience, making it perfect for both work and entertainment.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo 100 USB-A Wireless Combo Keyboard and Mouse



- Sleek combo with a streamlined design
- Keyboard with spill-resistant island keys
- A mouse that tracks and scrolls accurately

PN: GX31K80998

Lenovo 500 USB-C Universal Dock



- 9 powerful expansion ports to maximize productivity.
- Next-gen plug-and-play simplicity and dynamic power delivery.
- Constructed using 40% recycled plastic materials.

PN: G0AA0135xx2

Lenovo 100e Chromebook Gen 4 (Intel)

Performance

Processor

Intel N Series

Operating System*

ChromeOS

Graphics

Intel UHD Graphics (integrated)

Chipset

Intel SoC (System on Chip) platform

Memory

4GB LPDDR5-4800, soldered
8GB LPDDR5-4800, soldered

Storage

32GB eMMC 5.1 on systemboard
64GB eMMC 5.1 on systemboard

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Waves MaxxAudio
Single microphone

Camera*

HD 720p

Battery¹

47Wh battery (up to 12 hr), Rapid Charge

¹Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0

Design

Display²

11.6" HD (1366x768) TN Anti-glare 16:9
- 250nits, 45% NTSC

11.6" HD (1366x768) IPS Glossy 16:9
- 250nits, 50% NTSC, touch

²IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS

Keyboard

Top-load keyboard, 6-row, spill-resistant,
Anti-pick proof keycaps with full skirt design

Touchpad

Mylar surface touchpad
60.5 x 104 mm (2.38 x 4.09 inches)

Dimensions³

287 x 204.6 x 18.6 mm (11.3 x 8.1 x 0.73 inches)

³The system dimensions may vary depending on configurations.

Weight⁴

Around 1.23 kg (2.71 lbs)

⁴The system weight is approximate and may vary depending on configurations

Color

Graphite grey

Case material

PC-ABS (top)
PC-ABS (bottom)

Connectivity

WLAN + Bluetooth*

Intel Wi-Fi 6 AX203, Bluetooth 5.1
Up to Intel Wi-Fi 6E AX211, Bluetooth 5.1

Ports

2x USB-A (USB 5Gbps)
1x USB-C (USB 10Gbps), with PD & DP
1x HDMI 1.4
1x Headphone / microphone combo jack (3.5mm)

Security & Privacy

Security

Google Security Chip H1
Camera privacy shutter
Kensington Nano Security Slot

Certifications

Green Certifications⁵

ENERGY STAR 8.0
ErP Lot 6/26
EPEAT Gold Registered
TCO Certified 9.0
RoHS compliant

⁵The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

ASTM F963