

HPE ProLiant DL360 Gen11 4514Y 2.0GHz 16-core 1P 32GB-R MR408i-o NC 8SFF 1000W PS Server (P70542-421)



What's new

- Powered by 5th Gen Intel® Xeon® Scalable processors that supports up to 64 cores & 385W, and 16 DIMMs for up to 8 TB of high bandwidth DDR5 memory up to 5600 MHz.
- 16 DIMMs per processor for up to 8 TB total DDR5 memory per server with increased performance, High Bandwidth Memory (HBM) support, and lower power requirements.
- Advanced data transfer rates and higher network speeds from the PCIe Gen5 serial expansion bus, with up to 2 x16 PCIe Gen5 and 2 OCP slots.
- Includes the new HPE Integrated Lights-Out 6 (iLO 6) server management software that enables you to securely configure, monitor, and update your HPE ProLiant Gen11 servers seamlessly, from anywhere.
- Supports up to 3 single wide (SW) GPUs[1] to accelerate graphic intense workloads.
- Supports Liquid Cooling Modules for

Overview

Are you looking for a scalable, compute-dense solution for hybrid cloud or other data workloads in a virtualized and containerized environment?

The HPE ProLiant DL360 Gen11 server is a rack-optimized, 1U 2P solution that delivers exceptional compute performance, upgraded high-speed data transfer rate, and memory depth at 2P compute capability.

Powered by 4th and 5th Gen Intel® Xeon® Scalable Processors with up to 64 cores, 8 TB of memory, and 20 EDSFF drives as well as increased memory bandwidth and high-speed PCIe Gen5 I/O, the HPE ProLiant DL360 Gen11 server is a perfect solution for Electronic Design Automation (EDA), CAD, and VDI.

The HPE ProLiant 360 Gen11 server is engineered to optimize IT with a cloud operating experience, built-in security, and optimized performance for workloads to drive your business forward.

highest thermal design points (TDPs).

Features

Intuitive Cloud Operating Experience: Simple, Self-service, and Automated

HPE ProLiant DL360 Gen11 servers are engineered for your hybrid world. ProLiant DL360 Gen11 servers are powered by 4th and 5th Gen Intel® Xeon® processors and simplify the way you control your business's compute—from edge to cloud—with a cloud operating experience.

Transform business operations and pivot your team from reactive to proactive with global visibility and insight through a self-service console.

Automate tasks for efficiency in deployment, instant scalability, and seamless, simplified support and lifecycle management to reduce and shorten maintenance windows.

Self-service automated experiences are engineered and built into all HPE ProLiant Gen11 servers, whether purchased as physical servers or consumed as a-service using HPE GreenLake as your compute and storage demands grow.

Simplify and secure server management from edge to cloud with HPE GreenLake for Compute Ops Management. HPE GreenLake for Compute Ops Management is an as-a-service compute management experience that delivers greater simplicity, agility, and speed across your entire compute landscape, globally.

Trusted Security by Design: Uncompromising, Fundamental, and Protected

The HPE ProLiant DL360 Gen11 server utilizes the HPE Silicon Root of Trust, HPE's fundamental approach to security that provides zero-trust architecture at the silicon level and ensures all server essential firmware is free from malware or compromised code.

Powered by 4th and 5th Gen Intel® Xeon® Scalable Processors, adds hardware- and software-assisted security features, including Intel® Software Guard Extensions and Intel® Boot Guard, which help secure the server hardware foundation on which critical apps run and better protect data in memory.

HPE ProLiant Gen11 servers continuously protect healthy servers by a) providing rapid detection of security-compromised servers, even to the point of not allowing them to boot if it identifies malicious code, and b) securing servers at the edge with IDevID certificates installed by default.

HPE ProLiant Gen11 servers provide automated recovery from a security event, including restoration of validated firmware, and facilitating recovery of the operating system, application, and data connections, providing a fast path to bring a server back online and into normal operations.

Embedded in Hewlett Packard Enterprise servers, HPE Integrated Lights-Out 6 (iLO 6) is an exclusive core intelligence that monitors server status, providing the means for reporting, ongoing management, service alerting, and local or remote management to quickly identify and resolve issues.

Optimized Performance for your Workloads: Accelerated, Open, and Efficient

The HPE ProLiant DL360 Gen11 server is an excellent choice for EDA, CAD, CDN, general-purpose virtualization workloads (including large-scale VDI), Intelligent Video Analytics, and Platforms (VCF & Containers) that require increased compute density with built-in security and flexibility.

Harness major computer performance. The HPE ProLiant DL360 Gen11 server is powered by the 4th and 5th Gen Intel® Xeon® Scalable Processors with next-generation technology that supports up to 64 cores, 385W, and up to 8 TB of memory.

The HPE ProLiant DL360 Gen11 server provides advanced data transfer rates and higher network speeds from the PCIe Gen5 serial expansion bus, with up to 3 x16 PCIe Gen5 and 2 OCP slots to improve I/O throughput and reduce latency.

The server provides 16 DIMMs per processor for up to 8 TB total DDR5 memory with increased memory bandwidth and performance, and lower power

requirements.

The HPE ProLiant DL360 Gen11 server provides real-time operational feedback on server performance plus recommendations for fine-tuning BIOS settings to customize for changing business needs.

Technical specifications

HPE ProLiant DL360 Gen11 4514Y 2.0GHz 16-core 1P 32GB-R MR408i-o NC 8SFF 1000W PS Server

Product Number	P70542-421
Processor name	Intel® Xeon® Silver 4514Y (16 core, 2.00 GHz, 30 MB L3, 150W)
Processor number	1 processor included
Processor core available	16 core
Processor cache	30 MB L3
Processor speed	2.00 GHz
Power supply type	1x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
Expansion slots	2-slots (x16 FH, x16 HH) as standard. Upgradeable to 3rd slot in HH (or remove Slot 2 bracket to be FH at Slot 3) in a 2nd processor configuration. And maximum 2 OCP 3.0 PCIe5 slots.
Memory type	HPE DDR5 Smart Memory
Included hard drives	None ship standard, 8 SFF supported
Optical drive type	Optional - HPE 9.5mm SATA DVD-RW Optical Drive, HPE Mobile USB DVD-RW Drive.
System fan features	5x Standard Fans
Network controller	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T Adapter for HPE
Storage controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller
Product dimensions	24,1 x 60 x 99 cm
Weight	32.33 kg
Infrastructure management	Included - HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download).
Warranty	3/3/3: Server Warranty includes three years of parts, three years of labor, and three years of onsite support coverage. Additional information regarding worldwide limited warranty and technical support is available at: https://h20564.www2.hpe.com/hpsc/wc/public/home . Additional HPE support and service coverage, to supplement the product warranty, is available. For more information, visit https://www.hpe.com/support

Hardware RAID controller support in EDSFF storages available Q2 2024



[For additional technical information, available models and options, please reference the QuickSpecs](#)

HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

Consulting services

Experts can help you map out your path to hybrid cloud and optimize your operations.

Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

Operational services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- HPE Complete Care Service: a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- HPE Tech Care Service: the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.

Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options.

[The Defective Media Retention \(DMR\)](#) service feature option applies only to Disk or eligible SSD/Flash Drives replaced by Hewlett Packard Enterprise due to malfunction. [Comprehensive Defective Material Retention \(CDMR\)](#) allows you to keep all data retentive components.


HPE GreenLake

[HPE GreenLake edge-to-cloud platform](#) is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please explore them [here](#).

**Make the right purchase decision.
Contact our presales specialists.**

[Find a partner](#)



Explore **HPE GreenLake**



**Hewlett Packard
Enterprise**

© Copyright 2024 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Intel, Intel Xeon, and Intel Optane are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries. All third-party marks are property of their respective owners.

Image may differ from the actual product
[PSN1014824446WWEN](#), April, 2024.