



## Business-class computing starts here.

Thinner and lighter than the previous generation and backed by enterprise-class support, the Latitude 14 3000 Series offers the essential features of a business-class laptop, providing the right balance of mobility, productivity, and affordability.

End users will stay productive with all-day battery life, spill resistant keyboard with optional backlit, up to 1TB of storage and option for Full HD or touch display. And IT will value the security, manageability, and outstanding reliability of Latitude, including 24/7 access to support with optional Dell ProSupport<sup>™</sup>.

It's also well-equipped with a portfolio of accessories for on-the-go or at-the-desk productivity when essential.

Feature	Technical Specification (4th Generation Intel® Sept 2014 - April 2015)	Technical Specification (5th Generation Intel® January 2015 - April 2016)
Series/Model Number	Latitude 14 3000 Series (3450)	Latitude 14 3000 Series (3450)
Processor Options	4th Generation Intel® Core i3/i5 Processors	5th Generation Intel <sup>®</sup> Celeron, Core™ up to i7 processors
Operating System	Microsoft <sup>®</sup> Windows <sup>®</sup> 7 Professional 32/64 bit Microsoft <sup>®</sup> Windows <sup>®</sup> 7 Professional 32/64- bit (available through downgrade rights from Windows <sup>®</sup> 8.1 Pro 64-bit) Microsoft <sup>®</sup> Windows <sup>®</sup> 8.1 64-bit Microsoft <sup>®</sup> Windows <sup>®</sup> 8.1 Pro 64-bit Microsoft <sup>®</sup> Windows <sup>®</sup> 8.1 Single Language 64-bit UBUNTU Linux 14.04 LTS (64-bit)	Microsoft <sup>®</sup> Windows <sup>®</sup> 7 rofessional 32/64 bit Microsoft <sup>®</sup> Windows <sup>®</sup> 7 Professional 32/64- bit (available through downgrade rights from Windows <sup>®</sup> 8.1 Pro 64-bit) Microsoft <sup>®</sup> Windows <sup>®</sup> 8.1 64-bit Microsoft <sup>®</sup> Windows <sup>®</sup> 8.1 Pro 64-bit Microsoft <sup>®</sup> Windows <sup>®</sup> 8.1 Single Language 64-bit UBUNTU Linux 14.04 LTS (64-bit)
Memory <sup>2,4</sup> Options	DDR3L SDRAM 1600MHz; 2 slots supporting up to $4GB^1$	DDR3L SDRAM 1600MHz; 2 slots supporting up to 16GB <sup>1</sup> remote
Chipset	Integrated with the Processor	Integrated with the processor
Graphics	Intel <sup>®</sup> Integrated HD Graphics 4400 (Core x - 4th Gen) Nvidia <sup>®</sup> GeForce <sup>®</sup> 830M	Intel® Integrated HD Graphics (Celeron) Intel® Integrated HD Graphics 5500 (Core x - 5th Gen)(Early 2015) Nvidia® GeForce® 830M
Display	14.0" HD (1366 x 768) Anti Glare (16:9) WLED	14.0" HD (1366 x 768) Anti Glare (16:9) WLED 14.0" FHD (1920 x 1080) Anti Glare (16:9) WLED 14.0" HD Touch with Corning® Gorilla® Glass NBT (1366 x 768) (16:9) WLED
Storage⁴ Options	500GB 7200RPM Hard Disk Drive 500GB 5400 RPM Hybrid Drive (8GB Cache)	500GB 7200RPM Hard Disk Drive 500GB 5400 RPM Hybrid Drive (8GB Cache) 1TB 5400RPM Hard Disk Drive 1TB 5400RPM Hybrid Drive (8GB Cache)
Security <sup>1</sup>	DDP Security Tools DDP Protected Workspace (1 year) Optional DDP E Encryption Software	DDP Security Tools DDP Protected Workspace (1 year) Optional DDP E Encryption Software
Docking Options	USB Docking Only	USB Docking Only
Optical Drive Options	External Options Only	External Options Only
Multimedia	High Quality Speakers Universal Headphone Jack Integrated digital array microphone Integrated 1.0mp HD video webcam	High Quality Speakers Universal Headphone Jack Integrated digital array microphone Integrated 1.0mp HD video webcam
Battery Options	4 cell 58 Whr Li-Ion (Prismatic cell) with ExpressCharge™	3 cell 43 Whr Li-Ion (Prismatic cell) with ExpressCharge™ 4 cell 58 Whr Li-Ion (Prismatic cell) with ExpressCharge™
Power Options	65 Watt or 90 Watt E4 AC Adapter	65 Watt or 90 Watt E4 AC Adapter
Connectivity options	10/100/1000 Gigabit Ethernet <b>Wireless LAN Options:</b> Intel 7265 2x2 dual band 802.11 AGN with BT Combo Card No Mobile Broadband Options	10/100/1000 Gigabit Ethernet <b>Wireless LAN Options:</b> Intel 7265 2x2 dual band 802.11 AGN with BT Combo Card Dell Wireless 1707 1x1 single band 802.11n + BT 4.0 (Early 2015) No Mobile Broadband Options
Ports, Slots & Chassis	Memory card reader 2 USB 3.0, 1 USB 2.0, HDMI, VGA Network connector (RJ-45) Optional Fingerprint Reader Lock slot	Memory card reader 2 USB 3.0, 1 USB 2.0, HDMI, VGA Network connector (RJ-45) Optional Fingerprint Reader Lock slot
Dimensions & Weight <sup>7</sup>	Width: 13.46" / 342.0mm Height: .87" / 22.2mm (non-Touch); .9" / 23.0mm (Touch) Depth: 9.68" / 245.9mm (non-Touch); 9.69" / 246.1mm (Touch) Starting weight: 4.2lbs / 1.9kg (with 3-cell battery)	Width: 13.46" / 342.0mm Height: .87" / 22.2mm (non-Touch); .9" / 23.0mm (Touch) Depth: 9.68" / 245.9mm (non-Touch); 9.69" / 246.1mm (Touch) Starting weight: 4.2lbs / 1.9kg (with 3-cell battery)
Regulatory and Environmental Compliance	Regulatory Model: P51G Regulatory Type: P51G001 ENERGY STAR 6.0 (Windows OS) EPEAT Registered. For specific country participation and rating, please visit www.epeat.net	Regulatory Model: P51G Regulatory Type: P51G001 ENERGY STAR 6.0 (Windows OS) EPEAT Registered. For specific country participation and rating, please visit www.epeat.net

Input	Single Pointing non-backlit keyboard Optional Single Pointing backlit keyboard Clickpad Touchpad	Single Pointing non-backlit keyboard Optional Single Pointing backlit keyboard Clickpad Touchpad
Peripheral Ecosystem <sup>1</sup>	Dell Monitor Stand with Port Replicator, Dell 22" or 24" Monitor, Dell Wireless Keyboard & Mouse, Dell Professional Topload Carrying Case	Dell Monitor Stand with Port Replicator, Dell 22" or 24" Monitor, Dell Wireless Keyboard & Mouse, Dell Professional Topload Carrying Case
Warranty and Service	Limited Hardware Warranty <sup>3</sup> ; Standard 1-year On Site Service after Remote Diagnosis <sup>5</sup> (3-3-3); Optional 3-year Dell ProSupport™ for IT <sup>6</sup> ; 4 year and 5 year service and support options <sup>6</sup>	Limited Hardware Warranty <sup>3</sup> ; Standard 1-year On Site Service after Remote Diagnosis <sup>5</sup> (3-3-3); Optional 3-year Dell ProSupport™ for IT <sup>6</sup> ; 4 year and 5 year service and support options <sup>6</sup>

<sup>1</sup>Offering may vary by country and by configuration

<sup>2</sup> A 64-bit operating system is required to support 4GB or more of system memory

<sup>3</sup> Limited Hardware Warranty: For copy of Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see www.dell.com/warranty

<sup>4</sup> GB means 1 billion bytes and TB equals 1 trillion bytes; actual capacity varies with preloaded material and operating environment and will be less.

<sup>5</sup>Onsite Service after Remote Diagnosis: Remote Diagnosis is determination by online/phone technician of cause of issue; may involve customer access to inside of system and multiple or extended sessions. If issue is covered by Limited Hardware Warranty (www.dell.com/warranty) and not resolved remotely, technician and/or part will be dispatched, usually within 1 business day following completion of Remote Diagnosis. Availability varies. Other conditions apply. <sup>6</sup> Dell Services: Availability and terms of Dell Services vary by region. For more information, visit www.dell.com/servicedescriptions.

<sup>7</sup> Weights vary depending on configuration and manufacturing variability.