

### PERFORMANCE

#### Processor

MediaTek Helio G88 (8C, 2x A75 @2.0GHz + 6x A55 @1.8GHz)

#### Graphics

Integrated ARM Mali-G52 MC2 GPU

#### Chipset

MediaTek SoC Platform

#### Memory

4GB Soldered LPDDR4x

#### Storage

128GB eMMC 5.1

#### Card Reader

microSD Card Slot

#### Storage Support

- 128GB eMMC 5.1 on systemboard
- microSD card, supports up to 1TB (exFAT)

#### Speakers

4 speakers, 1W x4, optimized with Dolby Atmos®

#### Microphone

Mono

#### Camera

Front 8.0MP / Rear 8.0MP

#### VoiceCall

No

#### Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- Hall sensor

#### Vibration Motor

No support

#### Battery

Integrated 7040mAh (Typ.)

#### Power Adapter

5V / 2A

### DESIGN

#### Display<sup>[1][2]</sup>

11" WUXGA (1920x1200) IPS 400nits Anti-fingerprint, 72% NTSC, 90Hz, Touch

#### Touchscreen

In-cell, 10-point Multi-touch

#### Case Material

Metal

#### Keyboard

None

#### Pen<sup>[3]</sup>

Pen Upgradable (Purchase Separately)

#### Dust and Water Resistant

IP52

#### Dimensions (WxDxH)<sup>[4]</sup>

255.26 x 166.31 x 7.15 mm (10.05 x 6.55 x 0.28 inches)

#### Weight<sup>[5]</sup>

Around 465 g (1.03 lbs)

#### Case Color

Luna Grey

### SOFTWARE

#### Operating System<sup>[6]</sup>

Android™ 13 or Later

### CONNECTIVITY

#### WLAN + Bluetooth®

11ac 1x1 + BT5.1

#### WWAN

None

#### Location Services

GPS + GLONASS + Galileo

#### Standard Ports

- 1x USB-C® 2.0 (support data transfer and charging)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

### SERVICE

#### Base Warranty<sup>[7]</sup>

1-year, Mail-in

### ACCESSORIES

#### Bundled Accessories<sup>[8]</sup>

None

### CERTIFICATIONS

#### Green Certifications

- ENERGY STAR® 8.0 (only available for TB330FU)
- ErP Lot 6
- ErP Lot 26
- RoHS compliant

#### Other Certifications

TÜV Rheinland® Low Blue Light (Hardware Solution)

### MODEL

**Product** : TB330FU

**TopSeller** : No

**Announce Date** : 2023-10-31

**EAN / UPC / JAN** : 197532686519



Product image is a sample, it may not match the real color of this model

#### Note:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[2] Measured diagonally, Lenovo Tab M11's screen size is 11" in the full rectangle without accounting for the rounded corners. Actual viewable area is less due to the rounded corners.

[3] For more details, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

[4] The system dimensions may vary depending on configurations.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] Expect OS upgrades until Android 15 and security patches until January 2028. For latest software upgrade plan, please visit <https://support.lenovo.com/solutions/ht501098>.

[7] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

[8] For more compatible accessories, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to <https://psref.lenovo.com/Detail/2375?M=ZADA0117US>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

## Base Warranty - Included with the system you purchase with default 1-year coverage window.

## Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service\*

\*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories

### Lenovo Tab Pen Plus

ZG38C05194

With 4,096 levels of pressure and tilt detection, sketch, draw or just take notes with the highest degree of precision, responsiveness and control yet with the new Lenovo Tab Pen Plus, featuring ultra-low-latency, hig...

### Lenovo Replaceable Pen Tips

ZG38C05644

To provide the best pen-writing experience with replaceable pen tip

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

Lenovo

PSREF  
Product Specifications  
Reference