




* All images in this datasheet are for illustrative purposes only.



Indoor DVLED

LSBE Fine Pitch Value Series



Easy Installation and Maintenance



Durable Frame Design



Value Brightness



Compatibility with LG Software Solutions


LSBE Value Series

Pixel Pitch	1.56 / 1.88 / 2.50 mm
Brightness	600 nits (Max)
Weight per Cabinet (lbs. / kg)	14.3 / 6.5
Service Access	Front
IP Rating Front / Rear	IP50 / IP50



Improved Flatness and Easy Maintenance

LSBE series utilizes two modules to form a single cabinet, which helps minimize the gaps between the modules resulting in a smoother screen. In addition, the structural advantage allows for easy maintenance.



Durable Frame Design

LSBE incorporates an aluminum cabinet that enhances durability, and its high-strength frame, surpassing that of plastic, allowing for stable operation.



Brightness

With a brightness of 600 nits, the LSBE Series clearly delivers content and attracts public attention, making it ideal for achieving bright indoor visibility.



Compatibility with LG Software Solutions

Powered by LG's high performance system controller, the LAED series is compatible with LG software solutions including SuperSign CMS, LED Assistant, and ConnectedCare, which help customers have even more control over their systems.*

*LG ConnectedCare and LG SuperSign CMS are each sold separately. Actual user interface may vary in different webOS versions.

SPECIFICATIONS

		LSBE015-GD	LSBE018-GD	LSBE025-GD
Pitch Name		P1.5	P1.8	P2.5
Physical Parameters	Pixel Configuration	Single SMD	Single SMD	Single SMD
	Pixel Pitch (mm)	1.56	1.88	2.50
	Module Resolution (W x H)	192 x 216	160 x 180	120 x 135
	Module Dimensions (W x H, in. / mm)	11.8 x 13.3 x .5 / 300 x 337.5 x 13	11.8 x 13.3 x .5 / 300 x 337.5 x 13	11.8 x 13.3 x .5 / 300 x 337.5 x 13
	Weight per Module (lbs. / kg)	2.1 / 0.95	2.1 / 0.95	2.1 / 0.95
	No. of Modules per Cabinet (W x H)	2 x 1	2 x 1	2 x 1
	Cabinet Resolution (W x H)	384 x 216	320 x 180	240 x 135
	Cabinet Dimensions (W x H x D, in. / mm)	23.6 x 13.3 x 2.8 / 600 x 337.5 x 72	23.6 x 13.3 x 2.8 / 600 x 337.5 x 72	23.6 x 13.3 x 2.8 / 600 x 337.5 x 72
	Cabinet Surface Area (ft ² / m ²)	14.3 / 6.5	14.3 / 6.5	14.3 / 6.5
	Weight per Cabinet (lbs. / kg)	6.5	6.5	6.5
	Weight per Unit Area (lbs./ft ² / kg/m ²)	6.6 / 32.0	6.6 / 32.0	6.6 / 32.0
	Physical Pixel Density (pixels/m ²)	409,600	248,089	160,000
	Flatness of Cabinet (mm)	±0.3	±0.3	±0.3
	Cabinet Material	Die-cast Aluminum	Die-cast Aluminum	Die-cast Aluminum
Service Access	Front	Front	Front	
Optical Specifications	Max. Brightness (After Calibration, nits)	600	600	600
	Color Temperature (K)	3,200-9,300	3,200-9,300	3,200-9,300
	Visual Viewing Angle (H x V)	160° x 150°	160° x 150°	160° x 150°
	Brightness Uniformity	97%	97%	97%
	Color Uniformity	±0.003 Cx, Cy	±0.003 Cx, Cy	±0.003 Cx, Cy
	Contrast Ratio	5,000:1	5,000:1	5,000:1
	Processing Depth (bit)	14	14	14
Electrical Specifications	Power Consumption (W/Cabinet, Max.)	107	103	93
	Power Consumption (W/Cabinet, Avg.)	45	41	36
	Power Consumption (W/m ² , Max.)	530	510	460
	Heat Dissipation (BTU/h/Cabinet, Max.)	365	351	317
	Heat Dissipation (BTU/h/Cabinet, Avg.)	153	140	122
	Heat Dissipation (BTU/h/m ² , Max.)	1,808	1,740	1,570
	Power Supply (Vac)	100 to 240	100 to 240	100 to 240
	Frame Rate (Hz)	50 / 60	50 / 60	50 / 60
Refresh Rate (Hz)	3,840	3,840	3,840	
Operation Specifications	LED Lifetime (Half Brightness)	Up to 100,000 hours	Up to 100,000 hours	Up to 100,000 hours
	Operating Temperature (°F / °C)	-4 to +104 / -20 to +40	-4 to +104 / -20 to +40	-4 to +104 / -20 to +40
	Operating Humidity	10-80% RH	10-80% RH	10-80% RH
	IP Rating Front / Rear	IP50 / IP50	IP50 / IP50	IP50 / IP50
Standard	Certification	CE, FCC, cTUVus, CB, KC, CCC	CE, FCC, cTUVus, CB, KC, CCC	CE, FCC, cTUVus, CB, KC, CCC
	Warranty	3 Year Limited	3 Year Limited	3 Year Limited
Environment		RoHS, REACH	RoHS, REACH	RoHS, REACH
Controller		CVBA	CVBA	CVBA
90 Degree Corner Cut		Yes	Yes	Yes

CVBA (Controller)

Cabinet		LSBE015-GD, LSBE018-GD, LSBE025-GD
Max Output Range	Loading Capacity	3,840 x 2,160 @ 60 Hz
	Output Resolution	8.2944 Million Pixels
Input	HDMI 2.0, HDCP 2.2, DP 1.2 / HDCP 1.3, OPS	
Output	Ethernet (To LED Screen) (16-channel)	
Control	LAN	Yes
	RS-232C	Yes (LOOP)
Sensor	Temperature	Yes
Video Processing	Brightness Adjustment, Chroma Adjustment, Improved Grayscale at Low Brightness, Scaling, HDR10 Pro	
Application	SuperSign CMS, webOS API, LG ConnectedCare ¹⁾ , Configuration SW (LED Assistant)	
Mechanical	Size (W x H x D, in. / mm)	17.4 x 2.5 x 12.1 / 443 x 63 x 307.5
	Weight (lbs. / kg)	10.8 / 4.9

¹⁾ The availability can differ by region.

* Specifications are subject to change without notice. Please make sure to check the product manual for details about product usage.