

## PERFORMANCE

### Processor

AMD Ryzen™ 5 7535U (6C / 12T, 2.9 / 4.55GHz, 3MB L2 / 16MB L3)

### Graphics

Integrated AMD Radeon™ 660M Graphics

### Chipset

AMD SoC Platform

### Memory

1x 16GB SO-DIMM DDR5-4800

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

### Max Memory<sup>[1]</sup>

Up to 64GB DDR5-4800

### Storage

256GB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal 2.0

### Storage Slot

Two M.2 slots

- One M.2 2242 PCIe® 4.0 x4 slot
- One M.2 2280 PCIe® 4.0 x4 slot

### Max Storage Support<sup>[2]</sup>

Up to two drives, 2x M.2 SSD

- M.2 2242 SSD up to 1TB
- M.2 2280 SSD up to 1TB

### Optical

None

### Card Reader

No card reader

### Audio Chip

High Definition (HD) Audio, Senary SN6141 codec

### Speakers

Stereo speakers, 2W x2, Dolby Atmos®, audio by HARMAN

### Microphone

2x, Array

### Camera

FHD 1080p with Privacy Shutter

### Battery

47Wh

### Power Adapter

65W USB-C® (2-pin)

## DESIGN

### Display<sup>[3]</sup>

16" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC

### Touchscreen

None

### Screen-to-Body Ratio

90.7%

### Pen

Pen Not Supported

### Keyboard

Backlit, French

### Dimensions (WxDxH)<sup>[4]</sup>

356.1 x 247.7 x 19.85 mm (14.02 x 9.75 x 0.78 inches)

### Weight<sup>[5]</sup>

Starting at 1.81 kg (3.99 lbs)

### Case Color

Black

### Case Material

Aluminium (Top), Aluminium (Bottom)

## SOFTWARE

### Operating System

Windows® 11 Pro, French

### Bundled Software

None

## CONNECTIVITY

### WLAN + Bluetooth®

Realtek® Wi-Fi® 6 RTL8852BE, 802.11ax 2x2 + BT5.3

### WWAN

Non-WWAN

### SIM Card

None

### Ethernet

100/1000M (RJ-45)

### NFC

None

### Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with USB PD 3.0 and DisplayPort™ 1.4
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 and DisplayPort™ 1.4
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)

### Docking

Various docking solutions supported via USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® E16 Gen 2 \(AMD\)](#)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0 Enabled

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Smart Card Reader

None

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Other Security

- Camera privacy shutter
- ThinkShield

## MANAGEABILITY

### System Management

Non-DASH

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications<sup>[6]</sup>

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 9.0

### Mil-Spec Test

MIL-STD-810H military test passed

### Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

## MODEL

**TopSeller** : Yes **Announce Date** : 2024-04-09

**EAN / UPC / JAN** : 197530434983 **End of Support** : 2030-11-02

### Note:

<sup>[1]</sup> The max memory is based on the technical readiness of the system, but not shipped by Lenovo.

<sup>[2]</sup> The system supports dual SSD via two M.2 slots, but Lenovo only offers one M.2 2242 SSD configuration and M.2 2280 slot for user self-extension.

<sup>[3]</sup> IPS (in-plane switching) technology may refer to IPS,.....

• Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

## Recommended Services

|        |   |
|--------|---|
| BEST   | 3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39180) |
| BETTER | 3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36151)      |
| GOOD   | 3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A23681)               |

Please click [here](#) to view the full list of accessories.



**PSREF**  
Product Specifications  
Reference