

PERFORMANCE

Display Size

24.5"

View Area

543.7x302.6 mm

Panel

In-Plane Switching

Backlight

WLED

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.2802x0.2802 mm

Dot / Pixel Per Inch

89.9 dpi

View Angle (H / V)

178° / 178°

Response Time

4ms (Extreme mode) / 6ms (Typical mode)

Color Support

16.7 Million

Refresh Rate

48Hz - 100Hz

Brightness

250 cd/m²

Contrast Ratio

1300:1

Color Gamut

99% sRGB, 99% Rec.709, 83% DCI-P3

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Camera

Modular Camera Support

Microphone

None

Speakers

Modular Speaker Support

Power Consumption (Typical / Maximum)

12.5W / 52W

Power Adapter

Integrated

Touchscreen

None

Smart System

None

DESIGN

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Case Color

Raven Black

Side Bezel Width

17.6 mm

Mounting

Supports VESA mount 100 x 100 mm

ThinkCentre® M Series Support

Tiny Support

Dimensions (WxDxH)

- Lowest Position | 557.3 x 199.7 x 356.8 mm (21.94 x 7.86 x 14.05 inches)
- Highest Position | 557.3 x 199.7 x 511.8 mm (21.94 x 7.86 x 20.15 inches)
- Head Only | 557.3 x 49 x 328.5 mm (21.94 x 1.93 x 12.93 inches)

Packaging Dimensions (WxDxH)

730 x 160 x 422 mm (28.74 x 6.30 x 16.61 inches)

Weight

- Monitor With Stand | 5.4 kg (11.9 lbs)
- Monitor Head Only | 3.4 kg (7.5 lbs)

Packaging Weight

8.4 kg (18.52 lbs)

CONNECTIVITY

USB Port

4x USB-A (USB 5Gbps, 1x BC1.2), 1x USB-B (USB 5Gbps, USB upstream)

Video Connector

1x HDMI® 2.1 TMDS, 1x DP 1.4 (HBR2), 1x DP 1.4 Out, 1x VGA

Network Connectivity

None

SERVICE

Base Warranty

3-year

CERTIFICATIONS

Environmental Certification

ENERGY STAR® Certified, TCO 9.0, TCO Edge 2.0, EPEAT™ Gold, EU Energy Efficiency Level (Level-D)

Ergonomic Certification

Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Low Blue Light, TÜV Rheinland® Flicker Free, TÜV Rheinland® Eye Comfort

Sync Technology

None

Special Features

- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support
Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).
Lenovo® Display Accessories and Display Manager is formerly Lenovo® Display Control Center.
- Natural Low Blue Light

SOFTWARE

Operating System

Support Windows® 10, Windows® 11

ACCESSORIES

Video Cables

HDMI® cable, DP cable

MODEL

Announce Date : 2024-03-19
EAN / UPC : 0195892096023 / 195892096023 / None
/ JAN



Product image is a sample, it may not match the real color of this model

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

Lenovo Adjustable Height Arm

4XFOH70603

This is the ultimate Lenovo Arm. Reduce neck and back pain by positioning the monitor to the most comfortable height and angle. Declutter your workspace by getting the monitor up off the desk. Perfect for any situatio...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference