

Product datasheet

Specifications



Easy Rack PDU, Switched Metered Outlet, 0U, 1 Phase, 7.4kW, 230V, 32A, (20) C13 and (4) C19 outlets, IEC60309 2P+E inlet

EPDU2132SMBO

Overview

Lead Time Usually in Stock

Main

Colour	Black
Product Or Component Type	PDU
Pdu Type	Metered outlet
Cord Length	3 m
Number Of Cables	1
Provided Equipment	Installation guide

Complementary

Input Voltage	200 V
Height	1800 mm
Width	55 mm
Output Voltage	230 V
Depth	56 mm
Net Weight	7.42 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60309 32 A 2P + E
Mounting Mode	Not rack-mountable
Rack Units	0U
Usb Compatible	No
Mounting Position	Vertical
Communication Port Protocol	SNMP
[In] Rated Current	32 A
Permissible Voltage	200...240 V
Max Line Current	32 A
Input Current Limits	32 A
Load Capacity	7360 VA
Network Frequency	50/60 Hz

Plug Standard	IEC 60309
Total Number Of Outlets	20 IEC 60320 C13
Communication Network Type	10/100BASE-T

Environment

Product Certifications	CE
Ambient Air Temperature For Operation	-5...50 °C
Relative Humidity	5...95 %
Operating Altitude	0...3000 m
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0...15000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	203 cm
Package 1 Width	19.5 cm
Package 1 Length	13 cm
Package 1 Weight	8.59 kg

Logistical informations

Country Of Origin	CN
--------------------------	----

Contractual warranty

Warranty	2 Years repair and Replace
-----------------	----------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)



RoHS/REACH

Well-being performance

Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive [Compliant with Exemptions](#)
