



PROJECTOR PA504W

Key Features

- 1.21-1.57 throw ratio enables seamless projector upgrades
- 4,000 ANSI Lumens offering bright images in any environment
- Convenient connectivity with dual HDMI and USB-A power supply
- Comprehensive LAN control for centralized device management
- High native contrast ratio achieved through Texas Instruments' 0.65" DMD chip



Product Description

The ViewSonic PA504W is a high-brightness lamp projector tailored for both education and business settings. It features a 1.21-1.57 throw ratio, allowing seamless projector upgrades in typical installation conditions. With 4000 ANSI Lumens, it ensures bright, vivid images even in well-lit environments, guaranteeing clarity for every presentation or lesson. Its Texas Instruments' 0.65" DMD Chip elevates the viewing experience with a high native contrast ratio, unveiling fine details for exceptional sharpness on the screen. Effortlessly switch between content sources via the dual HDMI ports. Additionally, you can combine it with the ViewSonic WPD-700 Wireless Screen Casting Kit, powered by the projector's USB-A output, for expanded versatility. Comprehensive LAN control takes this convenience further, providing streamlined device management. Based on DLP technology, it maintains consistent color performance and great readability over time and features a filter-free design for minimal maintenance requirements.



1. Adjustment Foot
 2. Lens
 3. Front IR
 4. Audio In
 5. HDMI x2
 6. USB-A(5V/1.5A, Service)
 7. Computer In

8. Monitor Out
 9. Video In
 10. RJ45
 11. Audio Out
 12. AC In
 13. RS232
 14. Kensington Lock

15. Zoom/Focus Ring
 16. Keypad
 17. LED Indicator
 18. Power Button

Visit Us

www.viewsonic.com

SPECIFICATION

Native Resolution:	1280x800
Brightness:	4000 (ANSI Lumens)
Contrast Ratio with SuperEco Mode:	22000:1
Display Color:	1.07 Billion Colors
Light Source Type:	200W UHP Lamp
Light Source Life (hours) with Normal Mode:	5000
Light Source Life (hours) with SuperEco Mode:	15000
Lens:	F=2.59-2.87, f=16.88-21.88mm
Projection Offset:	120%+/-5%
Throw Ratio:	1.21-1.57
Optical Zoom:	1.3x
Digital Zoom:	0.8x-2.0x
Image Size:	30"-300"
Throw Distance:	0.78m-10.14m (100"@2.61m)
Keystone:	V:+/-40°
Audible Noise (Normal):	31dB
Audible Noise (Eco):	27dB
Input Lag:	16ms
Resolution Support:	VGA(640 x 480) to FullHD(1920 x 1080)
HDTV Compatibility:	480i, 480p, 576i, 576p, 720p, 1080i, 1080p
Video Compatibility:	NTSC, PAL, SECAM
Horizontal Frequency:	15K-102KHz
Vertical Scan Rate:	23-120Hz

INPUT

Computer in (share with component):	1
Composite:	1
HDMI:	2 (HDMI 1.4/ HDCP 1.4)
Audio-in (3.5mm):	1

OTHERS

Power Supply Voltage:	100-240V+/- 10%, 50/60Hz (AC in)
Power Consumption:	Normal: 255W Standby: <0.5W
Operating Temperature:	0~40°C
Carton:	Brown
Net Weight:	2.33kg
Gross Weight:	3.54kg
Dimensions (WxDxH) with Adjustment Foot:	294x218x110mm
Packing Dimensions:	415x168x297mm
OSD Language:	English, French, Spanish, Thai, Korean, German, Italian, Russian, Swedish, Dutch, Polish, Czech, T-Chinese, S-Chinese, Japanese, Turkish, Portuguese, Finnish, Indonesian, India, Arabic, Vietnamese, Greek, Total 23 languages
User Guide Language:	English, S-Chinese, T-Chinese, Indonesian, Finish, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Arabic, Czech, Thai, Vietnamese, Total 20 languages

STANDARD ACCESSORY

Power Cord:	1
VGA Cable:	1
Remote Control:	1
QSG:	Yes
Warranty Card:	Yes (CN only)

OPTIONAL ACCESSORY

Lamp/Light Source:	RLC-130
Wall/Ceiling Mount:	PJ-WMK-007
Carry Bag:	PJ-CASE-008

Monitor out:	1
Audio-out (3.5mm):	1
Speaker:	10W
USB Type A (Power):	1 (5V/1.5A)

CONTROL

RS232 (DB 9-pin male):	1
RJ45 (LAN control):	1
USB Type A (Services):	1 (share with USB A Output)