

PERFORMANCE

Processor

Intel® Core™ Ultra 7 165U, 12C (2P + 8E + 2LPE) / 14T, Max Turbo up to 4.9GHz, 12MB

NPU

Intel® AI Boost integrated in Intel® Core™ Ultra processor

Graphics

Integrated Intel® Graphics

Chipset

Intel® SoC Platform

Memory

1x 16GB SO-DIMM DDR5-5600

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory^[1]

Up to 64GB DDR5-5600

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Support^[2]

One drive, up to 2TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

Audio Chip

High Definition (HD) Audio, Senary SN6147 codec

Speakers

Stereo speakers, 2W x2, Dolby Audio™

Camera

5.0MP + IR Discrete with Privacy Shutter

Microphone

2x, Array

Battery

Integrated 57Wh

Power Adapter

65W USB-C® Slim (2-pin)

DESIGN

Display^[3]

14" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, DBEF5, Touch

Touchscreen

On-cell, 10-point Multi-touch

Keyboard

Backlit, English

Case Color

Black

Case Material

PC-ABS (Top), PC-ABS (Bottom)

Dimensions (WxDxH)^[4]

313.7 x 226 x 18.92 mm (12.35 x 8.90 x 0.74 inches)

Weight^[5]

Starting at 1.4 kg (3.09 lbs)

SOFTWARE

Operating System

Windows® 11 Pro, English

CONNECTIVITY

Ethernet

100/1000M (RJ-45)

WLAN + Bluetooth^[6]

Intel® Wi-Fi® 6E AX211, 11ax 2x2 + BT5.3

Standard Ports

- 1x USB-A (Hi-Speed USB / USB 2.0)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On
- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), with USB PD 3.0 and DisplayPort™ 1.4
- 1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® L14 Gen 5 \(Intel®\)](#)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security

- IR camera for Windows® Hello (facial recognition)
- Camera privacy shutter

MANAGEABILITY

System Management^[7]

Intel® vPro® Enterprise

SERVICE

Base Warranty

1-year, Courier or Carry-in

CERTIFICATIONS

Green Certifications^[8]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6
- ErP Lot 26
- RoHS compliant
- TCO Certified 9.0

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Low Blue Light (Hardware Solution)

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller : Yes **Announce Date** : 2024-04-16

EAN / UPC / JAN : 197530495144 **End of Support** : 2030-11-16



Product image is a sample, it may not match the real color of this model

Note:

^[1] The max memory is based on the test results with current Lenovo memory offerings.

^[2] The storage capacity supported is based on the test results with current Lenovo storage offerings.

^[3] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

^[4] The system dimensions may vary depending on configurations.

^[5] The system weight is approximate and based on results in.....

· Lenovo reserves the right to change specifications without notice.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to

<https://psref.lenovo.com/Detail/2473?M=21L1001WUS>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

- The ThinkPad Hybrid USB-C with USB-A dock is a productivity solution for any USB-C or USB-A laptop, including non-Lenovo laptops from Dell, HP, and Apple, providing power, display, and port expansion in any m...

Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39383)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36154)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A14086)

For a full list of accessories and services, please visit: <https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference