

## OVERVIEW

Upgradeable Switched Outlet Level Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering individual outlet level control and a comprehensive view of outlet level power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. With the Geist Upgradeable hot-swap technology, users may easily update the rPDU technology with the addition of the appropriate Interchangeable Monitoring Device (IMD) as business needs change.

### Benefits

- Remotely reboot outlets to power cycle unresponsive IT equipment or increase runtime of critical equipment upon power failure with outlet-level control.
- Reliable power distribution with local and remote outlet-level power monitoring options offer quick access to critical power usage information down to the device level to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.



## Part #: VP7N20A2

**Model Number:** MNU5MGB0-24S203-2TL21A0A10-S

**Category:** Switched

**Sub Category:** Outlet Level Monitoring

**Power Configuration:** 20A, 120/208V WYE, 5.7kW

**Physical Configuration:** 66in / 1683mm, Vertical

**Product Summary:** rPDU, Switched Outlet Level Monitoring EC, 20A, 120/208V WYE, 5.7kW, Vertical, (24) NEMA 5-20R, 10ft / 3m power cord with L21-20P, Black Powder Coat.

**Monitoring:** Input and Outlet power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.

### Plug Form:



L21-20P

### Receptacle:



NEMA 5-20R  
(Quantity: 24)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

- Daisy-chain up to 50 devices on a single IP address and reduce deployment time with self-configuration of downstream devices.

## Product Specification and Options

### System Features

<b>Monitoring</b>	Input and Outlet power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
<b>Input Monitoring</b>	Total Unit Monitoring (kWh, W, VA, PF) Phase (A, B, C) Monitoring (kWh, W, VA, PF, V, A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Circuit Monitoring</b>	Circuit / Breaker Monitoring (A)  Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
<b>Outlet Monitoring</b>	Outlet Monitoring (kWh, W, VA, PF, V, A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements.
<b>Remote Power Management</b>	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
<b>Quantity Of Inputs</b>	1
<b>Voltage</b>	100-120/200-240V WYE
<b>Current</b>	20A x 3 Phase WYE
<b>VA per Input (Load Capacity)</b>	5.7kW (120V)
<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	None
<b>Switch</b>	No
<b>LCD Touchscreen Display / Auto Oriented</b>	Yes
<b>Indicators - LED(s)</b>	24
<b>Power Cable Wire Gauge</b>	12/5
<b>Power Cable Length</b>	10ft / 3m
<b>Power Entry Location</b>	Bottom Front
<b>Plug Type</b>	NEMA L21-20P Twistlock
<b>Receptacle/Socket Type #1</b>	NEMA 5-20R
<b>- Quantity on Face</b>	24
<b>- Quantity per Phase</b>	8
<b>- Style</b>	Individual
<b>- Voltage per Receptacle/Socket</b>	120V
<b>Network Connection</b>	Dual 10/100/1000Mbps Ethernet
<b>Protocols Supported</b>	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+, Modbus TCP
<b>Data Access Formats</b>	CSV datalog, JSON API, JSON datalog
<b>USB Support</b>	Yes
<b>IP Reset Button</b>	Yes
<b>Hard Reboot Button</b>	Yes
<b>Serial Connection</b>	RS232 via RJ45
<b>Remote Sensor RJ Connection Jacks</b>	1 (Supports up to 16 Sensors)

<b>Maximum Operating Temperature</b>	60C / 140F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	Zero U
<b>7938 Vertical Mounting Bracket Kit</b>	Yes
<b>Toolless Mounting Hardware - Center to Center Spacing</b>	61.25in and 64.75in / 1556mm and 1645mm
<b>Country of Origin</b>	USA, TAA Compliant and Buy American Act COTS Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	FCC Part 15 Class A Conformance
<b>Certification/Agency Approvals</b>	UL & c-UL Listed 62368-1
<b>Chassis Dimensions (LxWxD)</b>	66.25in x 2in x 2.6in / 1683mm x 51mm x 66mm
<b>Shipped Weight</b>	18lbs (8.16kg)