



Poly Blackwire 5220 3.5mm Top (85Q68AA)

Overview

Wear it well

The Blackwire 5200 Series fits your busy workday. Ergonomically designed for long lasting comfort. And with the easy-to-use connectivity you can work on a variety of devices throughout the day.

Get great sound

Tune out the inevitable workplace distractions with a headset full of features – soft, conforming ear cushions that provide passive noise canceling and a precisely tuned microphone masks nearby conversations.

Enjoy long lasting comfort

Your ears will thank you, especially after long conference calls. This headset is built to stay comfortable. Adjust it to fit the way you work. Need to move locations? The headset folds up for easy portability in the carrying case.

Features

Connectivity options

Enhanced connectivity for your devices: USB-C cord with tethered USB-A adapter for PC and 3.5 mm for mobile or tablet connectivity.

Wearing style

Premium PC wideband audio with noise-cancelling microphone and Digital Signal Processing (DSP) for a more natural voice sound.

SoundGuard Digital technology provides advance audio protection

Premium PC wideband audio with noise-canceling microphone and Digital Signal Processing (DSP) for a more natural voice sound.

Comfort and durability

Ultra-soft leatherette ear cushion(s) wrapped around pillow-soft memory foam provide long lasting comfort. A lightweight cushioned metal headband offers durability and a comfortable custom fit.

Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management. Conveniently placed indicator lights provide helpful but unobtrusive user call, mute, and volume status.

Enhanced call quality

Dynamic EQ optimizes the quality of your voice on calls, and automatically adjusts the EQ settings when you want high-quality sound for listening to music or for multimedia playback.

Specifications

Audio	Dynamic EQ optimized; Dynamic mute alert; Digital signal processing (DSP); Noise cancellation (NC); Hi-Fi stereo
Weight	138.8 g
Weight	0.31 lb
Package dimensions (W x D x H)	190 x 210 x 55 mm
Package weight	300 g
Special features	UC certified; Adjustable audio alerts
Minimum System Requirements	3.5 mm audio
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Headset (top only)

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Boom mic rotation	280°
Cable length	116 cm
Cable length (imperial)	3.81 ft
Cartons per layer	6
Cartons per pallet	36
Certified collaboration software	Skype for Business; Cisco Jabber; Avaya
Color	Black
Compatibility	Compatible with PCs via USB/USB Type-C®, connects to mobile devices and tablets via 3.5 mm and devices that support USB Type-C®
Compatible Operating Systems	macOS; Windows
Connection type	3.5 mm audio
Country of origin	Made in China or Mexico
ECCN	EAR99
Ear cushions	Artificial leather (surface material)
Ecolabels	TCO Certified
HTS code	8518302000
Headphone type	On-ear (stereo)
Impedance	32 ohms
Management Software	Plantronics Hub (desktop); Plantronics Manager Pro suites (Asset Management and Adoption, Call Quality and Analytics, Health and Safety)
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Stereo
Multiple order quantity	15
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Pallet (layers)	6
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	787.05 lb
Pallet weight	357 kg
Products per pallet	540
Products per pallet layer	90
Sensitivity (microphone)	-38 dBV/Pa

Sensitivity (speaker)	90 dB
Speaker bandwidth	200 Hz to 6.8 kHz (speech mode); 20 Hz to 20 kHz (media mode)
Speaker size	28 mm
UNSPSC code	43191638

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 15, 2024 7:00 AM UTC+0000