



# DIRECT VIEW LED LDS135-153


## Key Features

- Pre-assembled kit ready for instant use
- Foldable screen with the movable flight case for easy delivery
- Shock-proof, dustproof, and moisture-proof through GOB surface treatment
- Built-in stand with motorized height adjustment
- Impressive audio from Harman Kardon speakers



## Product Description

The ViewSonic® LDS135-153 is a foldable 135" All-in-One LED display that boasts instant use, easy delivery, and convenient maintenance, making it an ideal rental-ready solution for events, exhibitions, or any other short-term use. The pre-assembled design and built-in motorized height adjustment stand enable effortless setup within just a few minutes. Delivery convenience is greatly enhanced with the foldable screen design, reducing the packaging size of the movable flight case by nearly 50% compared to the previous generation, thus minimizing shipping costs. Utilizing Glue-on-Board (GOB) surface treatment technology, the IP54-rated LED modules provide enhanced protection against collisions, dust, and moisture during installation and use. With the seamless large screen and superior built-in Harman Kardon speakers, be ready to impress your audience everywhere from high-end boardrooms and receptions to galleries, auditoriums, and other large venues.



- |                           |                       |                                      |                        |
|---------------------------|-----------------------|--------------------------------------|------------------------|
| 1. Harman Kardon Speakers | 8. LAN & Control      | 15. IR Receiver                      | 22. 360° Silent Wheels |
| 2. Power Button           | 9. HDMI 2.0 x 2       | 16. Menu Control: Brightness Level   |                        |
| 3. HDMI Out               | 10. HDMI 1.4 x 2      | 17. Menu Control: Volume             |                        |
| 4. Audio Out              | 11. HDMI 2.1          | 18. Menu Control: Input Source       |                        |
| 5. S/PDIF Out             | 12. RS232             | 19. Power Button                     |                        |
| 6. IR In                  | 13. USB-C (5V/2A)     | 20. Indicator Light                  |                        |
| 7. USB 2.0 (5V/1.5A) x 2  | 14. USB 2.0 (5V/1.5A) | 21. Control Panel: Height Adjustment |                        |

**Visit Us**

[www.viewsonic.com](http://www.viewsonic.com)

## SPECIFICATION

|                        |   |
|------------------------|---|
| Screen Size:           | 135"  |
| Display Area (mm):     | 3000 (H) x 1687.5(V)                                      |
| Native Resolution:     | 1920x1080   |
| Panel Technology:      | Direct view LED   |
| LED Package Type:      | SMD 3 in 1 (GOB)  |
| Pixel Pitch (mm):      | 1.56  |
| Brightness (max.):     | 600 nits (8 levels adjustable)                            |
| Contrast Ratio (typ.): | 6000:1  |
| Orientation:           | Landscape   |
| Viewing Angles (typ.): | H = 170, V = 170  |
| LED Lifetime (typ.):   | 100,000 Hours   |
| Local Storage:         | Total 64GB<br>(56GB available storage)                    |
| Embedded OS:           | Android 9.0   |
| Resolution Support:    | VGA(640 x 480) to<br>1080p(1920 x 1080)                   |
| HDTV Compatibility:    | 480i, 480p, 576i, 576p, 720p, 1080i,<br>1080p, 2160P/60Hz |
| Horizontal Frequency:  | 23-120 kHz  |
| Vertical Scan Rate:    | 15-135 Hz   |

## INPUT

|                        |   |
|------------------------|---|
| HDMI:                  | x6<br>(HDMI 2.1 x 1, HDMI 2.0 x 3, HDMI 1.4<br>x 2) |
| USB Type A:            | x3<br>( USB2.0 x3)                                  |
| RJ45 Input (Internet): | x1  |
| IR in:                 | x1  |
| Wi-Fi Input:           | 2.4G/5G Hz  |
| USB Type C:            | x1<br>(Video input、 Power output (5V/2A))           |

## OUTPUT

|                    |   |
|--------------------|---|
| HDMI out:          | x2<br>(HDMI 2.0 external x1, internal x1) |
| Speaker:           | 20W x2 (Harman Kardon)                    |
| Audio out (3.5mm): | x1  |

## STANDARD ACCESSORIES

|                     |               |
|---------------------|---------------|
| Power Cord:         | x1            |
| LAN Cable (Cat 5A): | x1 (5m)       |
| Remote Control:     | x1            |
| QSG:                | x1            |
| Spare Parts:        | LED module x7 |
| Maintenance Tool:   | LD-MK-005 x1  |

## OPTIONAL ACCESSORIES

|                   |           |
|-------------------|-----------|
| Maintenance Tool: | LD-MK-005 |
|-------------------|-----------|

|                          |                                       |
|--------------------------|---------------------------------------|
| USB Type A (Power):      | Shared with USB input<br>(5V/1.5A x3) |
| <b>CONTROL</b>           |                                       |
| USB Type A (Services):   | x1(shared with USB A input)           |
| RS232 (DB 9-pin female): | x1                                    |
| IR Receiver:             | x1                                    |

## **OTHERS**

|                             |   |
|-----------------------------|---|
| Power Supply Voltage:       | 100-120V/30A~ 50/60Hz or<br>220-240V/15A~ 50Hz<br>(vary by country) |
| Power Consumption:          | 1500W (typ), 2500W (max)<br>< 0.5W (Sleep)                          |
| Operating Temperature:      | 0~40°C  |
| LED Module Quantity:        | 100   |
| Ingress Protection Rating:  | IP54(Front)   |
| Net Weight:                 | 548.95 lbs<br>(249 kg)  |
| Gross Weight:               | 939 lbs<br>(426 kg)   |
| Product Dimensions (WxHxD): | 1800x2022.8x760 mm(min.)<br>3010x2690x760 mm(max.)                  |
| Packing Dimensions (WxHxD): | 74.8x80.79x31.5 inches<br>(1900x2052x800 mm)                        |