

Fiber Splice Dome Enclosure - 6 Splicing Trays, 1152 Fiber Capacity, IP68 Rated

MODEL NUMBER: N600D-1152-6



Allows convenient outdoor connection of fiber cables and protects them from the elements in a large broadband deployment.

Features

Provides Durable, Customizable Protection for Outdoor Fiber Cable Runs

This fiber splicing dome enclosure comes with six splice trays that accommodate up to 192 unterminated cables to give you more flexibility in adjusting cable lengths and connection types directly on-site. The N600D-1152-6 is ideal for singlemode and multimode fiber infrastructure in municipal broadband installations, including residential (Fiber to the Home or FTTH) and commercial (Fiber to the Premise or FTTP). This also includes underground fiber runs and those spanning utility poles.

Flexible Connections in Your Fiber Network

By accommodating and protecting 1,152 splicing connections, the N600D-1152-6 provides a high level of scalability in your network design. The enclosure supports up to six cable entry passthroughs to support a variety of cable runs. Each hinged fiber splice tray allows access to internal cabling without having to remove other trays, making re-entry and re-use convenient.

IP68 Rating Denotes Resistance to Dust and Water

The N600D-1152-6's IP68 rating means the enclosure is 100% protected against dust and able to endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance.

Cable Management That's User Friendly

Built-in labeling cards log which fiber is spliced to each of the 12 main MPO cable colors. Integrated cable ties keep cables well organized and secure. Included tubing protects each splice point.

Multiple Installation Choices

Operating temperature range from -49°F to 149°F (-45°C to 65°C) supports safe installation in a wide range of outdoor climates. It can be installed on a pole, on a wall, on overhead telco lines or underground.

Highlights

- Recommended for FTTH/FTTP installations, including long underground fiber runs
- Accommodates up to 1,152 singlemode and multimode splicing connections
- Hinged splicing trays provide easy access to cabling without removing other trays
- IP68 rated to allow outdoor installations in up to 1.5 meters of water
- Compatible with pole, wall, aerial or underground installation

Package Includes

- N600D-1152-6 1,152 Fiber Splice Dome Enclosure
- (96) Splicing tubes
- (20) Cable ties
- (4) Choke plugs
- (8) Cable grommets
- EVA tube
- Silicon oil
- Insulation tape
- Cleaning paper
- Pole-mounting hardware
- Owner's manual

Specifications

OVERVIEW

UPC Code

037332279873



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Dome Closure
Technology	Multimode; Singlemode
Optical Mode	OM1; OM2; OM3; OM4; OM5; OS2; SM
Panel Dimensions	10.24" X 23.23"
Mode Type	Multimode; Singlemode
Firmware / Software Docs	
Offset Ports	No
CONNECTIONS	
Number of Ports	6
Ports Detail	2 x 8-17.5 mm round2 x 10-25 mm round2 10-25 mm oval
Cassette Capacity	6
Side A - Connector 1	RIBBON FIBER
Side B - Connector 1	RIBBON FIBER
Total Capacity	1152 fibers
Number of Cassette Splicing Trays	6
Splicing Tray Dimensions (hwd/mm)	15 x 132 x 276.5
Cassette Splicing Tray Capacity	192 ribbon fiber
PHYSICAL	
Color	Black; White
Material of Construction	Plastic
Number of Fibers	1152
Housing Color	Black
Rackmountable	No
Shipping Dimensions (hwd / in.)	9.60 x 23.60 x 11.00
Shipping Weight (lbs.)	13.45
Shipping Weight (kg)	6.10
Unit Dimensions (hwd / in.)	23.220 x 10.240 x 23.220
Mounting Details	WALL, POLE, AERIAL
ENVIRONMENTAL	
Operating Temperature Range	-49° to 149° F (-45° to 65° C)
Storage Temperature Range	-49° to 149° F (-45° to 65° C)
Operating Humidity Range	5% to 85% RH, non-condensing
Storage Humidity Range	5% to 85% RH, non-condensing



Powering Business Worldwide

TRIPP LITE
SERIES

FEATURES & SPECIFICATIONS	
Grounding	1 x feed-through ground stud
All-in-One Kit	No
Mounting Accessory Included	No
IP68 Rated	Yes
Ingress Protection (IP) Rating	IP68
Numbered Ports	No
Built-in Cable Management	No
Keystone Jacks	No
Built-in Cables	No
Color-Coded Connections	No
EIA/TIA 2/32 Spacing	No
Labeled Ports	No
Down-Angled Ports	No
Outdoor Use	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.