

PERFORMANCE**Processor**

MediaTek Helio G90T (8C, 2x A76 @2.05GHz + 6x A55 @2.0GHz)

Graphics

Integrated Arm Mali-G76 MC4 GPU

Chipset

MediaTek SoC Platform

Memory

8GB Soldered LPDDR4x

Storage

256GB UFS 2.1

Card Reader

microSD Card Slot

Storage Support

- 256GB UFS 2.1 on systemboard
- microSD card, supports FAT32 up to 512GB, exFAT up to 1TB

Speakers

Quad JBL® speakers, Synopsys codec, 2 x1W (on the top), 2 x2W (on the bottom) with 5cc audio chamber, Lenovo® Premium Audio (LPA) Solution design, optimized with Dolby Atmos®

Microphone

2x, Array

Camera

Front 8.0MP / Rear 8.0MP

VoiceCall

No

Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- ToF sensor

Vibration Motor

Eccentric Rotating Mass (ERM)

Battery

Integrated 7500mAh (Min.) / 7700mAh (Typ.)

Power Adapter

10V / 2A

DESIGN**Display**^[1]

11" 2K (2000x1200) IPS 400nits Anti-fingerprint, 60Hz, Dolby Vision®, Touch

Touchscreen

10-point Multi-touch

Case Material

Metal + Plastic, Fabric

Pen^[2]

Pen Upgradable (Purchase Separately)

Dimensions (WxDxH)^[3]

256.8 x 169.0 x 7.9-8.3 mm (10.11 x 6.65 x 0.31-0.32 inches)

Weight^[4]

Around 650 g (1.43 lbs)

Case Color

Storm Grey

SOFTWARE**Operating System**^[5]

Android™ 11 or Later

CONNECTIVITY**WLAN + Bluetooth®**

Wi-Fi® 5, 802.11ac 2x2 + BT5.0

WWAN

None

Location Services

No location service

Standard Ports

- 1x USB-C® 2.0 (support data transfer and charging)
- 1x Card slot

SERVICE**Base Warranty**^[6]

1-year, Mail-in with 1-year Battery

ACCESSORIES**Bundled Accessories**^[7]

None

CERTIFICATIONS**Green Certifications**

- ENERGY STAR® 8.0 (only available for Lenovo® YT-J706F)
- RoHS compliant

Dust and Water Resistant

IP52

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

Product : Lenovo® YT-J706F

TopSeller : No

Announce Date : 2021-07-20

EAN / UPC / JAN : 196118213880



Product image is a sample, it may not match the real color of this model

Note:

^[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

^[2] For details upon pen compatibility, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>. Pen availability may vary by country / region.

^[3] The system dimensions may vary depending on configurations.

^[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

^[5] For latest operating system and security patches deliver plan, please visit <https://support.lenovo.com/solutions/ht501098>.

^[6] For warranty upgrade service, please go to

<https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

^[7] For more compatible accessories, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

Lenovo reserves the right to change specifications without notice.

California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to

<https://psref.lenovo.com/Detail/1676?M=ZA8W0084US>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration)

- Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Active Pen 3 (2023)

ZG38C04479

With 4,096 levels of pressure and tilt detection, the Lenovo Active Pen 3 (2023) affords users the highest level of precision and control as they sketch or just take notes.



Lenovo Precision Pen 2 (2023)

ZG38C04470

With 4,096 levels of pressure and tilt detection, the Lenovo Precision affords users the highest level of precision and control as they sketch or just take notes.

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF

Product Specifications
Reference