

PERFORMANCE

Processor
AMD Ryzen™ 5 7430U (6C / 12T, 2.3 / 4.3GHz, 3MB L2 / 16MB L3)

Graphics
Integrated AMD Radeon™ Graphics

Chipset
AMD SoC Platform

Memory
8GB Soldered DDR4-3200

Memory Slots
One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

Max Memory^[1]
Up to 16GB (8GB soldered + 8GB SO-DIMM) DDR4-3200 offering

Storage
256GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Storage Support^[2]
Models with 38Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 2242 SSD up to 512GB

Storage Slot
Models with 38Wh battery: one 2.5" drive slot + one M.2 slot

- One 2.5" SATA HDD slot
- One M.2 2280 PCIe® 3.0 x4 slot

Card Reader
None

Optical
None

Audio Chip
High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers
Stereo speakers, 1.5W x2, Dolby Audio™

Camera
HD 720p with Privacy Shutter

Microphone
2x, Array

Battery
Integrated 38Wh

Power Adapter
65W USB-C® (3-pin)

DESIGN

Display
15.6" FHD (1920x1080) TN 250nits Anti-glare

Touchscreen
None

Keyboard
Non-backlit, French / English

Touchpad
Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 62 x 104 mm (2.44 x 4.09 inches)

Case Color
Business Black

Surface Treatment
Texture

Case Material
PC-ABS (Top), PC-ABS (Bottom)

Dimensions (WxDxH)^[3]
359.2 x 235.8 x 19.9 mm (14.14 x 9.28 x 0.78 inches)

Weight^[4]
Starting at 1.65 kg (3.64 lbs)

SOFTWARE

Operating System
Windows® 11 Pro, French / English

Bundled Software
Office Trial

CONNECTIVITY

Ethernet
100/1000M (RJ-45)

WLAN + Bluetooth^[5]
Wi-Fi® 6, 802.11ax 2x2 + BT5.2

Standard Ports

- 1x USB 2.0
- 1x USB 3.2 Gen 1
- 1x USB-C® 3.2 Gen 1 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.2)
- 1x HDMI® 1.4b
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x Power connector

Docking
Various docking solutions supported via USB-C®. For more compatible docking solutions, please visit [Docking for Lenovo® V15 G4 ABP](#)

SECURITY & PRIVACY

Security Chip
Firmware TPM 2.0 Enabled

Fingerprint Reader
None

Physical Locks
Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security
Camera privacy shutter

SERVICE

Base Warranty
1-year, Courier or Carry-in

Included Upgrade
None

ACCESSORIES

Bundled Accessories^[6]
None

CERTIFICATIONS

Green Certifications^[7]

- TCO Certified 9.0
- ENERGY STAR® 8.0
- EPEAT™ Silver Registered
- ErP Lot 6
- ErP Lot 26
- FSC certified package
- RoHS compliant

Other Certifications
TÜV Rheinland® Low Blue Light (Software Solution)

Mil-Spec Test
MIL-STD-810H military test passed

MODEL

TopSeller	: Yes	Announce Date	: 2024-06-19
EAN / UPC / JAN	: 198154611613	End of Support	: 2030-04-26

Product image is a sample, it may not match the real color of this model

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to <https://psref.lenovo.com/Detail/2353?M=83CR0017CA>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo 65W USB-C DC Travel Adapter

40AK0065WW

Power up and stay productive on the road with this DC Travel adapter. Lenovo 65W USB-C DC Travel Adapter is the universal DC adapter, providing 65W power via USB-C for outdoor use.

Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38566)
BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0U55751)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0Q81869)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference