

**PERFORMANCE****Processor<sup>[1]</sup>**

Intel® Core™ i9-14900, 24C (8P + 16E) / 32T, Max Turbo up to 5.8GHz, P-core 2.0 / 5.4GHz, E-core 1.5 / 4.3GHz, 36MB

**Graphics**

Integrated Intel® UHD Graphics 770

**Chipset**

Intel® Q670 Chipset

**Memory**

1x 32GB SO-DIMM DDR5-5200

**Memory Slots**

Two DDR5 SO-DIMM slots, dual-channel capable

**Max Memory<sup>[2]</sup>**

Up to 64GB (2x 32GB DDR5 SO-DIMM)

**Storage**

256GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

**Storage Support<sup>[3]</sup>**

Up to two drives, 2x M.2 2280 SSD

- M.2 2280 SSD up to 2TB

**Card Reader**

No card reader

**Optical**

None

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC233 codec

**Speakers**

Premium, 2Wx1

**Power Supply**

230W 89% Adapter

**DESIGN****Keyboard**

USB Traditional Keyboard, Black, French

**Mouse**

USB Calliope Mouse, Black

**Expansion Slots**

- One PCIe® 4.0 x8, low-profile
- Two M.2 PCIe® Gen 4x4 slots (for SSD)
- One M.2 slot (for WLAN)

**Case Color**

Black

**Stand**

Vertical Stand

**Adapter Cage**

None

**Toolless Chassis Screw**

None

**Dust Filter**

None

**Mounting**

None

**IO Box**

None

**Form Factor**

Tiny (1L)

**Dimensions (WxDxH)<sup>[4]</sup>**

179 x 182.9 x 36.5 mm with rubber feet (7.05 x 7.2 x 1.44 inches with rubber feet)

**Weight<sup>[5]</sup>**

1.25 kg (2.76 lbs)

**CONNECTIVITY****Ethernet**

Integrated 100/1000M

**WLAN + Bluetooth<sup>[6]</sup>**

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

**Front Ports**

- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), with Always On and 5V@2.1A charging
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x headphone / microphone combo jack (3.5mm)

**Optional Front Ports (configured)**

None

**Rear Ports**

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), with Smart Power On
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4a (HBR2, DSC)
- 1x Ethernet (GbE RJ-45)

**Optional Rear Ports (configured)**

1x DP

**SECURITY & PRIVACY****Security Chip**

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

**Fingerprint Reader**

No fingerprint reader

**Physical Locks**

Kensington® Security Slot™, 3 x 7 mm

**Chassis Intrusion Switch**

Chassis Intrusion Switch

**MANAGEABILITY****System Management<sup>[7]</sup>**

Intel® vPro® Enterprise

**SERVICE****Base Warranty**

3-year, Onsite

**Included Upgrade**

None

**CERTIFICATIONS****Green Certifications<sup>[8]</sup>**

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 3
- RoHS compliant
- TCO Certified 9.0

**Mil-Spec Test**

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Solar Radiation, Contamination by Fluids, Salt Fog)

**SOFTWARE****Operating System**

Windows® 11 Pro, French

**Bundled Software**

None

**ACCESSORIES****Bundled Accessories**

None

**MODEL**

**TopSeller** : Yes

**Announce Date** : 2024-07-23

**EAN / UPC / JAN** : 198153870011

**End of Support** : 2031-02-23

**Note:**

[1] Intel Max Turbo frequency will vary depending on application workload and the hardware and software configurations, see <http://www.intel.com/technology/turboboost/> for more information.

[2] The max memory is based on the test results with current Lenovo memory offerings.

[3] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

[4] The system dimensions may vary depending on configurations.

[5] The system weight is approximate and based on results in.....

[6] Lenovo reserves the right to change specifications without notice.

To see more note information, please link to <https://psref.lenovo.com/Detail/2470?M=12TH000WCA>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkCentre Tiny VESA Mount II

4XF0N03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The VESA standard enables this mount to attach to anything that is VESA comp...

## Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39206)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39278)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0V07841)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference