



Philips Signage Solutions
E-paper Signage

25"
Android

SignageSolutions



25BDL41501

Full colour power free displays

Technology for a brighter future

From confidently coloured menus to paper-free posters, bring new era display potential to life. Digitise paper signs or swap out digital models showing static imagery with ultra clear, easily updatable, more sustainable ePaper technology.

Operational flexibility

- Technology for the future
- PPDS Wave-ready for remote management

Brilliant performance. Blazing processor speed

- Android SoC processor
- Full colour ePaper display
- Sunlight readable

Cost-effective system solution

- Zero power to show a static image 24/7/365
- Super low power to change the content

Versatile placement

- No need for a constant power connection
- Sized to easily swap out paper posters and signage

PHILIPS

Specifications

Picture/Display

- Diagonal screen size (inch): 25.3 inch
- Panel resolution: 3200 x 1800
- Aspect ratio: 16:9
- Display colors: 60k
- Operating system: Android 11

Connectivity

- Video input: USB
- Audio output: Audio Left/Right (3.5mm jack)
- Other connections: micro SD, micro USB

Communication

- Ethernet: 10M/100M
- Wi-Fi/ WLAN: 2Tx/2Rx 802.11 ac/a/b/g/n Wi-Fi + BT 5.1 Module

Convenience

- Placement: Landscape (24/7), Portrait (24/7)
- Network controllable: LAN (RJ45)

Operating conditions

- Temperature range (operation): 15~ 35 °C
- Temperature range (storage): -20 ~ 60 °C
- Relative humidity: 20% ~ 80 %
- Altitude: 0 ~ 3000 m

Power

- Mains power: 20V/2.25A adapter

Accessories

- Included Accessories: AC power adapter, Quick start guide (x1)

Miscellaneous

- On-Screen Display Languages: English, Simplified Chinese
- Regulatory approvals: CE, CB, UL, FCC
- Warranty: 3 year warranty

Internal Player

- CPU: Rockchip PX30S
- Memory: 2GB DDR4
- Storage: 16GB EMMC

Dimensions

- Set dimensions (W x H x D): 598.6 x 350.2 x 37.5 mm
- Bezel width: 18.6/18.6/18.6/22mm
- Wall Mount: 100x100mm VESA mount
- Product weight: 2.7 kg

Highlights

Powered by Android

Android-powered Philips professional displays are flexible and secure, optimised for native Android apps and the easy installation of web apps and software directly on the display. All controlled via an Internet connection.

Easy content loading

Displaying 60,000 colours, including blue, for clear and confident messaging, and with 16GB internal memory, with no need for an external media player. Plug into a power source to upload new static content for instant play via USB, LAN or WiFi connections.

PPDS Wave-ready

Your PPDS Wave-ready display enables you to manage and maintain this device remotely, securely switching out content wherever you are, whenever you choose. This evolutionary cloud platform puts you fully in control, with simplified installation and set-up, monitoring and controlling displays, upgrading firmware, managing playlists and setting power schedules. Saving you time, energy and environmental impact.

Low to no power consumption

Perfect for environments without close access to power. Philips Tableaux can be positioned and repositioned, displaying colourful static content in the same way as paper posters, requiring super low power only when loading new content.

Technology for the future

Developing technology for your sustainable future – power free, waste free colourful paper poster replacements.



Issue date 2023-11-20

Version: 1.0.1

12 NC: 8670 001 90386
EAN: 87 12581 80334 6

© 2023 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com