

# ThinkPad X12 Detachable Gen 2 21LK002UCA

Lenovo

**PSREF**  
Product Specifications  
Reference

## PERFORMANCE

### Processor

Intel® Core™ Ultra 7 164U, 12C (2P + 8E + 2LPE) / 14T, Max Turbo up to 4.8GHz, 12MB

### NPU

Integrated Intel® AI Boost, up to 11 TOPS

### Graphics

Integrated Intel® Graphics

### Chipset

Intel® SoC Platform

### Memory<sup>[1]</sup>

32GB Soldered LPDDR5x-6400

### Storage

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal 2.0

### Storage Support

One drive, up to 1TB M.2 2242 SSD

### Speakers

Stereo speakers, 1W x2, Dolby Audio™

### Microphone

2x, Array

### Camera

Front 5.0MP + IR Discrete with Privacy Shutter / Rear 8.0MP

### VoiceCall

No

### Sensors

- Accelerometer (G) sensor
- Gyroscope sensor
- Hall sensor
- Inclinometer sensor

### Vibration Motor

No support

### Battery

Integrated 42Wh

### Power Adapter

65W USB-C® Slim (2-pin)

## DESIGN

### Display<sup>[2]</sup>

12.3" FHD+ (1920x1280) IPS 400nits Anti-reflection / Anti-smudge, 100% sRGB, Lower Power, Touch

### Touchscreen

GMF / GF2, 10-point Multi-touch

### Case Material

Magnesium-aluminium

### Keyboard

Backlit, French

### Pen

Lenovo® Precision Pen

### Dimensions (WxDxH)<sup>[3]</sup>

Tablet: 283.3 x 203.5 x 8.8 mm (11.15 x 8.01 x 0.35 inches)

Folio keyboard: 283.3 x 217.8 x 5.7 mm (11.15 x 8.57 x 0.22 inches)

Total: 283.3 x 208.1 x 14.5 mm (11.15 x 8.19 x 0.57 inches)

### Weight<sup>[4]</sup>

Tablet: 0.76 kg (1.67 lbs)

Folio keyboard: 0.34 kg (0.75 lbs)

Total: 1.1 kg (2.42 lbs)

### Case Color

Black

## SOFTWARE

### Operating System

Windows® 11 Pro, French

### Bundled Software

None

## CONNECTIVITY

### WLAN + Bluetooth®

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

### WWAN

Non-WWAN

### SIM Card

None

### NFC

None

### Location Services

No location service

### Standard Ports

- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 and DisplayPort™ 2.1
- 1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Pogo pin connector (8-point)

### Optional Ports (configured)

None

### Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® X12 Detachable Gen 2](#)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0 Enabled

### Fingerprint Reader

Touch Style, Match-on-Chip, on Keyboard

## MANAGEABILITY

### System Management

Intel® vPro® Enterprise

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories<sup>[5]</sup>

ThinkPad® X12 Detachable Gen 2 Folio Keyboard

## CERTIFICATIONS

### Green Certifications<sup>[6][7]</sup>

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 10.0

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

TopSeller : Yes

Announce Date : 2024-06-10

EAN / UPC / JAN : 198153657148



Product image is a sample, it may not match the real color of this model

Note:

[1] Installed memory is actually LPDDR5x-7500 but run as LPDDR5x-6400 due to platform limitation.

[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[3] The system dimensions may vary depending on.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/2482?M=21LK002UCA>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

## Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39383)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36154)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A14086)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference