

PERFORMANCE

Processor
Intel® Core™ Ultra 7 155U, 12C (2P + 8E + 2LPE) / 14T, Max Turbo up to 4.8GHz, 12MB

AI PC Category
AI PC

NPU
Intel® AI Boost, up to 11 TOPS

Graphics
Integrated Intel® Graphics

Chipset
Intel® SoC Platform

Memory
16GB Soldered LPDDR5x-7467

Memory Slots
Memory soldered to systemboard, no slots, dual-channel

Max Memory
16GB soldered memory, not upgradable

Storage
512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Storage Support^[1]
One drive, up to 2TB M.2 2280 SSD

Storage Slot
One M.2 2280 PCIe® 4.0 x4 slot

Card Reader
None

Optical
None

Audio Chip
High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers
Stereo speakers, 2W x2, Dolby Audio™

Camera
5.0MP + IR Discrete with Privacy Shutter

Microphone
2x, 360°

Battery
Integrated 58Wh

Power Adapter
65W USB-C® Slim (2-pin)

DESIGN

Display^[2]
14" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, DBEF5

Touchscreen
None

Keyboard
Backlit, French

Case Color
Black

Case Material
Carbon Fiber Hybrid (Top), Aluminium (Bottom)

Dimensions (WxDxH)^[3]
313.6 x 219.4 x 16.9 mm (12.35 x 8.64 x 0.67 inches)

Weight^[4]
Starting at 1.24 kg (2.73 lbs)

SOFTWARE

Operating System
Windows® 11 Pro, French

Bundled Software
None

CONNECTIVITY

Ethernet^[5]
No Onboard Ethernet

WLAN + Bluetooth^[6]
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

WWAN
None

SIM Card
None

NFC
None

- Standard Ports**
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
 - 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
 - 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
 - 1x HDMI® 2.1, up to 4K/60Hz
 - 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)
None

Docking
Various docking solutions supported via Thunderbolt™ / USB-C®.
For more compatible docking solutions, please visit [Docking for ThinkPad® T14s Gen 5](#)

SECURITY & PRIVACY

Smart Card Reader
None

Security Chip
Discrete TPM 2.0 Enabled

Fingerprint Reader
Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks
Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security

- Camera privacy shutter (camera models)
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management
Non-vPro®

SERVICE

Base Warranty
1-year, Courier or Carry-in

Included Upgrade
None

ACCESSORIES

Bundled Accessories^[7]
None

CERTIFICATIONS

- Green Certifications**^[8]
- ENERGY STAR® 8.0
 - EPEAT™ Gold Registered
 - ErP Lot 6/26
 - RoHS compliant
 - TCO Certified 9.0

Mil-Spec Test
MIL-STD-810H military test passed

MODEL

TopSeller	: Yes	Announce Date	: 2024-05-21
EAN / UPC / JAN	: 198154120696	End of Support	: 2030-11-16

Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[3] The system dimensions may vary depending on configurations.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[5] Ethernet support via optional Lenovo USB-C to Ethernet Adapter.

[6] Wi-Fi 6E full features might be limited by country-level.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to <https://psref.lenovo.com/Detail/2474?M=21LS0058CA>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39383)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36154)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A14086)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference