

Philips Public LED 5000 Series

44" Cabinets

Philips Signage Solutions
LED Display

44"

Direct View LED



44HDL5000PP

Philips Public LED 5000

Elevate your visual journey

Empower uniquely crafted Public LED displays that redefine audience engagement. Deliver your immersive visual experiences with seamless connectivity, variable sizing and customisable curvature, allowing you to design a breathtaking display.

Ensures crystal-clear content

- Ensures crystal-clear content and great colour accuracy.
- Brightness uniformity exceeding 97%.

Vivid picture enhancement

- Contrast excellence
- Elevate your visual experience.
- Lower power consumption

Precisely aligned, seamless and bezel-free

- Front-access maintenance
- Create bezel-free video walls
- Lightweight wall-mountable or hoisted installation
- Built-in cable management

PHILIPS

Specifications

Picture/Display

- Aspect ratio: 1:2
- Brightness Uniformity: $\geq 97\%$
- Calibration (brightness/colour): Supported
- Colour temperature adjust range: 4000~9500 K (by software)
- Colour temperature default: 6500±500 K
- Contrast ratio (typical): $\geq 3000:1$
- Viewing angle (horizontal): 150 degree
- Viewing angle (vertical): 150 degree
- Picture enhancement: Wide colour gamut display
- Placement: Landscape, Portrait
- Frame frequency (Hz): 50 & 60
- Refresh rate (Hz): Up to 3840 Hz
- Three specific modules of pixel pitch: 1.9 mm, 2.5 mm and 3.9 mm

Convenience

- Ease of installation: Guide pins, Light weight, Locking mechanism for cabinet
- Power loop through: - for 230 V environments: 8 cabinets or fewer - for 110 V environments: 4 cabinets or fewer
- Signal control loop through: RJ45

Operating conditions

- Temperature range (operation): -20~45 °C

- Temperature range (storage): -20~50 °C
- LED Lifetime: TBD
- Humidity range (operation)[RH]: 10~80%
- Humidity range (storage) [RH]: 10~85%

Cabinet

- Cabinet area (m²): 0.50
- Cabinet size (mm): 500 x 1000 x 40
- Data connector: RJ45
- Power connector: In/Out (C14/C13)
- Receiving card brand: Novastar
- Weight (kg): 11.2
- Cabinet diagonal (inch): 44.02
- Cabinet construction: Die-cast aluminium

Accessories

- LAN cable (RJ45, CAT-5): 1 pcs
- QSG: 1 pcs

Miscellaneous

- Warranty: 2 years
- Regulatory approvals: RoHS, EAC, EN61000-3-2, EN61000-3-3, IEC/UL60950, IEC/UL62368, IEC62471, EN55032, EN55035, FCC SDOC, Part 15, Class A

Highlights

Ensures crystal-clear content

Ensures crystal-clear content and great colour accuracy. Achieves smooth, judder-free images with a high refresh rate.

Brightness uniformity exceeding 97%.

Revel in consistent brilliance with a brightness uniformity that exceeds 97%.

Elevate your visual experience.

Elevate your visual experience with a wide colour gamut for lifelike images.

Contrast excellence

Witness exceptional clarity with a contrast ratio of $\geq 3000:1$.

Lower power consumption

Developing technology for your sustainable business future through built-in power saving features.

Lightweight wall-mountable or hoisted installation

As well as an optional range of connections and brackets for wall mounting, the Philips Public LED 5000 Series also supports fixed hoisting installations.

Front-access maintenance

Internal electronics are easy to access and replace for service and maintenance. The modules in the cabinet can be easily and safely removed with the dedicated removal tool.

Bezel-free

Simply connect multiple LED display cabinets to create the resolution that you want — whether its 4K, 8K or even higher. Compared to LCD screens, LED displays boast higher refresh rates that enable smoother images. Whatever the application, you'll thrill your audience with crystal-clear picture quality.

Built-in cable management

Philips Public LED 5000 Series displays come with built-in cable management, keeping power and data cables tidy. Meanwhile, cabinets are daisy chained for both power and data, using PPDS' unique board-to-board module and cabinet connection design, minimising clutter and speeding up installations.

