



Key Features

- Customizable screen size with All-in-One design for hassle-free installation
- Anti-collision, dustproof, and moisture-proof through GOB surface treatment
- Centralized and efficient management via LAN control
- Detachable system control box for minimalistic aesthetics and easy access
- Ultra-slim design that seamlessly blends into any space



Product Description

The ViewSonic LDC series is an innovative, customizable All-in-One LED display that offers flexible sizing and effortless installation—all in a single solution. Combine the LDC031-120 LED cabinet to create video walls in diverse aspect ratios and sizes, delivering compelling digital signage that brings your concepts to life. Its all-in-one design ensures a hassle-free installation process and intuitive operation. Using Glue-on-Board (GOB) surface treatment technology, the IP54-rated LED modules provide enhanced protection against collision, dust, and moisture—making it ideal for public spaces such as lobbies, shopping malls, and transportation hubs. With its slim 31mm thickness and a control box that can be detached to achieve a 99% screen-to-body ratio, this premium display offers an exceptional viewing experience with sleek aesthetics. Complete with centralized management through LAN connectivity to enhance operational efficiency.

1. Speakers	8. Light Sensor	15. Menu Control: Brightness Level
2. HDMI Out	9. IR Receiver	16. Power Button
3. SPDIF Out	10. USB-C	17. Indicator Light
4. HDMI In*4	11. USB-A 3.0	
5. LAN	12. USB-A 2.0	
6. Audio Out*2	13. Menu Control: Setting	
7. IR Interface	14. Menu Control: Enter	

SPECIFICATION		OTHERS	
Screen Size:	31.5"	Power Supply Voltage:	100-120V/30A ~ 50/60Hz or 220-240V/15A ~ 50Hz (vary by country)
Display Area (mm):	640 (H) x 480(V)	Power Consumption:	145W per cabinet < 0.5W (Hibernate)
Native Resolution:	512x384	Operating Temperature:	0~40°C
Panel Technology:	Direct view LED	LED Module Quantity:	6 per cabinet
LED Package Type:	IMD 2 in 1 (GOB)	Ingress Protection Rating:	IP54(Front)
Bonding Wire:	Copper	Net Weight:	13.89 lbs (6.3kg) per cabinet
Pixel Pitch (mm):	1.25	Product Dimensions (WxHxD):	25.2x18.9x1.2 inches (640 x 480 x 31mm) per cabinet
Brightness (max.):	600 nits (100 levels adjustable)	STANDARD ACCESSORIES	
Contrast Ratio (typ.):	6500:1	Power Cord:	x1
Orientation:	Landscape	LAN Cable (Cat 5E):	x1
Viewing Angles (typ.):	H = 170, V = 170	IR Extender Cable:	x1
LED Lifetime (typ.):	100,000 Hours	Remote Control:	x1
Local Storage:	Total 32GB (26GB available storage)	QSG:	x1 (Installation guide)
Embedded OS:	Android 9.0	Wall Mount:	x1
Resolution Support:	VGA(640 x 480) to 4K(3840 x 2160@60hz)	Spare Parts:	LED module 7%
HDTV Compatibility:	480p, 576p, 720p, 1080p, 2160p	Maintenance Tool:	LD-MK-004 x1
Horizontal Frequency:	31K-94kHz	Maintenance Tool:	LD-MK-004
Vertical Scan Rate:	56-85Hz	Floor Stand:	LD-STND-009 (support 4x3/4x4/5x3/5x4/6x3/6x4)
INPUT		OPTIONAL ACCESSORIES	
HDMI:	x4 (HDMI 2.0, HDCP 2.2) (internal x3 + external x1)	x2 (USB3.0 x1, USB2.0 x1)	
USB Type A:	x2 (USB3.0 x1, USB2.0 x1)	x3 (internet x2, control x1)	
RJ45 Input (Internet):	x1	Wi-Fi Input:	2.4G/5G Hz
IR in:	x1	USB Type C:	x1 (data only)
OUTPUT			
HDMI out:	x1 (HDMI 1.4, HDCP 1.4) (internal x1)	Speaker:	30Wx2
Speaker:	30Wx2	Audio out (3.5mm):	x2
Audio out (3.5mm):	x2	USB Type A (Power):	Shared with USB input (5V/0.9A x1, 5V/0.5A x1, USB-C 5V/1A x1)
CONTROL			
RJ45 (LAN control):	x1(shared with internet)		
USB Type A (Services):	x1(shared with USB A input)		
RS232 (DB 9-pin female):	x1		
IR Receiver:	x1		

Copyright © ViewSonic Corporation 2000-2024. All rights reserved.