

NEC MultiSync® M651-2 LCD 65" Message Essential Large Format Display

Datasheet



Intuitive professional content delivery

Great first impressions can make all the difference; presenting your business in the best possible way will boost your brand. With slim, modern styling, 24/7 operation and high haze panel to reduce reflections when ambient light is high, the Mxx1-2 series is the professional way to deliver your message, yet at an attractive price point.

With the optional Raspberry PI Compute Module or the more powerful Intel® Smart Display Module (Intel® SDM) computing device, you are primed and ready for intuitive signage creation delivering real-time media playback for exceptional visual experiences. For advertising, infotainment and meeting room applications, the Mxx1-2-2 Series provides powerful, upgradable functionality and all the aesthetic appeal to effortlessly reflect your brand credentials.

Benefits

Modern and slim design – robust yet elegant allowing for an unobtrusive integration into any application and environment.

Secure remote management – control your devices remotely and securely using NEC NaviSet Administrator 2; proactively manage maintenance requirements saving time and resources

Ease of use and operation – smart installation, operation and maintenance functionality ensures accurate performance over the entire lifetime of the display saving time, effort and resources.

Future Ready Connectivity – featuring multiple industry standard digital and analogue signal inputs for flexible integration into AV infrastructures.

Effortless content playback – the integrated USB media player supports various image video file formats for effortless and standalone content playback.

Product Information

Product Name	NEC MultiSync® M651-2
Product Group	LCD 65" Message Essential Large Format Display
Order Code	60006086

Display

Panel Technology	IPS with Direct LED backlights
Screen Size [inch/cm]	65 / 163.9
Aspect Ratio	16:9
Brightness [cd/m ²]	500
Contrast Ratio	≥ 8000:1 ¹
Viewing Angle [°]	178 horizontal / 178 vertical (typ. at contrast ratio 10:1)
Colour Depth [bn]	1.073 (8bit + FRC)
HDR	HDR10; HLG; PQ
Response Time (typ.) [ms]	6
Panel Refresh Rate [Hz]	60
Haze Level [%]	Pro (25)
Supported Orientation	Landscape; Portrait

Resolution

Native Resolution	3840 x 2160
Supported Resolutions	1024 x 768; 1366 x 768; 1650 x 1050; 3840 x 2160; 1280 x 1024; 1400 x 1050; 1920 x 1080; 4096 x 2160 1280 x 720; 1440 x 900; 1920 x 1200; 1360 x 768; 1600 x 1200; 1920 x 2160;

Synchronisation Rate

Horizontal Frequency [kHz]	26 - 135
Vertical Frequency [Hz]	23 - 86

Connectivity

Input Video Digital	1 x DisplayPort (with HDCP); 2 x HDMI (with HDCP)
Input Audio Digital	1 x DisplayPort; 2 x HDMI
Input Control	LAN 100Mbit; remote control wire (3,5mm jack); RS232
Input Data	1 x USB 2.0 (MediaPlayer)
Output Audio Analogue	1 x 3,5 mm jack
Input Detect	Custom; First; Last

Open Modular Intelligence

Intel® SDM	accepts Intel® Smart Display Modules Large and Small up to 66 W
Compute Module Slot	RPi Compute Module 4

Sensors

Temperature Sensor	Integrated, 3 sensors, triggered actions programmable
--------------------	---

Electrical

Power Consumption [W]	165 shipping
Power Savings Mode [W]	< 0.5; < 2 (Networked Standby)
Power Management	VESA DPMS
Power Supply	100-240 V AC; 50/60 Hz; internal

Environmental Conditions

Operating Temperature [°C]	+0 to +40
Operating Humidity [%]	20 to 80
Storage Humidity [%]	10 to 90
Storage Temperature [°C]	-20 to 60

Mechanical

Dimensions (W x H x D) [mm]	1,462.3 x 837.3 x 68.1
Weight [kg]	29.4
Bezel Width [mm]	14.9
VESA Mounting [mm]	4 holes; 400 x 400 (FDMI); M8
Ingress Protection	IP5x (front); IP2x (back)
Packaging Dimensions (W x H x D) [mm]	1,736 x 1,033 x 280
Packaging Weight [kg]	41.7
Colour Bezel	Pantone 426M (black)
Material	Metal

Media Player

Supported File Storage / File System	USB 2.0 / FAT16, FAT32
--------------------------------------	------------------------

Supported Image Formats	JPG (baseline, progressive, RGB, CMYK); max. resolution 15360 x 8640
Supported Video Formats	MPG (MPEG1/2/4, max res 1080p@30Hz); MP4 (MPEG2/4, H.263, H.264, HEVC/H.265, max res 3840x2160@60Hz); TS (MPEG2, H.264, HEVC/H.265, max res 3840x2160@60Hz); audio: LPCM, MP3, AAC; WMV (video H.264, Windows Media Video 9, max res 1080p@30Hz, audio WMA 9, WMA 10 Pro)
Supported Audio Formats	MP3 (MP3); max. bit-rate 320 kBit/s

Available Options

Accessories	Feet (ST-65M); Presence Sensor (KT-RC3); Trolley (PD04-Tipster Trolley); Wall mount (PDW S 32-65 L, PDW S 32-65 P)
-------------	--

Regulatory

Safety and Ergonomics	BSMI; CE; EAC; EMC Class B; Energy Star 8; FCC Class B; KC/KCC; PSB; RCM; RoHS; VCCI
Pixel Failure Class	ISO 9241-307, Class 1
Resistance to Fire	Metal backcover, plastic material certified acc. to UL94-5VB

Green Features

Energy Efficiency	Energy consumption: 156 kWh/1000 h; Energy efficiency class: G; LED backlight
Ecological Standards	EnergyStar 8.0

Additional Features

Special Characteristics	DICOM Simulation; HDMI ARC; Powered USB Port (10 W); Removable Logo
Audio	Integrated Speakers (10 W + 10 W)
Shipping Content	2x AAA batteries; Display; HDMI Cable; Power Cable; Remote Control; Setup Manual
Warranty	3 years warranty incl. backlight; additional services available; optional 4. + 5. year warranty extension ²
Operating Hours	24/7
External Control	AMX NetLinx Support; ASCII Control Commands; Crestron Connected; HDMI CEC; HTTP Browser; PJLink; Scheduled Timer; Scheduled Timer; SNMP
Remote Management	Automated Email Alerts; NEC NaViSet Administrator 2
Security	Disable HW Buttons; Disable IR Functionality; Emergency Notification

¹ out of the box conditions, local dimming ON

² please refer to terms and conditions of warranty extensions



RoHS



VCCI



CE



RCM



FCC Class B

This document is © 2024 Sharp NEC Display Solutions Europe GmbH.

All rights reserved in favour of their respective owners. All hardware and software names are brand names and/or registered trademarks of the respective manufacturers. All specifications are subject to change without notice. Errors and omissions are excepted. 02.10.2024