

## PERFORMANCE

### Processor

Intel® Core™ i9-14900, 24C (8P + 16E) / 32T, Max Turbo up to 5.8GHz, P-core 2.0 / 5.4GHz, E-core 1.5 / 4.3GHz, 36MB

### NPU

Discrete NPU card

### Graphics<sup>[1]</sup>

NVIDIA® GeForce RTX™ 4060 8GB GDDR6

### Chipset

Intel® SoC Platform

### Memory

1x 32GB SO-DIMM DDR5-5200

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

### Max Memory<sup>[2]</sup>

Up to 64GB DDR5-5200

### Storage

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

### Storage Support<sup>[3]</sup>

Dual SSD mode: up to two drives, 2x M.2 SSD  
• M.2 2280 SSD up to 2TB

### Card Reader

No card reader

### Optical

None

### Audio Chip

High Definition (HD) Audio

### Speakers

2Wx1

### Power Supply

350W 92%

## DESIGN

### Keyboard

USB Calliope Keyboard, Black, French

### Mouse

USB Calliope Mouse, Black

### Expansion Slots

Four M.2 slots (one for WLAN, one for AI Card, two for SSD)

### Case Color

Luna Grey

### Pen

Pen Not Supported

### Form Factor

Tiny (3.6L)

### Dimensions (WxDxH)<sup>[4]</sup>

195 x 191 x 108 mm (7.68 x 7.52 x 4.25 inches)

### Weight<sup>[5]</sup>

Around 3.5 kg (7.72 lbs)

## CONNECTIVITY

### Ethernet

Integrated 100/1000M

### WLAN + Bluetooth®

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

### WWAN

Non-WWAN

### Front Ports

- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports 5V@2.1A charging
- 1x headphone / microphone combo jack (3.5mm)

### Rear Ports

- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x HDMI® 2.1 TMDS
- 1x HDMI® 2.1a FRL
- 4x DisplayPort™ 1.4a
- 1x Ethernet (GbE RJ-45)

### Optional Rear Ports (configured)

- DP 1.4
- 1x HDMI® 2.1a FRL, 3x DP 1.4a (HBR3, DSC) on NVIDIA® GeForce RTX™ 4060

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0 integrated in chipset

### Fingerprint Reader

No fingerprint reader

### Physical Locks

Kensington® Security Slot™

## MANAGEABILITY

### System Management<sup>[6]</sup>

Intel® vPro® Enterprise

## SERVICE

### Base Warranty

1-year, Onsite

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 3
- GREENGUARD®
- RoHS compliant
- TCO Certified

## SOFTWARE

### Operating System

Windows® 11 Pro, French

### Bundled Software

None

## ACCESSORIES

### Bundled Accessories

None

## MODEL

**TopSeller** : Yes

**Announce Date** : 2024-07-02

**EAN / UPC / JAN** : 198154604714

**End of Support** : 2031-01-29



Product image is a sample, it may not match the real color of this model

Note:

[1] The information of integrated graphics are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

[2] The max memory is based on the test results with current Lenovo memory offerings.

[3] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

[4] The system dimensions may vary depending on configurations.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] Intel vPro offers a superset of DASH's defined.....

• Lenovo reserves the right to change specifications without notice.

To see more note information, please link to <https://psref.lenovo.com/Detail/2489?M=12W1001HCA>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkCentre Tiny VESA Mount II

4XFON03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The VESA standard enables this mount to attach to anything that is VESA comp...



### ThinkPad USB3.0 to Ethernet Adapter

4X90S91830

The ThinkPad USB3.0 to Ethernet Adapter is quick and easy way to connect your notebook and desktop to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference