

PERFORMANCE**Processor**

MediaTek Kompanio 838 (8C, 2x A78 @2.6GHz + 6x A55 @2.0GHz)

NPU

Integrated MediaTek NPU 650, up to 4 TOPS

Graphics

Integrated Arm Mali-G57 MC3 GPU

Chipset

MediaTek SoC Platform

Memory^[1]

4GB Soldered LPDDR4x-3733

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

4GB soldered memory, not upgradable

Storage

64GB eMMC 5.1

Storage Slot

eMMC on systemboard, no slots

Max Storage Support^[2]

64GB eMMC 5.1 on systemboard

Card Reader

No card reader

Audio Chip

High Definition (HD) Audio

Speakers

Stereo speakers, 1W x2, optimized with Waves MaxxAudio®, Smart Amplifier (AMP)

Microphone

2x, Array

Camera

Front 5.0MP with Privacy Shutter / Rear 8.0MP

Battery

29Wh

Power Adapter

45W USB-C® (3-pin)

DESIGN**Display^[3]**

10.95" WUXGA (1920x1200) IPS 400nits Glossy / Anti-fingerprint, 72% NTSC, 60Hz, Gorilla® Glass 3, Touch

Touchscreen

In-cell, 10-point Multi-touch

Pen

Pen Upgradable (Purchase Separately)

Keyboard

None

Touchpad

Mylar® surface one-piece multi-touch trackpad on the keyboard, 48.8 x 86.8 mm (1.92 x 3.42 inches)

Dimensions (WxDxH)^[4]

273.92 x 173.72 x 14.35 mm (10.78 x 6.84 x 0.56 inches)

Weight^[5]

Around 805 g (1.77 lbs)

Case Color

Luna Grey

Case Material

PU

Surface Treatment

Anodizing Sandblasting

Others

Buttons: power key, volume key

SOFTWARE**Operating System**

ChromeOS

Bundled Software

None

CONNECTIVITY**WLAN + Bluetooth**

Wi-Fi® 6, 802.11ax 2x2 + BT5.3

WWAN

WWAN Not Supported

SIM Card

None

Ethernet

No Onboard Ethernet

Standard Ports

- 2x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with USB PD 3.0 and DisplayPort™ 1.4
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Pogo pin connector (3-point)

Docking

- Chromebook folio keyboard with touchpad (Pogo pin, detachable)
- Various docking solutions are supported via USB-C®. For more compatible docking solutions, please visit [Docking for Lenovo® Chromebook Duet EDU G2](#)

SECURITY & PRIVACY**Security Chip**

Google Security Chip H1

Fingerprint Reader

None

Other Security

Camera privacy shutter

SERVICE**Base Warranty**

1-year, Mail-in

Included Upgrade

None

ACCESSORIES**Bundled Accessories**

None

CERTIFICATIONS**Green Certifications^[6]**

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

- ASTM F963 test passed
- TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

Product : LNV Chrome Duet EDU G2

TopSeller : Yes EAN / UPC / JAN: 198153586189

Announce Date: 2024-08-15 End of Support : N/A

Note:

[1] Installed memory is actually LPDDR4x-4266 but runs as LPDDR4x-3733 due to processor limitation.

[2] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[3] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[4] The system dimensions may vary depending on configurations.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS. Please visit epeat.net and energystar.gov for more information.

• Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.

• Lenovo reserves the right to change specifications without notice.

• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Recommended Accessories

 United States of America



Lenovo Self-Charging Bluetooth Keyboard-French Canadian 058 4Y41R69498



Lenovo GaN Nano 65W Adapter
40AWGN65US

Please click [here](#) to view the full list of accessories.

Recommended Services

BEST	4Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0V13679)
BETTER	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0Q81869)

Lenovo

PSREF
Product Specifications
Reference