

**PERFORMANCE****Display Size**

27"

**View Area**

597.9x336.3 mm

**Panel**

In-Plane Switching

**Backlight**

WLED

**Aspect Ratio**

16:9

**Resolution**

1920x1080

**Pixel Pitch**

0.3114x0.3114 mm

**Dot / Pixel Per Inch**

82 dpi

**View Angle (H / V)**

178° / 178°

**Response Time**

1ms (MPRT@100Hz) / 4ms (Extreme Mode) / 6ms (Normal Mode) / 14ms (Off Mode)

**Color Support**

16.7 Million

**Refresh Rate**

48Hz - 100Hz

**Brightness**300 cd/m<sup>2</sup>**Contrast Ratio**

1500:1

**Color Gamut**

99% sRGB

**Screen Surface Treatment**

Anti-glare

**Curvature**

None

**Camera**

None

**Microphone**

None

**Speakers**

3Wx2

**Power Consumption (Typical / Maximum)**

17.5W / 31.5W

**Power Adapter**

Integrated

**Touchscreen**

None

**Smart System**

None

**DESIGN****Stand**

Tilt

**Case Color**

Cloud Grey

**Side Bezel Width**

2.0 mm

**Mounting**

Supports VESA mount 100mm

**ThinkCentre® M Series Support**

None

**Dimensions (WxDxH)<sup>[1]</sup>**

- Lowest Position | 611.5 x 181.5 x 474.6 mm (24.07 x 7.15 x 18.69 inches)
- Highest Position | 611.5 x 181.5 x 474.6 mm (24.07 x 7.15 x 18.69 inches)
- Head Only | 611.5 x 41.0 x 355.6 mm (24.07 x 1.61 x 14.00 inches)

**Packaging Dimensions (WxDxH)**

715.0 x 113.0 x 417.0 mm (28.15 x 4.45 x 16.42 inches)

**Weight<sup>[2]</sup>**

- Monitor With Stand | 3.88kg (8.55lbs)
- Monitor Head Only | 2.91 kg (6.42 lbs)

**Packaging Weight**

6.22 kg (13.71 lbs)

**CONNECTIVITY****USB Port**

None

**Video Connector**

2x HDMI® 1.4, 1x VGA

**Network Connectivity**

None

**SERVICE****Base Warranty**

1-year

**CERTIFICATIONS****Environmental Certification**

RoHS, EU Energy Efficiency Level (Level-D), EPEAT™ Gold, ENERGY STAR® Certified

**Ergonomic Certification**

TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort, Eyesafe® Display 2.0

**Sync Technology**

None

**Special Features**

- Lenovo® Artery (Lenovo® Accessories and Display Manager) Support
- Lenovo® Artery supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).
- Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- Natural Low Blue Light

**SOFTWARE****Operating System**

Support Windows® 10, Windows® 11

**ACCESSORIES****Video Cables**

HDMI® cable

**MODEL****Announce Date****EAN /****UPC /**

: 2024-07-03 / 0198153419067 / 198153419067 / None

**JAN**

Product image is a sample, it may not match the real color of this model

**Note:**<sup>[1]</sup> The system dimensions may vary depending on configurations.<sup>[2]</sup> The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

Lenovo reserves the right to change specifications without notice.

To see more note information, please link to  
<https://psref.lenovo.com/Detail/2613?M=67BEKCC1US>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkCentre Tiny VESA Mount II

4XF0N03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The VESA standard enables this mount to attach to anything that is VESA comp...



### NanoSaver Essential Cable Lock from Lenovo

4XE1F30276

The Lenovo Security Cable Lock allows customers to manage physical security access within the enterprise, offices, schools, libraries, or in other public spaces. Cable locks help reduce theft, and increase physical as...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference