

Big Impact Meets Budget Friendly

High Bright Budget-Friendly DLP® Projectors

An outstanding price-performance ratio performer, the InFocus Genesis III Series combines ultra-long lamp life, high brightness, and superb connectivity. They are designed for tight budgets, so you don't have to sacrifice image quality or performance.

The InFocus Genesis III Series truly offers the best of both worlds: affordability and great projection capabilities, making it the perfect choice for cost-conscious users who demand excellence.



Models:

IN0002SL, IN0004SL, IN0006SL

Industry-leading 15000 hours lamp lifespan

Our lamps are designed to last longer, ensuring extended durability and long-term performance. This exceptional longevity reduces the need for replacements, offering unparalleled reliability and cost savings over time.

Bright, Vivid Images On Any Surface with 4000 lumens

Transform any room into a dynamic presentation space or vibrant cinema even in ambient environment. With 4000 lumens, image colours and details are crisp and clear. Presentations look more professional, and even simple video clips become more engaging.

Low Latency Gaming Mode for Seamless Gameplay

Enhance your gaming experience with low-latency for smoother and more responsive gameplay. The Game Mode minimizes lag to ensure real-time game delivery, making your gameplay more immersive and exhilarating so you can enjoy the game to the fullest.

Eco-Friendly with Minimal Maintenance

With minimal maintenance and no filter to replace, this means less waste and reduced environmental impact contributing to sustainability and supports a greener future while providing reliable and consistent performance.

WHY CHOOSE GENESIS III SERIES



Advanced Digital Image Correction

With the new digital edge masking and image shift features – we make getting those final image adjustments perfect easy.



24/7 Operation

The Genesis III Series is designed for 24/7 operations in standard orientation and is ideal for applications requiring extended projection periods.



Direct Power On/ Direct Power off

No more waiting. The projector instantly powers up when it receives an electric current. When you are finished, simply switch off the power, no need for lengthy cooling period to shut it down.



USB-A Power for Devices

The integrated USB-A power source conveniently powers HDMI devices like Google Chromecast or a wireless dongle to enhance presentation performance.



Low Total Cost of Ownership

Industry-leading 15000 hours of lamp life and filter-free design saves you time and money.



Lightweight and Portable

Its compact and light form makes it portable giving you flexibility for different uses.



Outstanding 30000 : 1 Contrast Ratio

Indulge in a vivid, clear visual feast with enhanced image clarity and better details with deeper blacks and brighter whites.




Full 3D Capability

The InFocus Genesis III Series is designed to display 3D content from almost any 3D source, including 3D Blu-ray players and the latest game consoles. Picture watching a movie at home or visualizing product concepts at the office - characters and products pop out and deliver a mesmerizing visual experience.



GENESIS III SERIES CONNECTIVITY



InFocus Genesis III		IN0002SL	IN0004SL	IN0006SL
Image	Projection Technology	TI DLP®	TI DLP®	TI DLP®
	Panel Size	0.55" DMD	0.55" DMD	0.65" DMD
	Native Resolution	SVGA, 800 x 600	XGA, 1024 x 768	WXGA, 1280 x 800
	Aspect Ratio	4:3	4:3	16:10
	Brightness (Lumens)	4000	4000	4000
	Contrast Ratio	30000:1	30000:1	30000:1
	Light Source	UHP Lamp 15000	UHP Lamp UHP	UHP Lamp UHP
	Light Source Life Maximum (Hours)	15000	15000	15000
	Maximum Supported Resolution	1920 x 1200	1920 x 1200	1920 x 1200
	Horizontal Sync. Range (KHz)	15~ 97.55	15~ 97.55	15~ 97.55
Vertical Sync. Range (Hz)	54 ~ 85	54 ~ 85	54 ~ 85	
Uniformity (%)	80%	80%	80%	
Optical	Lens	1.1X	1.1X	1.1X
	Lens Zoom Adjustment	Manual	Manual	Manual
	Image Offset (%)	115%	115%	112.4%
	Focal Length (mm)	21.85~24.01	21.85~24.01	21.85~24.01
	Keystone Adjustment	Manual/Automatic	Manual/Automatic	Manual/Automatic
	Vertical Keystone Correction	± 40°	± 40°	± 40°
	Projection Factor	1.94 ~ 2.16:1	1.94 ~ 2.16:1	1.54 ~ 1.72:1
	Projection Distance (Meters/Feet)	1.2 ~ 12.0 / 3.94 ~ 39.36	1.2 ~ 12.0 / 3.94 ~ 39.36	1.0 ~ 10.0 / 3.28 ~ 32.80
	Optical Zoom	1.1:1	1.1:1	1.1:1
	Digital Zoom Demagnification / Magnification	0.8x ~ 2.0x	0.8x ~ 2.0x	0.8x ~ 2.0x
	Focus Adjustment	Manual	Manual	Manual

General	Product Dimensions (L x W x H) (mm / in)	Operating Humidity (%)	Max Operating Altitude (meters / feet)	Power Supply
	313 x 236 x 96.4/ 12.4 x 9.3 x 3.8	10 ~ 85	3048 / 10000	10 ~ 240 V AC; 50 ~ 60Hz
	Product Weight (Kilograms / Pounds)	Storage Humidity (%)	Operating Temperature (Celsius / Fahrenheit)	Power Consumption Min / Max (w)
	2.9 / 6.4	10 ~ 85	5 ~ 40 / 41 ~ 104	210 ~ 267
Packaged Dimensions (L x W x H) (mm / in)	Fan Noise (dB)	Storage Temperature (Celsius / Fahrenheit)	Safety and Regulatory	
395 x 337 x 166/ 15.6 x 13.3 x 6.5	27	-10 ~ 60 / 14 ~ 140	CB, CE, EAC, cTUVus, CCC, FCC, UKCA, NOM, PSB, BIS	
Packaged Weight (Kilograms / Pounds)	Audio (W)	Security	Environmental	
4.1 / 9.0	1 x 10	Kensington Security Slot™, PIN Code Lock & Timer	WEEE, EU RoHS, China RoHS, CEL, CECP	

* Product specifications, terms, and offerings are subject to change at any time without notice and may vary between countries. Please check with your local InFocus distributor for more information.

** Actual lamp life may vary based on the environment and projector usage. Conditions that may affect lamp life include temperature, altitude, and air particulate matter etc.

Images shown herein are simulations. ©2024 Maxnerva Technology Services Limited. All rights reserved. InFocus and the InFocus logo are trademarks of Maxnerva Technology Services Limited. All trademarks or the registered trademarks are the property of their respective companies.
INFOCUS_GENESIS III_DS_EN_VER_16072401