



Downloads

Brochures:

[**Newland 3-Stage Quick Assembly Height Adjustable Tables | Sell Sheet \(PDF\)**](#)
959.35KB

[**Product Spec Sheet
\(PDF\)**](#)

[**Tables à hauteur réglable en 3 stades Newland - montage rapide | Fiche de vente \(PDF\)**](#)
960.95KB



Newland

NL60243QHT

NEWLAND | 60"X24" HEIGHT ADJUSTABLE RECTANGULAR TABLE - 2

LEGS

Newland - simple and modular components combining classic design, quality and value to support a wide range of workspace applications. From private offices, open plan, meeting and training spaces, Newland offers functional and practical desking solutions that will stand the test of time.

- quick assembly electric height adjustable bases with leg columns preassembled to telescopic cross bar assembly including electric motors. Unfold leg columns, attach feet and worksurface support to base; fasten assembly to top; plug in connections and start to use
- 3-stage base. range of adjustability with 1" thick top is 22.6" to 48.2"H
- easy to use up-down controller with digital read-out and four memory programmable positions
- may be specified as complete tables or may order tops and bases separately.
- dual motor with 265 lbs. lift capacity.
- anti-collision sensor
- standby power consumption 0.1W. Active power consumption 220W
- operates at 1.2" per second
- operating decibel - 42db
- 8' long power cord
- meets applicable ANSI/BIFMA x5.5 standards
- laminate tops covered by Global's lifetime warranty
Five-year warranty on base components including electrical components and motorized parts
- ETL/CETL and Greenguard Certified
- shipped easy to assemble in 2 cartons
- worksurface is dimensioned to allow 1" gap around perimeter in a nominal footprint

Finish Options:

Laminate finish: Available in all Newland finishes

Base finish: Black or Tungsten



Options

Select Finish
Selection

Noce Grigio NGL



Select Base
Selection

Black



Summary

Options You Have
Selected:

Finish Selection:



Noce Grigio NGL

Base Selection:



Black

- Finish Selection : Noce Grigio NGL
- Base Selection : Black

List Price: **\$1330.00**

Quantity:

Discount (%):

Total Price: **\$1330.00**

Total Weight: 116.0 lb | 52.61 kg

Total Volume: 4.0 ft³ | 0.11 m³

Specifications

Dimensions: 58"W x 23"D x 22.6"-48.2"H

Weight: 116 lbs / 52.62 kg

Volume: 5 ft³ / 0.14 m³
