



Environmental Certificates



[Newland](#)

**NLP404
NEWLAND | "L" SHAPED DESK WITH 3-STAGE HEIGHT
ADJUSTABLE TABLE**

Newland - simple and modular components combining classic design, quality and value to support a wide range of workspace applications. From private offices to open plan, meeting and training spaces, Newland offers functional and practical desking solutions that will stand the test of time.

- rectangular height adjustable table and credenza with pedestal
- thermally fused laminate top, 1" thick
- 2 mm matching edge
- leveling glides included
- 3-stage base - range of adjustability is 22.6" to 48.2"H
- easy to use up-down controller with digital read-out and four memory programmable positions
- dual motor with 265 lbs. lift capacity
- anti-collision sensor
- standby power consumption 0.1W. Active power consumption 220W
- operates at 1.2" per second
- operating decibel - 42db
- 8' long power cord
- meets applicable ANSI/BIFMA x5.5 standards
- laminate tops covered by Global's lifetime warranty
- five-year warranty on base components including electrical components and motorized parts
- ETL/CETL and Greenguard Certified
- worksurface is dimensioned to allow 1" gap around perimeter in a nominal footprint
- designed for quick and easy assembly
- can be assembled for left or right hand applications

Finish Options:

Laminate finish: Available in all Newland finishes



Package Includes:

NL4623HAT: Rectangular top

MLIR30B: 3-stage height adjustable base

NL7224C: Credenza

NL23HBF: Hanging box/file pedestal

Specifications:

Weight: 287.2 lbs / 130.27 kg

Volume: 16.35 ft³ / 0.46 m³

Overall Dimensions

70"W x 72"D x 22.6-48.2"H
