

Made with  
Tech Blue  
magnesium  
alloy

Business Premium

## PORTÉGÉ X40L-M

### Experience The Future of Work with AI-Powered Excellence

Discover the ultimate in AI-powered computing with the new PORTÉGÉ X40L-M. Experience top-notch performance, sleek design, and advanced AI features that take your productivity to new heights.



#### UNRIVALLED PERFORMANCE

The Intel® EVO™ platform, powered by Intel® Core™ Ultra processor



#### YOUR DIGITAL ASSISTANT

AI Copilot streamlines tasks with voice or text commands, enhancing efficiency and device navigation



#### AI-ENHANCED CAMERA

AI features ensure clear visuals with background blurring and eye contact adjustments for an elevated video conferring experience.

Lightest  
14"



Ultrathin  
15.9mm



From  
1.05kg



Intel® Core™  
Ultra processor



Eyesafe® display filters HEV blue light reduces eye strain



dynabook's own BIOS, TPM 2.0 & fingerprint reader for boosted security



Tested to MIL-STD-810H for superior durability



Integrated dual-array microphones with AI Noise Reduction improves call quality



HDMI 2.0, built-in RJ45, USB 3.2 to Type-C ports with Thunderbolt™ 4



4 speaker system enhanced with Dolby Atmos sound technology

# Why Dynabook?

## More than three decades of business innovation

Dynabook is the world’s laptop pioneer, with an unrivaled track record of helping businesses succeed with leading-edge mobile solutions.

## Dynabook controls the entire process

For unmatched quality and reliability, our Tecra and Portégé PCs are designed, engineered and manufactured at Dynabook facilities. The same goes for our image development services

## Quality, reliability, performance. You have our assurance.

Dynabook introduced an extremely rigorous pre-production testing process for our business-class mobile computers that has dramatically lowered annual field failure rates

## Unrivaled Performance & Efficiency

Unleash unparalleled performance and energy efficiency with the Intel® EVO™ platform and Intel® Core™ Ultra processor, paired with Intel® Arc graphics and Intel® AI Boost, ensuring blazing-fast speed, extended battery life, and stunning visuals.

## Sleek Magnesium Alloy Chassis

Experience the perfect blend of lightweight design and robust construction with a Tech Blue magnesium alloy chassis, weighing just 1.05kg and measuring a slim 15.9mm. Its 14-inch ultra-thin bezel display, backlit keyboard, and spacious ClickPad offer both elegance and functionality.

## Comfortable Viewing Experience

The PORTEGÉ X40L-M's Eyesafe® 16:10 IPS 1920x1200 display reduces eye strain with its HEV blue light filter while delivering vibrant colours.

## Serious About Security

With a comprehensive suite of security features, including hardware, firmware, software, and identity protection, the PORTEGÉ X40L-M ensures your data remains secure, making it the perfect choice for sensitive work environments.

Experience the next level of mobile computing with the PORTEGÉ X40L-M – where performance and productivity meets sophistication. Discover the future of computing today.



Contact our Enterprise Consultants



Visit [asia.dynabook.com](http://asia.dynabook.com)

# Specifications



Intel® Core™ Ultra processor

PROCESSOR	Intel® Core™ Ultra 7 processor 165H ( upto 5.0GHz, 16 Cores , 24MB Cache) Intel® Core™ Ultra 7 processor 155H ( upto 4.8GHz, 16 Cores , 24MB Cache) Intel® Core™ Ultra 5 processor 135H ( upto 4.6GHz, 14 Cores , 18MB Cache) Intel® Core™ Ultra 5 processor 125H ( upto 4.5GHz, 14 Cores , 18MB Cache)
OPERATING SYSTEM	Windows 11 Pro
SYSTEM MEMORY	8GB/16GB/32GB OnBoard LPDDR5X RAM 6400 MHz
DISPLAY	14.0 WUXGA 16:10 Full HD (400NIT), resolution 1,920 x 1,200with Eyesafe® Display Certified
GRAPHICS	Intel® Arc™ Graphics
STORAGE*	Choice of 256GB/512GB NVMe™ M.2 PCIe Gen3 or 512GB/1TB/2TB NVMe™ M.2 PCIe Gen4
INPUT DEVICE	Large Glass feel ClickPad™ with multi gesture support, Frameless Full-Size Backlit Spill Resistant Keyboard
COMMUNICATIONS	Intel® Wi-Fi 6E Dual Band Wireless LAN (802.11ax), Bluetooth® 5.2 Intel® Ethernet Connection i219 (10/100/1000Mbps)
BUILT-IN CAMERA & MICROPHONE	HD-camera or HD plus IR- user-facing camera for Windows Hello (face authentication) and AI features to enhance privacy and video quality. 360-degree dual microphones including AI features for Noise Reduction
SOUND SYSTEM	4 speaker system® supported by Dolby Atmos® technology
INTERFACES	2 x USB Type-C ports with Thunderbolt™ 4 which supports data transfer, power delivery and display port, 2x USB 3.2 (1 x supporting power off and charge), 1x Gigabit LAN, 1 x HDMI2.1, 1x external headphone (stereo/micro-phone combo socket), 1x microSD™ card slot
BATTERY TYPE	4-cell, 65Whr Lithium-Ion Polymer (not user replaceable) Quick charge technology (30 minutes charge = 4 hours of battery)
POWER RATING	65W USB Type-C AC Adaptor
SECURITY FEATURES	Fingerprint Reader (integrated in the power button), IR camera with face authentication (Optional), Advanced Encryption (TPM 2.0), slot for Secure Cable Lock, Webcam Shutter Slider, Windows Hello support, Intel® Authenticate support, user password, supervisor password, SSD password on request, Dynabook BIOS, Microsoft Secured-Core PC Certified
PROTECTION FEATURES	Magnesium Alloy Chassis, designed to pass MIL-STD-810H military standards
PHYSICAL DIMENSIONS	312.4 x 224 x 15.9mm
WEIGHT	Starting from 1.05kg
WARRANTY*	3-year International Limited Warranty (Carry-in) 1-year Battery Limited Warranty
ENVIRONMENTAL SPECIFICATIONS	EPEAT® Gold Registered, ENERGY STAR 8.0, RoHS compliant

\* Actual product features and specifications depend on model and local availability. For more information, please visit <http://asia.dynabook.com>  
+ Dynabook's standard limited warranty terms and limitations apply. For more details, please visit <https://asia.dynabook.com/warrantylaptop/>

### Optional Accessories

- PS0120LA1PRP - Dynabook Thunderbolt 4 Dock
- PS0001UA1PRP - Dynabook USB-C to HDMI/VGA/LAN/USB3.0 Travel adapter
- PA5356E-2PRP - Dynabook USB-C Dock
- PA5352E-1AC3 - Dynabook USB-C AC Adapter 65W