

## PERFORMANCE

### Processor

Intel® N100 (4C / 4T, Max Turbo up to 3.4GHz, 6MB)

### Graphics

Integrated Intel® UHD Graphics

### Chipset

Intel® SoC Platform

### Memory<sup>[1]</sup>

8GB Soldered LPDDR5-4800

### Memory Slots

Memory soldered to systemboard, no slots

### Max Memory

8GB soldered memory, not upgradable

### Storage

64GB eMMC 5.1

### Storage Support<sup>[2]</sup>

64GB eMMC 5.1 on systemboard

### Storage Slot

eMMC on systemboard, no slots

### Card Reader

No card reader

### Audio Chip

High Definition (HD) Audio, Realtek® 5682I-VS codec

### Speakers

Stereo speakers, 2W x2, optimized with Waves MaxxAudio®

### Camera

Front HD 720p with Privacy Shutter + Rear 5.0MP

### Microphone

Mono (Front) + Mono (Rear)

### Battery

Integrated 47Wh

### Power Adapter

65W USB-C® (2-pin)

## DESIGN

### Display<sup>[3]</sup>

11.6" HD (1366x768) IPS 250nits Glossy / Anti-fingerprint 60Hz, 50% NTSC, Touch

### Touchscreen

Direct Bonding, 10-point Multi-touch

### Keyboard

Non-backlit, English

### Touchpad

Buttonless Mylar® surface multi-touch touchpad, 60.5 x 104 mm (2.38 x 4.09 inches)

### Case Color

Grey

### Surface Treatment

Texture

### Case Material

PC-ABS + 15% Talc (Top), PC-ABS + 15% Talc (Bottom)

### Pen

Pen Upgradable (Purchase Separately)

### Dimensions (WxDxH)<sup>[4]</sup>

289.6 x 202.4 x 20.4 mm (11.4 x 7.97 x 0.80 inches)

### Weight<sup>[5]</sup>

Around 1.33 kg (2.93 lbs)

## SOFTWARE

### Operating System

ChromeOS

### Bundled Software

None

## CONNECTIVITY

### Ethernet

No Onboard Ethernet

### WLAN + Bluetooth®

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

### WWAN

Non-WWAN

### SIM Card

None

### Standard Ports

- 1x HDMI® 1.4
- 1x Headphone / microphone combo jack (3.5mm)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with PD and DisplayPort™

### Docking

Various docking solutions supported via USB-C®.

For more compatible docking solutions, please visit .

[Docking for Lenovo® 500e Chromebook Gen 4s](#)

## SECURITY & PRIVACY

### Security Chip

Google Security Chip H1

### Fingerprint Reader

None

### Physical Locks

Kensington® NanoSaver® lock Slot

### Other Security

Camera privacy shutter

## SERVICE

### Base Warranty

1-year, Mail-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories<sup>[6]</sup>

None

## CERTIFICATIONS

### Green Certifications<sup>[7]</sup>

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant
- TCO Certified 9.0

### Other Certifications

ASTM F963 test passed

### Mil-Spec Test

Work in progress

## MODEL

TopSeller : Yes

Announce Date : 2024-11-04

EAN / UPC / JAN : 198154990732

End of Support : N/A



Product image is a sample, it may not match the real color of this model

Note:

[1] Installed memory is actually LPDDR5-6400 but run as LPDDR5-4800 due to platform limitation.

[2] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[3] IPS (in-plane switching) technology may refer to IPS,.....

· Lenovo reserves the right to change specifications without notice.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to

<https://psref.lenovo.com/Detail/2675?M=83L40001US>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



## Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38566)
BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0U55751)
GOOD	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0Q81869)

For a full list of Accidental Damage Protection services, please visit: <https://smartfind.lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference