

CHERRY STREAM MOUSE COMFORT

The silent click mouse with ergonomic shape and wireless freedom.



Models may vary from the image shown

With the STREAM MOUSE COMFORT you experience working comfort at the highest level - with the innovative and ergonomic mouse technology, user-friendly design and wireless freedom merge into a faithful companion that lives up to your needs!

Dreamteam features: Ergonomics and wireless freedom

The cordless right-hand mouse is the optimal solution for comfortable and efficient working. With state-of-the-art 2.4 GHz wireless technology and a generous range of up to 10 m, you can remain flexible all the time in your workplace.

The ergonomic wireless mouse is specifically designed for right-handed people with medium to large hands. Every aspect of its design aims to promote a natural and relaxed hand posture. The high-quality metal scroll wheel not only lends an elegant appearance, but also ensures a correspondingly high-quality tactile experience. The handy thumb rest with the attractive Voronoi pattern offers a pleasant feel and gives the mouse a touch of elegance. Your thumb is also very comfortable and relieved. The generous sliding surfaces on the underside significantly reduce friction, which makes the mouse extremely smooth and easy to navigate over all surfaces.

CHERRY 

Sophisticated technology meets comfort while working: Relaxed and efficient throughout the working day!

With the CHERRY STREAM MOUSE COMFORT you experience absolute precision with every movement – with a resolution of up to 4000 dpi, the large computer mouse enables exact control. Thanks to the innovative and 4-step adjustable dpi switch, you can adjust the sensitivity to your individual requirements in no time at all.

Thanks to the clever dongle holder on the back, the stylish yet minimalistic wireless mouse makes searching for the receiver a thing of the past. Thanks to the battery life of up to 16 months, the optical mouse guarantees particularly long-lasting use. A flashing LED on the top signals in good time when a battery change is required, while the on/off switch helps extend the battery life. This means you can stay in control of your workflow without worrying about unexpected interruptions.

The perfect balance: Practical benefits and individuality

The front and back buttons on the side are extremely useful in everyday use. With a single click, you can easily switch between digital content or actions for intuitive and smooth operation. These features make it easier to focus on the essentials. In addition, the free CHERRY KEYS software offers the possibility to adapt the mouse settings according to individual needs and thus offers additional advantages for an optimal user experience.

The STREAM MOUSE COMFORT seamlessly combines comfort, design and efficiency. It is the ideal choice for demanding users who are looking for a companion which combines ergonomics, design and efficiency.

FUNCTION AND PERFORMANCE

- Ergonomic 6-button mouse for right-handed users
- Undisturbed working with whisper-quiet mouse buttons
- Fatigue-free working thanks to rubberized thumb pad with modern Voronoi pattern

- High-quality metal mouse wheel ensures durability, a pleasant feel and precise scrolling
- Interference-free 2.4 GHz wireless technology with a range of up to 10 meters
- Highly precise sensor with resolution adjustable in four stages up to 4000 dpi
- AES-128 encryption
- Integrated battery status display and up to 16 months battery life
- Generous glide pads for effortless navigation on all surfaces
- Nano USB receiver and simple plug & play start up
- GS approval

TECHNICAL DATA

Weight main product:	5 oz
Dimensions product without packaging:	4,99 in x 3,35 in x 1,96 in
Storage temperature:	-4 °F - 149 °F
Working temperature:	32 °F - 122 °F
Max. Current consumption (mA)	16 mA
Mouse:	
Product approvals:	<ul style="list-style-type: none"> • CE • China RoHS • EU RoHS • GS • FCC • Windows Hardware Compatibility • REACH • UKCA
System Requirements-Hardware:	USB-A

Operating system:	<ul style="list-style-type: none"> • Windows 7 • Windows 8 • Windows 10 • Windows 11
Scope of delivery:	<ul style="list-style-type: none"> • 1 x AA battery • Manual • Mouse • Nano-USB-Receiver
Switch type:	silent
Number of keys:	6
Thumb buttons:	yes
Max. resolution (dpi):	4.000 dpi
dpi switch:	yes
dpi levels:	4
Software support:	CHERRY KEYS
USB dongle:	yes
2.4 Ghz wireless connection:	yes
Encryption in wireless mode:	yes
Wireless range:	33 ft
Connection via Bluetooth:	no
Number of batteries:	1
Battery type:	Alkaline
Battery design:	AA
Battery rechargeable:	no
Battery replaceable:	yes
Model number:	JD-855M
Protection class:	Standard
Warranty:	2 years warranty
Number of side buttons:	2

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

EAN / SKU / UPC	Protection class	Color
4025112110603 JW-8550-2 840183607524	Standard	black
4025112110597 JW-8550-0 840183607517	Standard	white-grey

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.