

IDEAL

4001



SHREDDER

Workhorse with a Large 16" feed opening. Heavy duty cabinet with caster to be mobile. Double protection from overheating



TECHNICAL DATA

Bin Size	44 gallons
Feed Opening	16"
Power Supply	115V
Max Horsepower	1
Dimensions (w x d x h)	25.25 x 23.25 x 37.2"
Shipping Weight	242 lbs

	Particle Size	Sheet Capacity*	Shred Capabilities
 4001 P4 CROSS-CUT IDEDSH0324H	$\frac{3}{16} \times 1 \frac{1}{2}$ "	25-28*	Paper, Staples, Paper Clips, Credit Cards, CDs / DVDs
 4001 P5 CROSS-CUT IDEDSH0323H	$\frac{3}{32} \times \frac{5}{8}$ "	13-16*	Paper, Staples, Paper Clips, Credit Cards, CDs / DVDs

*Certified using 8.5 x 11" 20-lb bond paper and recommended power supply.

Shredder Bags

IDEACO901H

Shredder Oil

IDEACCED21/4H



Sheet Capacity is based on 70 gsm paper, and are normally only achievable in ideal situations, so heavier duty paper will shred less sheets. In many cases the capacities quoted are theoretical as conditions vary and are dependent on operator usage, age and condition of machines, how regularly cutters are oiled, type and quality of paper etc.

SUPERIOR GERMAN QUALITY



1 PATENTED SAFETY SHIELD

Electronically controlled transparent safety shield keeps fingers, ties, and other objects away from the cutting shafts. The shield protects the operator from stray splinters of plastic.

2 ENVIRONMENTALLY FRIENDLY BIN

Wooden cabinet on casters holds durable, lightweight shred bin that can be used with or without disposable bags.

3 CAPACITY INDICATOR

The ECC (Electronic Capacity Control) indicator shows how hard the shredder is working and helps prevent paper jams.

4 EASY SWITCH

Multifunction control element uses optical signals to indicate operational status and functions as an emergency stop switch.

IDEAL

800-826-0161
help@simplyideal.net
simplyideal.net



LIMITED
WARRANTY



MADE IN
GERMANY



EASY
SWITCH



ZERO
ENERGY



ECO
FRIENDLY



SAFETY
PROTECTION SYSTEM



ELECTRONIC CAPACITY
CONTROL