



Extreme performance. Infinite possibilities

Unlock your potential with the most powerful Z AI workstation. The Z8 Fury delivers performance with up to 60 cores in a single CPU to also unleash the power of 4 high-end GPUs. Now you can breeze through even the most complex machine learning and data science projects, virtual production, and VFX.



Relentless power. Extraordinary expandability

Tackle the most complex workflows with up to a 60 core Intel® Xeon® W CPU[1], up to 4 high-end GPUs, 2TB DDR5 RAM, 120TB storage and 2,250W of power.[2] Easily expand as work evolves with tool-less access, 8 PCIe slots, and 4 front accessible NVMe bays[3].

Engineered to stay cool and quiet

Push desktop workstation performance without disruptive noise. Smart fan control keeps the system whisper-quiet by tuning fan speeds in real-time using over 20 temperature sensors. Precisely placed vents and ducts streamline airflow and heat removal.

Your AI powerhouse, in-house.

Accelerate AI development and inferencing with the Z8 Fury AI workstation with up to 4 NVIDIA RTX™ 6000 Ada Generation GPUs[4] delivering up to 5,828 AI TOPS for advanced AI. Process proprietary data securely on a local workstation for fast insights.

Featuring

Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

Intel® Xeon® W processor

Get optimized performance whether your professional application utilizes high core count or high frequency with the Intel® Xeon® W processor. [1]

Security is your top priority

The HP Wolf Pro Security Edition provides preconfigured enterprise-level PC protection for small and medium sized businesses.

Professional Grade Graphics

Tackle complex renderings, simulations and datasets with professional grade graphics.

Specifications

Form factor	Tower
Operating system	Windows 11 Pro ^[1]
Processor family	Intel® Xeon® W processor
Processor	Intel® Xeon® W5-3535X (up to 4.8 GHz with Intel® Turbo Boost Technology, 52.5 MB L3 cache, 20 cores, 40 threads) [6,7]
Chipset	Intel® W790
Memory	32 GB DDR5-4800 MT/s (2 x 16 GB)
Memory Slots	16 DIMM
Internal Storage	1 TB HP Z Turbo Drive PCIe® Gen4 TLC M.2 SSD
Internal drive bays	Six PCIe® M.2 SSD; Six 3.5" HDD
External drive bays	Four NVMe™ M.2 SSD; Two 3.5" HDD; Two 9.5 mm ODD
Graphics	Discrete
Graphics (discrete)	NVIDIA RTX™ A1000 (8 GB GDDR6 dedicated)
Compatible displays	All HP Z Displays and HP DreamColor Displays are supported. For more information see http://www.hp.com/go/zdisplays
Audio	Realtek ALC3205-CG
Minimum dimensions (W x D x H)	21.59 x 55.12 x 44.45 cm
Weight	Starting at 22 kg (<i>Exact weights depend upon configuration (System weight only)</i>)
Keyboard	HP 125 Wired Keyboard
Pointing device	HP Wired 320M Mouse
Ports	4 USB Type-A 5Gbps signaling rate; 1 headphone/microphone combo ^[29] 1 PCIe 3 x8; 2 PCIe 5 x16; 1 PCIe 5 x4; 2 PCIe 4 x16; 2 PCIe 4 x4; 2 PCIe 4 x8
Expansion slots	(<i>Rear bulkhead access can be achieved through all slots but 2 PCIe 4 x8 are internal access only for M.2.</i>)
Package dimensions (W x D x H)	33.2 x 73.4 x 63.6 cm
Package weight	Starting at 27.95 kg
Power	2250 W aggregate internal power supply, up to 90% efficiency, active PFC; 1450 W internal power supply, up to 90% efficiency, active PFC; 1450 W redundant internal power supply, up to 90% efficiency, active PFC; 1125 W internal power supply, up to 90% efficiency, active PFC; 1125 W redundant internal power supply, up to 90% efficiency, active PFC
Energy star certified	ENERGY STAR® certified
Management features	HP Driver Packs; HP System Software Manager (download); HP BIOS Configuration Utility (download); HP Smart Support
Sustainable impact specifications	Low Halogen; 40% post-consumer recycled plastic; 25% ITC-derived closed loop plastic; Bulk packaging available; External power supply 90% efficiency; Plastic cushion inserts contain 80% recycled content; Ocean-bound plastic in system fan; 10% post-industrial recycled metal
Security management	Full volume encryption; HP Secure Erase; Kensington lock slot; Secure authentication; TPM 2.0 certified; HP BIOSphere; HP Sure Run; HP Sure Click; HP Sure Sense; HP Sure Admin; HP Platform Certificate; HP Sure Start; HP Sure Recover; Self-Encrypted Drives ^[20,21,22,23,24,25,26,27]
Software included	HP PC Hardware Diagnostics UEFI; HP Performance Advisor; HP Support Assistant; HP PC Hardware Diagnostics Windows; HP Image Assistant; HP Manageability Integration Kit; HP Anyware; HP Services Scan; HP Data Science Stack Manager ^[17,18,19,32,33]
UPC number	(ABA) 198828651105; (ABC) 198828651112

Top Recommended Displays, Accessories and Services

Speakerphones

Poly Sync 20+ USB-C Speakerphone	772D0AA
Poly Sync 20 USB-C Speakerphone	7F0J7AA
Poly Sync 10 USB-A USB-C Speakerphone	772C3AA

Wireless Headset

Poly Voyager Surround 80 UC USB-C Headset +USB-C/A Adapter	8G7T9AA
Poly Voyager Focus 2 USB-C-C Headset +USB-C/A Adapter	9T9J3AA

Wired Headset

Poly Blackwire 8225 Stereo USB-C Headset +USB-C/A Adapter	8X223AA
---	---------

Messaging Footnotes

[1] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[2] Optional, configurable features. Configuration for 120TB requires separate additional purchase. For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 35GB is reserved for system recovery software.

[3] Optional, configurable features. Two front accessible NVMe bays require a 5.25 bay carrier.

[4] Graphics are sold separately or as an optional feature.

Technical Specifications Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[17] HP Performance Advisor Software - HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one—and every day after. Learn more or download at: <https://www8.hp.com/us/en/workstations/performance-advisor.html>.

[18] HP Support Assistant requires Windows and Internet access.

[19] HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html>.

[20] HP Sure Click requires Windows 11 Pro or Enterprise. See https://bit.ly/2PrLT6A_SureClick for complete details.

[21] HP Sure Start Gen7 is available on select HP PCs and Workstations. See product specifications for availability.

[22] HP Sure Recover Gen4 is available on select HP PCs and requires an open network connection. You must back up important files, data, photos, videos, etc. before using HP Sure Recover to avoid loss of data.

[23] HP Sure Sense requires Windows 11 Pro or Enterprise and supports Microsoft Internet Explorer, Google Chrome™, and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

[24] HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.

[25] HP Sure Admin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.

[26] HP Secure Erase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88.

[27] HP BIOSphere Gen6 features may vary depending on the platform and configurations.

[29] Front entry contain: 1 headset connector; 4 SuperSpeed USB Type-A 5Gbps signaling rate. Front Entry and Front Premium offer Battery Charging 1.2 through one of the USB Type-A ports.

[32] HP Services Scan is provided with Windows Update on select products and will check entitlement on each hardware device to determine if an HP TechPulse-enabled service has been purchased, and will download applicable software automatically. HP TechPulse is a telemetry and analytics platform that provides critical data around devices and applications. For full system requirements or to disable this feature, please visit <http://www.hpdaas.com/requirements>. Not applicable in China.

[33] HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one—and every day after. Learn more or download at: <https://www8.hp.com/us-en/workstations/performance-advisor.html>.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA is trademark and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® is registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

