

# PORTÉGÉ® X40-M

PNM1BU-OEM00U

## ENTER A NEW ERA OF AI-POWERED PRODUCTIVITY

Designed for today's elite professionals, this all-new, premium, aluminum alloy 14-inch laptop is equipped with powerful hardware, a larger 16:10 screen, and productivity-boosting AI.



### PREMIUM PERFORMANCE

Delivering unprecedented speed and efficiency, the Portégé X40 features Intel® Core™ Ultra processors with a Neural Processing Unit and Intel® Arc™ graphics for accelerated performance and enhanced battery life.



### LONGER-LASTING BATTERY LIFE

The larger, AI-optimized 60Wh battery provides extended unplugged productivity. Sleep & Charge technology allows for charging of USB devices even when the laptop is off.



### CONNECT AT SUPERHERO SPEEDS

Stay connected with Wi-Fi 6E and a comprehensive selection of ports, including HDMI, Thunderbolt 4, USB Type-A, and a microSD card slot, ensuring you have all the connections you need.



### A STUNNING VISUAL EXPERIENCE

Experience the vibrant new 14-inch WUXGA display with a 16:10 aspect ratio, providing crisp and clear visuals and more vertical work space for enhanced multitasking and productivity.



### MASTERING THE HYBRID WORKPLACE

The Portégé X40-M's 5MP AI-enhanced webcam, dual microphones, and upgraded audio system with DTS processing make it perfect for clear, productive video conferencing.



### SUPERCHARGE YOUR PRODUCTIVITY WITH AI

Microsoft Copilot, accessible via a dedicated key, streamlines tasks, like launching apps and adjusting system settings, through voice or text commands, enhancing efficiency and device navigation.



## Laptops That Defend Against Cyber Threats



Dynabook's Windows 11 Secured-core PC laptops offer advanced security by integrating robust hardware and software defenses into their core components. These laptops provide a fortified shield against sophisticated cyber threats, employing specialized hardware protections and firmware safeguards. They ensure unparalleled security from boot-up, defending against malware and firmware attacks to safeguard critical data and uphold the integrity of business operations.



## PRODUCT SPECIFICATIONS

### Operating System\*

- Windows 11 Pro

### Processor\*

- Intel® Core™ Ultra 5 (Series 1) 125U

### Memory\*

- 16GB of DDR5 (Field upgradable)

### Graphics

- Intel® Arc™ Graphics

### Display\*

- 14.0" WUXGA (1920x1200)

### Storage\*

- 512GB PCIe NVMe SSD

### Communications

- Intel® Ethernet Connection i219
- Intel® Wi-Fi 6E AX211, 6 GHz, 802.11ax
- Bluetooth™

### Camera w/ Privacy Shutter\*

- 5MP Webcam

### Audio

- Stereo Speakers w/ DTS Processing
- Dual-microphone array

### Ports

- HDMI®
- Two (2) USB-C/Thunderbolt 4 ports
- Two (2) USB 3.2 Gen 1 Type-A ports
  - One supporting USB Sleep & Charge
- RJ-45 Ethernet LAN port
- Headset jack (Microphone / Headphone combo port)
- microSD™ card slot

### Security\*

- Microsoft Secured-core PC
- Trusted Platform Module 2.0
- Fingerprint Reader
- Security Lock Slot

### Input Devices

- Premium Raised-tile, Spill-resistant, Backlit Keyboard
- ClickPad Pointing Device

### Battery

- 60 Wh Li-Polymer Battery

### Physical Description

- Metallic Dark Blue
- Aluminum Alloy Chassis
- Designed to MIL-STD-810H standards
- 313.2 x 221.75 x 18.6 millimeters
- Starting at 1.44 kilograms (3.17 pounds)

### Regulatory / Environmental Specifications

- EPEAT® Rated
- ENERGY STAR® Qualified
- RoHS Compatible

### Warranty\*

- 3-Year Standard Limited Warranty

### Optional Accessories

- PS0120UAIPRP – Dynabook Thunderbolt™ 4 Dock
- PA5356U-IPRP – Dynabook USB-C® Dock
- PS0001UAIPRP – USB-C® to HDMI® / VGA / LAN / USB 3.0 Adapter with Power Delivery (PD) Charging
- PS0089UAIPRP – USB-C® to VGA / LAN Adapter with Power Delivery (PD) Charging
- PA5270U-IPRP – USB-C® to VGA Adapter with Power Delivery (PD) Charging
- PA5352U-1ACA – 65W USB-C® AC Adapter (5V / 9V / 15V / 20V)



### +Care Service® Warranty with On-Site

Portégé laptops are backed by one of the best standard warranties in the business. For even greater peace of mind, Dynabook's industry-leading +Care Service® Warranty with On-site can be added for worry-free reliability with up to four years of coverage. With comprehensive warranty coverage and access to a vast service and support network, Dynabook helps businesses minimize downtime, reduce IT costs, and ensure uninterrupted productivity.

\* Based on Configuration

\*\* Visit <http://us.dynabook.com/info> for a complete list of all product legal footnotes