# **5G NR M2M Gateway**

Industrial IoT 5G NR M2M gateway for Wi-Fi and RS-232/RS-485 with digital and analog I/O  $\,$ 



**DWM-3010** 

- Wireless 802.11ac/n/g/b/a
- 5G NR/ LTE (sub-6 GHz/LTE Cat.20)
- WPA/WPA2/WPA-PSK/WPA2-PSK/802.1x encryption
- Advanced VPN: IPSec/OpenVPN/L2TP/PPTP/GRE
- Remote management with D-ECS (D-Link Edge Cloud Solution)
- Connect up to 50 devices to your Wi-Fi network
- Rugged design for wide-temperature operation













#### **High-Speed 5G NR Internet**

5G NR speeds up to 1 Gbps for lightning-fast downloads, lower latency and reduced congestion



#### Up to 50 Devices

Connect up to 50 Wi-Fi devices in device-dense working environments



#### **Dual-Band AC1200**

866 Mbps (5 GHz) + 300 Mbps (2.4 GHz) dual-band connectivity



#### **Dual SIM Slots**

Dual SIM slots allows redundant connectivity to ensure uninterrupted operatoin



#### **Gigabit Ethernet Ports**

High-speed Gigabit connections for wired devices



### Supports IPv6

Future-proof and compatible with the next generation of Internet standards

	1 x 10/100/1000 Ethernet WAN/LAN Ports, 2 x 10/100/1000 Ethernet LAN port	
Device Interfaces  LED	1 x 10/100/1000 Ethernet WAN/LAN Ports, 2 x 10/100/1000 Ethernet LAN port	
LED	The state of the s	
	Serial: Blue	
	Fast Flashing: Data packets transferred via serial port	
	Status: Blue OFF: Host disconnected	
	Fast Flashing: WAN Ethernet or LTE connection established, obtaining IP	
	PWR: Blue	
	OFF: Device is powered OFF or in standby mode	
	Steady ON: Device is powered ON	
	Flashing once per second: Device is at "Delay OFF" mode	
	Fast Flashing: Firmware is upgrading or device is in recovery mode Wi-Fi 2.4 GHz: Blue	
	OFF: 2.4 GHz Wi-Fi is disabled	
	Steady ON: 2.4 GHz Wi-Fi is enabled	
	Fast Flashing: Data is being transmitted/received via 2.4 GHz Wi-Fi	
	Wi-Fi 5 GHz: Blue	
	OFF: 5 GHz Wi-Fi is disabled	
	Steady ON: 5 GHz Wi-Fi is enabled Fast Flashing: Data is being transmitted/received via 5 GHz Wi-Fi	
	5G NR & 4G LTE Cellular: Blue	
	5G LED Steady ON: 5G NR enabled	
	4G LED Steady ON: 4G LTE enabled	
	SIM-A LED Steady ON: SIM-A is inserted for 3G/4G/5G connection	
	SIM-A LED OFF: SIM-A is not inserted or not in use	
	SIM-B LED Steady ON: SIM-B is inserted for 3G/4G/5G connection	
	SIM-B LED OFF: SIM-B is not inserted or not in use	
	SIGNAL LED Steady ON: 3G/4G/5G signal strength is at high level (>60%) SIGNAL LED Flashing: 3G/4G/5G signal strength is at low level (<60%)	
	WAN/LAN1 - 3: Green	
	Steady ON: Ethernet LAN or WAN connection is established	
	Flash: data packets are transferring	
Power Supply	DC 9V / 2.7A ~ 36V / 0.7A	
Ethernet	1 x 10/100/1000 Ethernet WAN/LAN port 2 x 10/100/1000 Ethernet LAN ports	
SMA Antenna	4 x Female type jack for 5G NR/LTE 2 x Male type jack for Wi-Fi	
Communication Bus	1 x RS-232 (Tx/Rx)	
	1 x RS-485 (D+(B), D-(A))	
Digital I/O	2 x DI (Isolated, "Logic 0": 0~2V, "Logic 1": 5V ~ 30V)	
	2 x DO (Isolated, Non-Relayed Output, 24V/300 mA for each port)	
Analog I/O	$2 \times AI (0\sim10V, 12 \text{ bit ADC, sampling rate up to } 125 \text{ KHz})$	
5G NR/4G LTE Modem		
5G NR	5G NR, Sub-6 GHz, 100 MHz (BW)	
4G LTE	LTE support up to Cat.20	
Operating Bands	5G NR Refarmed Sub-6: n1, n2, n3, n5, n7, n8, n12, n20, n28, n41, n66, n71	
	New Sub-6: n77, n78, n79	0 000 000 000 000 000
	LTE FDD: B1, B2, B3, B4, B5, B7, B8, B12, B13, B14, B17, B18, B19, B20, B25, B26, B28 LTE TDD: B34, B38, B39, B40, B41, B42, B46, B48	s, b29, b30, b32, b66, B/T
	WCDMA/HSPA+: B1, B2, B3/9, B4, B5/6/19, B8	
Maximum Callular		
Maximum Cellular	5G NR: 900 Mbps (DL, Ethernet) / 150 Mbps (UL, Ethernet)	
Data Throughput		
Interface	USB 3.0 miniPCle	
Dual SIM Slots	3V/1.8V 6-pin standard (3FF Micro SIM)	



<b>Software Specificat</b>	ions	/ DWM-3010 5G NR M2M Gateway
Standards	IEEE 802.11 ac/n/g/b/a, 2.4 GHz/5 GHz	
Wi-Fi Data Rates	Up to 866 Mbps with 802.11ac clients	
	Up to 300 Mbps with 802.11n clients	
Web UI		
Web Management	English (default)	
LAN Default IP Address	192.168.0.1	
Default Subnet Mask	255.255.255.0	
Wireless WAN		
5G NR/4G LTE	5G NR/4G LTE modem to connect to Internet	
WAN Control		
WAN	Cellular & Config Ether-WAN; Failover	
Cellular	3GPP, 5G NR/4G LTE, IPv4/v6	
Ether-WAN	Dynamic IP, Static IP, PPPoP, PPTP, L2TP	
Network Monitor	ICMP/DNS Query	
Dual SIM slots for CELL	SIM A, SIM B failover	
Wi-Fi		
Standard	802.11 ac/n/g/b	
Mode	AP router, WDS, WDS hybrid modes	
Functions	Multi-SSID, WMM	
Security	WEP, WPA, WPA2, WPA-PSK, WPA2-PSK, 802.1x	
Captive Portal	External web portal	
2.4 GHz SSID	DWM-3010-XXXX (XXXX is last four random digits based on MAC address)	
5 GHz SSID	DWM-3010-5G-XXXX (XXXX is last four random digits based on MAC address)	
Auto Channel Scan	Enabled	
Pre-shared Key	Random 8-character key (alphanumeric case sensitive)	
Protocol		
LAN & VLAN	DHCP server/relay, port/tag based VLAN	
IPv6	Dual stack, IPv4/IPv6	
Port Forwarding	NAT 1-1, 1-many, transversal, DMZ, Virtual Server & Computer, VPN passthrough	
Routing	Static, Dynamic - RIP1/RIP2, OSPF, BGP	
QoS	Policy-based, 802.1q and TOS for priority queues	
Service		
Cellular Toolkit	Data usage, SMS, SIM PIN, USSD, Network Scan	
Event Handling	User-defined mgmt/notify event; action & trigger by SMS, mail, syslog, SNMP trap, N	Modbus, I/O
D-ECS (D-Link Edge Cloud	Remote Management of Devices, Zero Touch Deployment, Device GPS Location	



Solution)

Software Specifi	ications / DWM-3010 5G NR M2M Gateway
Security	
VPN Tunneling	IPSec, OpenVPN, PPTP, L2TP, GRE
Scenario	Site/host to site/host; dynamic VPN
VPN Capability	IPSec up to 16 tunnels
Firewall	SPI firewall iwth stealth mode, IPS
Access Control	Packet filter, URL blocking, MAC filter
Field Com	
Virtual COM	RFC2217, TCP client, TCP server, UDP
Modbus	Gateway for Modbus TCP/RTU/ASCII Master/Slave Access; Slave for Device Status/Information Access
Administration	
Configuration	Web UI, CLI, Command Script, D-ECS (D-Link Edge Cloud Solution)
Management	SNMPv3 Std. & D-ECS (D-Link Edge Cloud Solution)
System	Upgrade, backup & restore, reboot & reset, Syslog

# **Electrical Characteristics**

Power

Diagnostics

Power Input DC 9V/2A - 36V/0.7A +/- 5%

Packet analyzer, diagnostic tools

Environmental Requirements		
Temperature		
Operating Temp./Humidity	Temperature: -30°C ~ 60°C, Humidity: 10%~95% non-condensing	
Storage Temp.	Temperature: -40°C ~ 85°C, Humidity: 0%~95% non-condensing	
RoHS	RoHS compliant	

## **ID/Mechanical**





Dimensions	62 x 125 x 160 mm (w/o mounting kit)
Weight	1.15 kg

## **Order Information**

DWM-3010 5G NR M2M Gateway