

ThinkPad X9-14 Gen 1

PSREF

Product Specifications Reference

PERFORMANCE

Processor

Intel® Core™ Ultra 5 226V, 8C (4P + 4LPE) / 8T, Max Turbo up to 4.5GHz, 8MB

AI PC Category

Copilot+ PC

NPU

Integrated Intel® AI Boost, up to 40 TOPS

Graphics

Integrated Intel® Arc™ Graphics 130V

Chipset

Intel® SoC Platform

Memory

16GB Soldered LPDDR5x-8533, MoP Memory

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

16GB soldered memory, not upgradable

Storage

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Support^[1]

One drive, up to 2TB M.2 2242 SSD

Storage Slot

One M.2 2242 PCIe® 4.0 x4 slot

Card Reader

None

Audio Chip

High Definition (HD) Audio, Cirrus Logic® CS42L43

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Camera

FHD 1080p + IR Discrete with E-shutter

Microphone

2x, Array

Battery

Integrated 55Wh

Power Adapter

65W USB-C® Slim GaN (2-pin)

DESIGN

Display

14" WUXGA (1920x1200) OLED 400nits Anti-glare, 100% DCI-P3, 60Hz, DisplayHDR™ True Black 500, Dolby Vision®

Touchscreen

None

Keyboard

Backlit, French

Touchpad

Buttonless glass surface multi-touch Haptic Touchpad, supports Precision TouchPad (PTP), 80 x 130 mm (3.15 x 5.12 inches)

Case Color

Grey

Case Material

Aluminium (Top), Aluminium (Bottom)

Pen

Pen Not Supported

Dimensions (WxDxH)^[2]

311.8 x 212.3 x 6.7 - 17.18 mm (12.28 x 8.36 x 0.26 - 0.68 inches)

Weight^[3]

Starting at 1.21 kg (2.66 lbs)

SOFTWARE

Operating System

Windows® 11 Pro, French / Canadian French / English

Bundled Software

Intel® Connectivity Performance Suite

CONNECTIVITY

Ethernet^[4]

No Onboard Ethernet

WLAN + Bluetooth^[5]

Intel® Wi-Fi® 7 BE201, 802.11be 2x2 + BT5.4

WWAN

Non-WWAN

SIM Card

None

NFC

None

Standard Ports

- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)

None

Docking

Various docking solutions supported via Thunderbolt™ / USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® X9-14 Gen 1](#)

SECURITY & PRIVACY

Smart Card Reader

None

Security Chip

Discrete TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Other Security

- E-shutter
- IR camera for Windows® Hello (facial recognition)
- Ultrasonic Human Presence Detection (WUXGA models)

MANAGEABILITY

System Management

Non-vPro®

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES

Bundled Accessories^[6]

None

CERTIFICATIONS

Green Certifications^[7]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 10.0

Other Certifications

- Intel® Evo™ Platform
- Eyesafe® Certified 2.0

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller : Yes **Announce Date** : 2025-01-17

EAN / UPC / JAN : 198156422088 **End of Support** : 2031-08-21

Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] The system dimensions may vary depending on configurations.

[3] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[4] Ethernet support via optional Lenovo USB-C to Ethernet Adapter.

[5] 6GHz Wi-Fi 7 operation is subject to the regulation.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/2705?M=21QA0000CA>

Premier Support - A direct 24x7x365 line to our most elite technicians.

Advanced technical support, 24x7x365, in more than 100 markets

Technical Account Managers for proactive relationship and escalation management

Comprehensive hardware & OEM software support

Priority on service delivery and repair parts

Single point of contact for simplified end-to-end case management

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

ThinkPad Universal USB-C Dock

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39383)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36154)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A14086)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

PSREF
Product Specifications
Reference