





- Incredible True 4K UHD resolution and laser technology HDR and HLG compatible
- Lights on viewing bright 3500 lumens Perfect for big screen home entertainment and immersive gaming
- Small form factor for easy installation 1.6x zoom, 360-degree and portrait projection
- Lightning-fast gaming Supports 1080p 240Hz at 4.4ms and 4K 60Hz at 17ms



The UHZ35 is one of Optoma's most compact and hassle-free 4K UHD DuraCore laser projectors to date. Designed for maintenance-free continuous operation, it delivers powerful image performance with flexible installation features and extensive connectivity options in a sleek, compact form factor, up to 34% smaller than previous Optoma models.¹

An added benefit, the UHZ35 features an external power supply offering more reliability, portability and energy efficiency.

Specifications

Display/image	055387668898, Colour: White
Display/image Display technology	DLP™
Resolution	UHD (3840x2160)
Brightness	3.500 lumens
Contrast ratio	500,000:1
Native aspect ratio	16:9
Aspect ratio - compatible	4:3,16:9,16:10
Keystone correction -	+/-30°
horizontal	.,
Keystone correction - vertical	+/-30°
Displayable colours (millions)	1073.4
Horizontal scan rate	15 ~ 140Khz
Vertical scan rate	24 ~ 240Hz
Uniformity	80%
Screen size	0.66m ~ 7.7m (26" ~ 303") diagonal
Lamp info	
Light source type	Laser
LASER life	30,000 hours
Optical	
Throw ratio	1.4:1 ~ 2.24:1
Projection distance (m)	1.3m - 9.4m
Zoom	1.6
Zoom type	Manual
Focal length (mm)	20.91 ~ 32.62
Native offset	116%
Connectivity	
Connections	Inputs 1 x HDMI 2.0, 1 x HDMI 2.0 (eARC)
	Outputs 1 x Audio 3.5mm, 1 x USB-A power 1.5A
	Control 1 x RJ45, 1 x RS232
	CONTOL FATIONO, FATIO202
General	
Noise level (min)	28dB
Noise level (max)	35dB
PC compatibility	UHD, FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4,43MHz
	SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p, 576i/p, 720p/50/60Hz) 1080i/50/60Hz) 1080p/50/60Hz)
3D compatibility	720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz) Yes (DLP 3D; PC frame sequential 120Hz 3D, Blu-ray DVD 3D)
3D compatibility 3D	Full 3D
Security IP rating	Security bar, Kensington Lock, Password protected interface
IP rating	IP6X 25 Ianguagaa Arabia Czach Daniah Dutah English Farsi
OSD / display languages	25 languages: Arabic, Czech, Danish, Dutch, English, Farsi, Finnish, French, German, Greek, Hungarian, Indonesian, Italian Japanese, Norwegian, Polish, Portuguese, Romanian, Russian Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish, Vietnamese
24/7 operation	Yes
360° operation	Yes
Operating conditions	0°C ~ 40°C, Max. Humidity 80%, Max. Altitude 10,00ft
Remote control	Card style
Speaker count	1
Watts per speaker	1 15W
watts per speaker In the box	AC power cord
	AC power cord Remote control with 1x CR2025 Battery Basic user manual
Input lag	4.40ms
Optional wireless models	UHDCast Pro
Power	
Power supply	External power supply, 100V ~ 240V, 50-60Hz
Power consumption (standby)	<0.5W
	126W
Power consumption (min)	
Power consumption (min) Power consumption (max)	185W
Power consumption (max)	185W
Power consumption (max) Weight and dimensions	185W 274 x 216 x 114

Copyright © 2024, Optoma and its logo is a registered trademark of Optoma Corporation. Optoma Europe Ltd is the licensee of the registered trademark. All other product names and company names used herein are for identification purposes only and may be trademarks or registered trademarks of their respective owners. Errors and omissions excepted, all specifications are subject to change without notice. All images are for representation purposes only and may be simulated. ¹ Based on the comparison of the 2023 Optoma mainstream laser projectors and its previous generation. ² Comparison of 2023 Optoma mainstream laser projectors. 06112024022141