



Environmental Certificates



[Newland](#)

**MLIR30B
NEWLAND | QUICK ASSEMBLY ELECTRIC HEIGHT
ADJUSTABLE BASE - 2 LEGS**

- quick assembly 2-leg, 3-stage electric height adjustable table base

- beam and leg columns with motors are all preassembled
- unfold leg columns and lock into place
- for use with NLxxxHAT tops
- width adjustable for 46"W to 76"W tops
- 3-stage base - range of adjustability without 1" thick top is 21.6" to 47.2"H
- easy to use up-down controller with digital read-out and four memory programmable positions
- dual motor with 265 lbs. lift capacity
- anti-collision sensor
- standby power consumption 0.1W / active power consumption 220W
- operates at 1.2" per second
- operating decibel - 42db
- 8' long power cord
- shipped partially assembled in 1 carton

Finish Options:

Base finish: Black or Tungsten



Specifications

Dimensions: 42.5"W x 22.8"D x 21.6"-47.1"H

Weight: 77.2 lbs / 35 kg

Volume: 2.9 ft³ / 0.08 m³
