



Environmental Certificates



[Newland](#)

**NL48243QHT
NEWLAND | 48"X24" HEIGHT ADJUSTABLE RECTANGULAR
TABLE - 2 LEGS**

Newland - simple and modular components combining classic design, quality and value to support a wide range of workspace applications. From private offices, open plan, meeting and training spaces, Newland offers functional and practical desking solutions that will stand the test of time.

- quick assembly electric height adjustable bases with leg columns preassembled to telescopic cross bar assembly including electric motors. Unfold leg columns, attach feet and worksurface support to base; fasten assembly to top; plug in connections and start to use
- 3-stage base. range of adjustability with 1" thick top is 22.6" to 48.2"H
- easy to use up-down controller with digital read-out and four memory programmable positions
- may be specified as complete tables or may order tops and bases separately
- dual motor with 265 lbs. lift capacity
- anti-collision sensor
- standby power consumption 0.1W. Active power consumption 220W
- operates at 1.2" per second
- operating decibel - 42db
- 8' long power cord
- meets applicable ANSI/BIFMA x5.5 standards
- laminate tops covered by Global's lifetime warranty
- five-year warranty on base components including electrical components and motorized parts
- ETL/CETL and Greenguard Certified
- shipped easy to assemble in 2 cartons
- worksurface is dimensioned to allow 1" gap around perimeter in a nominal footprint

Finish Options:

Laminate finish: Available in all Newland finishes

Base finish: Black or Tungsten



Specifications

Dimensions: 46"W x 23"D x 22.6"-48.2"H

Weight: 108 lbs / 48.99 kg

Volume: 5 ft³ / 0.14 m³
