

# ThinkPad T14s Gen 6 (AMD)

## PSREF

### Product Specifications Reference

## PERFORMANCE

### Processor

AMD Ryzen™ AI 7 PRO 360 (8C / 16T, 2.0 / 5.0GHz, 8MB L2 / 16MB L3)

### AI PC Category

Copilot+ PC

### NPU

Integrated AMD Ryzen™ AI, up to 50 TOPS

### Graphics

Integrated AMD Radeon™ 880M Graphics

### Chipset

AMD SoC Platform

### Memory

32GB Soldered LPDDR5x-7500

### Memory Slots

Memory soldered to systemboard, no slots, dual-channel

### Max Memory

32GB soldered memory, not upgradable

### Storage

512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

### Storage Support<sup>[1]</sup>

One drive, up to 1TB M.2 2280 SSD

### Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

### Card Reader

None

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Dolby Atmos®

### Camera

5.0MP + IR Discrete with Privacy Shutter

### Microphone

2x, 360°

### Battery

Integrated 58Wh

### Power Adapter

65W USB-C® (3-pin)

## DESIGN

### Display<sup>[2]</sup>

14" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, DBEF5, Touch

### Touchscreen

On-cell, 10-point Multi-touch

### Keyboard

Backlit, English

### Case Color

Black

### Case Material

Carbon Fiber Hybrid (Top), Aluminium (Bottom)

### Pen

Pen Not Supported

### Dimensions (WxDxH)<sup>[3]</sup>

313.6 x 219.4 x 16.9 mm (12.35 x 8.64 x 0.67 inches)

### Weight<sup>[4]</sup>

Starting at 1.37 kg (3.02 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro, English

### Bundled Software

None

## CONNECTIVITY

### Ethernet<sup>[5]</sup>

No Onboard Ethernet

### WLAN + Bluetooth<sup>[6]</sup>

Qualcomm® Wi-Fi® 7 NCM825, 802.11be 2x2 + BT5.3

### WWAN

Non-WWAN

### SIM Card

None

### NFC

None

### Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

### Optional Ports (configured)

None

### Docking

Various docking solutions supported via Thunderbolt™ / USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® T14s Gen 6 \(AMD\)](#)

## SECURITY & PRIVACY

### Smart Card Reader

None

### Security Chip

Discrete TPM 2.0 Enabled

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Other Security

- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)
- Ultrasonic Human Presence Detection

## MANAGEABILITY

### System Management

Non-DASH

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

3Y Premier Support Upgrade from 1Y Courier/Carry-in, CO2 Offset 0.5 ton (2nd Generation Carbon Offset Projects)

## ACCESSORIES

### Bundled Accessories<sup>[7]</sup>

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 10.0

### Other Certifications

Eyesafe® Certified 2.0

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

**TopSeller** : Yes **Announce Date** : 2024-10-23

**EAN / UPC / JAN** : 198155190575 **End of Support** : 2031-05-22

Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[3] The system dimensions may vary depending on configurations.

[4] The system weight is approximate and based on results in.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/2579?M=21M1002AAU>

## Premier Support - A direct 24x7x365 line to our most elite technicians.

Advanced technical support, 24x7x365, in more than 100 markets

Technical Account Managers for proactive relationship and escalation management

Comprehensive hardware & OEM software support

Priority on service delivery and repair parts

Single point of contact for simplified end-to-end case management

Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Copilot+PC



AMD

Copilot+PC



AMD

## Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support CPN (5WS1L42224)
BETTER	3Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L42431)
GOOD	4Y Premier Support upgrade from 3Y Premier Support (5WS0W86726)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**PSREF**  
Product Specifications  
Reference