

## PERFORMANCE

### Display Size

27"

### View Area

596.7x335.7 mm

### Panel

In-Plane Switching

### Backlight

WLED

### Aspect Ratio

16:9

### Resolution

2560x1440

### Pixel Pitch

0.2331x0.2331 mm

### Dot / Pixel Per Inch

109 dpi

### View Angle (H / V)

178° / 178°

### Response Time

0.5ms (MPRT) / 1ms (Level 4) / 2ms (Level 3) / 3ms (Level 2) / 4ms (Level 1)

### Color Support

1.07 Billion

### Refresh Rate

180Hz(DP)

### Brightness

450 cd/m<sup>2</sup>

### Contrast Ratio

1000:1

### Color Gamut

99% sRGB, 90% DCI-P3

### Screen Surface Treatment

Anti-glare

### Curvature

None

### Camera

None

### Microphone

None

### Speakers

None

### Power Consumption (Typical / Maximum)

22W / 46W

### Power Adapter

Integrated

### Touchscreen

None

### Smart System

None

## DESIGN

### Stand

Tilt, Swivel, Pivot, Height Adjust Stand

### Case Color

Black

### Side Bezel Width

1.2 mm

### Mounting

Supports VESA mount 100mm

### ThinkCentre® M Series Support

None

### Dimensions (WxDxH)<sup>[1]</sup>

- Lowest Position | 613.2 x 258.8 x 385 mm (24.14 x 10.19 x 15.16 inches)
- Highest Position | 613.2 x 258.8 x 505 mm (24.14 x 10.19 x 19.88 inches)
- Head Only | 613.2 x 52.2 x 367.8 mm (24.14 x 2.06 x 14.48 inches)

### Packaging Dimensions (WxDxH)

680 x 161 x 527 mm (26.77 x 6.34 x 20.75 inches)

### Weight<sup>[2]</sup>

- Monitor With Stand | 6.14 kg (13.54 lbs)
- Monitor Head Only | 4.30 kg (9.47 lbs)

### Packaging Weight

8.16 kg (17.96 lbs)

## CONNECTIVITY

### USB Port

None

### Video Connector

2x HDMI® 2.1 TMDS, 1x DP 1.4

### Network Connectivity

None

## SERVICE

### Base Warranty

1-year

## CERTIFICATIONS

### Environmental Certification

EU Energy Efficiency Level (Level-F)

### Ergonomic Certification

TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free

### Sync Technology

None

### Special Features

- DisplayHDR™ 400
- ClearMR 6000
- AMD FreeSync™  
AMD FreeSync™ technology only can work with AMD Radeon™ series graphics card.
- VESA Adaptive Sync
- Lenovo® Artery (Lenovo® Accessories and Display Manager) Support  
Lenovo® Artery supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).  
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- Natural Low Blue Light

## SOFTWARE

### Operating System

Support Windows® 10, Windows® 11

## ACCESSORIES

### Video Cables

DP Cable

## MODEL

Announce Date : 2024-06-14  
EAN / UPC / JAN : 0198153418459 / 198153418459 / None



Product image is a sample, it may not match the real color of this model

Note:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/2575?M=67C5GAC1US>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...



### Kensington MicroSaver 2.0 Twin Cable Lock from Lenovo

4XEON80915

Protect your devices. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Twin Head Cable Lock from Lenovo. It locks 2 devices with the same cable lock. Engineered to be the smallest, strongest l...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference