

# Product data sheet

Specifications



APC Smart-UPS On-Line,  
1500VA, Rackmount 2U, 120V, 6x  
NEMA 5-15R outlets, Network  
Card, Extended runtime, W/ rail kit,  
TAA

SRT1500RMXLA-NCUS

## Overview

Lead time Usually in Stock

## Main

Main Input Voltage	120 V
Product or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	120 V
Kw Rating	1350 W
Rated power in VA	1500 VA
Input Connection Type	NEMA 5-15P
output connection type	6 NEMA 5-15R
Number of rack unit	2U
Cable length	6 ft (1.8 m)
Number of cables	1
Provided equipment	CD with software
Range of Product	Smart-UPS On-Line

## Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Battery Type	Lead-Acid battery
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Voltage	48V
Battery Charge Power (Watts)	91 W rated
Battery Life	3...5 year(s)
Extendable Run Time	1

## General

Topology Double Conversion Online

product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

## Physical

color	Black
Height	3.3 in (8.5 cm)
Width	17.008 in (43.2 cm)
Depth	20.0000000000 in (50.8 cm)
Net Weight	48.5 lb(US) (22 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

## Input

Input Frequency	40 - 70 Hz auto-sensing
Efficiency at full load	108...150 V

## Output

Maximum configurable power in VA	1500 VA
Max Configurable Power (Watts)	1350 W
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Waveform Type	Sine wave
Harmonic distortion	Less than 2%
Crest factor	3 : 1
Bypass type	Built-in Bypass

## Conformance

Product Certifications	ENERGY STAR V2.0 (USA)
------------------------	------------------------

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-4...122 °F (-20...50 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Acoustic level	50 dBA
Online Thermal Dissipation	463 Btu/h
IP degree of protection	IP20

## Communications & Management

Free slots	0
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off (EPO)	Yes

## Surge Protection and Filtering

Surge energy rating	432 J
---------------------	-------

## Ordering and shipping details

GTIN	731304740575
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.7 in (24.6 cm)
Package 1 Width	29.5 in (74.9 cm)
Package 1 Length	23.4 in (59.4 cm)
Package 1 Weight	65.3 lb(US) (29.6 kg)

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

## Sustainability


**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)



Transparency RoHS/REACH

## Well-being performance

 **Rohs Exemption Information** [Yes](#)

## Environmental Certifications

 **Energy Star®** [ENERGY STAR UPS V2.0 \(USA\)](#)

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

**Eu Rohs Directive** [Compliant with Exemptions](#)

**China Rohs Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

**Environmental Disclosure** [Product Environmental Profile](#)

**Circularity Profile** [End of Life Information](#)

Image of product / Alternate images

Alternative

---

