

## PERFORMANCE

### Processor

AMD Ryzen™ 5 8540U (6C / 12T, 3.2 / 4.9GHz, 6MB L2 / 16MB L3)

### NPU

None

### Graphics

Integrated AMD Radeon™ 740M Graphics

### Chipset

AMD SoC Platform

### Memory

8GB Soldered DDR5-5600 + 8GB SO-DIMM DDR5-5600

### Memory Slots

One memory soldered to systemboard, one DDR5 SO-DIMM slot, dual-channel capable

### Max Memory<sup>[1]</sup>

Up to 24GB (8GB soldered + 16GB SO-DIMM) DDR5-5600 offering

### Storage

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

### Max Storage Support<sup>[2][3]</sup>

Up to two drives, 2x M.2 SSD  
• M.2 2242 SSD up to 1TB

### Storage Slot

Two M.2 2242 PCIe® 4.0 x4 slots

### Card Reader

SD Card Reader

### Optical

None

### Audio Chip

High Definition (HD) Audio

### Speakers

Stereo speakers, 2W x2, optimized with Dolby Audio™

### Camera

FHD 1080p + IR with Privacy Shutter

### Microphone

2x, Array

### Battery

60Wh

### Power Adapter

65W Round Tip (3-pin)

## DESIGN

### Display<sup>[4]</sup>

15.3" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC, 60Hz, Touch

### Touchscreen

On-cell, 10-point Multi-touch

### Keyboard

Backlit, French / English

### Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

### Case Color

Cosmic Blue

### Surface Treatment

IMR (Top), Texture (Bottom)

### Case Material

PC-ABS (Top), PC-ABS (Bottom)

### Pen

Pen Not Supported

### Dimensions (WxDxH)<sup>[5][6]</sup>

343.4 x 239.5 x 17.9-18.9 mm (13.52 x 9.43 x 0.70-0.74 inches)

### Weight<sup>[7]</sup>

Starting at 1.63 kg (3.59 lbs)

## SOFTWARE

### Operating System

Windows® 11 Home, French / English

### Bundled Software

Office Trial

## CONNECTIVITY

### WLAN + Bluetooth<sup>[8]</sup>

Wi-Fi® 6, 802.11ax 2x2 + BT5.3

### WWAN

Non-WWAN

### Ethernet

No Onboard Ethernet

### Standard Ports

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with USB PD 3.0 and DisplayPort™ 1.2
- 1x HDMI® 1.4
- 1x Headphone / microphone combo jack (3.5mm)
- 1x SD card reader
- 1x Power connector

### Docking

Various docking solutions supported via USB-C®.

For more compatible docking solutions, please visit [Docking for IdeaPad® Slim 3 15AHP10](#)

## SECURITY & PRIVACY

### Security Chip

Microsoft® Pluton TPM 2.0 Enabled

### Fingerprint Reader

None

### Other Security

- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications<sup>[9]</sup>

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant

### Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

### Mil-Spec Test

MIL-STD-810H military test passed (21 test items)

## MODEL

<b>TopSeller</b>	: No	<b>Announce Date</b>	: 2025-03-10
<b>EAN / UPC / JAN</b>	: 198157182585	<b>End of Support</b>	: 2031-01-09



Product image is a sample, it may not match the real color of this model  
• Lenovo reserves the right to change specifications without notice.  
To see more note information, please access the [web page](#).

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo Powered USB-C Travel Hub

4X90S92381

Travel-Ready Productivity Powerhouse; One-stop travel docking is finally here. Connect and charge new and legacy devices wherever you happen to be. Sleek and compact, the Lenovo Powered USB-C Travel Hub fits unlimited...

## Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38620)
BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0T73714)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K75663)

Please click [here](#) to view the full list of accessories.

**Lenovo**

**PSREF**  
Product Specifications  
Reference